

61.115.23 ✓ ACTIVE

TE Internal #: 61-0115-023-000

Standard Circular Connectors, 132A Contact Current Rating (Max),
Power, Brass, 58 Shell Size, Metal, Pin

[View on TE.com >](#)



Connectors > Circular Connectors > Standard Circular Connectors



Sealable: **No**

Contact Current Rating (Max): **132 A**

Circuit Application: **Power**

Shell Base Material: **Brass**

Circular Connector Shell Size: **58**

Features

Product Type Features

| | |
|------------|-------|
| Sealable | No |
| Shell Type | Metal |

Body Features

| | |
|---------------------|-------|
| Shell Base Material | Brass |
|---------------------|-------|

Contact Features

| | |
|---------------------------------|-------|
| Contact Current Rating (Max) | 132 A |
| Circular Connector Contact Type | Pin |

Termination Features

| | |
|------------------------------------|-------|
| Termination Method to Wire & Cable | Crimp |
|------------------------------------|-------|

Housing Features

| | |
|-------------------------------|----|
| Circular Connector Shell Size | 58 |
|-------------------------------|----|

Operation/Application

| | |
|---------------------|------------|
| Durability Rating | 500 Cycles |
| Circuit Application | Power |



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

| | |
|---|---|
| EU RoHS Directive 2011/65/EU | Compliant with Exemptions |
| EU ELV Directive 2000/53/EC | Compliant with Exemptions |
| China RoHS 2 Directive MIIT Order No 32, 2016 | Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | <p>Current ECHA Candidate List: JUN 2020 (209)</p> <p>Candidate List Declared Against: JUN 2020 (209)</p> <p>SVHC > Threshold: Pb (2.5% in Component)</p> <p>Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.</p> |
| Halogen Content | Not Yet Reviewed for halogen content |
| Solder Process Capability | Not reviewed for solder process capability |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

| | |
|--|---|
| <p>TE Part # C0-0207-000-000 BATTERY CRIMPING TOOL</p> | <p>TE Part # C0-0209-000-000 CRIMP SPLITS MK 12-C FOR 35 SQUARE</p> |
|--|---|

Customers Also Bought



TE Part #1986713-7
PWR TB DBL PIN 7P, 15.00 PCB



TE Part #1-87230-6
32 MODII HDR DRRA UNSHRD .100




TE Part #61-0114-023-000
CONTACT PIN 10 MM



TE Part #BKA145N00580200000
923 EXTENSION, SPEEDTEC-READY



TE Part #60-0103-023-000
CONTACT SOCKET 10 MM




TE Part #5054324002
RNF-100-1-1/2-3-SP



TE Part #6-1437624-6
PKG60B1/8=KNOB PLASTIC BLK 1/8



TE Part #1103431-1
MALE INSERT, CRIMP, 12-POS. TYPE III+



TE Part #1-1393767-6
R10-E2X2-115V=R10



TE Part #1-1393767-3
R10-E2X2-V28=R10

Documents

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_61-0115-023-000_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_61-0115-023-000_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_61-0115-023-000_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

61-0115-023-000

English