



Safety Data Sheet according to Regulation (EC) No 1907/2006

Page 1 of 11

SDS No. : 304659
V004.3

LOCTITE LB 8014 known as 8014, Food Grade

Revision: 20.10.2016
printing date: 26.11.2020

Replaces version from: 12.06.2015

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

LOCTITE LB 8014 known as 8014, Food Grade

Contains:

Calcium dihydroxide

1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use:
Lubricant

1.3. Details of the supplier of the safety data sheet

Henkel Ltd
Wood Lane End
HP2 4RQ Hemel Hempstead

Great Britain

Phone: +44 1442 278000
Fax-no.: +44 1442 278071

ua-productsafety.uk@uk.henkel.com

1.4. Emergency telephone number

24 Hours Emergency Tel: +44 (0)1442 278497

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification (CLP):

Skin irritation	Category 2
H315 Causes skin irritation.	
Serious eye damage	Category 1
H318 Causes serious eye damage.	
Chronic hazards to the aquatic environment	Category 3
H412 Harmful to aquatic life with long lasting effects.	

2.2. Label elements

Label elements (CLP):

Hazard pictogram:



Signal word:	Danger
Hazard statement:	H315 Causes skin irritation. H318 Causes serious eye damage. H412 Harmful to aquatic life with long lasting effects.
Precautionary statement: Prevention	P273 Avoid release to the environment. P280 Wear eye protection/face protection.
Precautionary statement: Response	P302+P352 IF ON SKIN: Wash with plenty of water. P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

2.3. Other hazards

None if used properly.

Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

General chemical description:

Lubricant

Declaration of the ingredients according to CLP (EC) No 1272/2008:

Hazardous components CAS-No.	EC Number REACH-Reg No.	content	Classification
Calcium dihydroxide 1305-62-0	215-137-3 01-2119475151-45	10- < 20 %	Skin Irrit. 2; Dermal H315 Eye Dam. 1 H318 STOT SE 3; Inhalation H335
zinc oxide 1314-13-2	215-222-5 01-2119463881-32	0,25- < 2,5 %	Aquatic Acute 1 H400 Aquatic Chronic 1 H410

For full text of the H - statements and other abbreviations see section 16 "Other information".

Substances without classification may have community workplace exposure limits available.

SECTION 4: First aid measures

4.1. Description of first aid measures

Inhalation:

Move to fresh air. If symptoms persist, seek medical advice.

Skin contact:

Rinse with running water and soap.

Seek medical advice.

Eye contact:

Rinse immediately with plenty of running water (for 10 minutes). Seek medical attention if necessary.

Ingestion:

Rinse out mouth, drink 1-2 glasses of water, do not induce vomiting.

Seek medical advice.

4.2. Most important symptoms and effects, both acute and delayed

EYE: Irritation, conjunctivitis.

SKIN: Redness, inflammation.

4.3. Indication of any immediate medical attention and special treatment needed

See section: Description of first aid measures

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media:

Carbon dioxide, foam, powder

Extinguishing media which must not be used for safety reasons:

None known

5.2. Special hazards arising from the substance or mixture

Oxides of carbon, oxides of nitrogen, irritating organic vapors.
Sulphur oxides

5.3. Advice for firefighters

Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear.

Additional information:

In case of fire, keep containers cool with water spray.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Avoid contact with skin and eyes.

Wear protective equipment.

Ensure adequate ventilation.

6.2. Environmental precautions

Do not empty into drains / surface water / ground water.

6.3. Methods and material for containment and cleaning up

For small spills wipe up with paper towel and place in container for disposal.

For large spills absorb onto inert absorbent material and place in sealed container for disposal.

6.4. Reference to other sections

See advice in section 8

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Avoid skin and eye contact.

See advice in section 8

Hygiene measures:

Good industrial hygiene practices should be observed.

Do not eat, drink or smoke while working.

Wash hands before work breaks and after finishing work.

7.2. Conditions for safe storage, including any incompatibilities

Store in original containers at 8-21°C (46.4-69.8°F) and do not return residual materials to containers as contamination may reduce the shelf life of the bulk product.

7.3. Specific end use(s)
Lubricant**SECTION 8: Exposure controls/personal protection****8.1. Control parameters****Occupational Exposure Limits**Valid for
Great Britain

Ingredient [Regulated substance]	ppm	mg/m ³	Value type	Short term exposure limit category / Remarks	Regulatory list
Calcium dihydroxide 1305-62-0 [CALCIUM HYDROXIDE]		5	Time Weighted Average (TWA):		EH40 WEL
Calcium dihydroxide 1305-62-0 [CALCIUM DIHYDROXIDE]		5	Time Weighted Average (TWA):	Indicative	ECLTV
Talc (Mg ₃ H ₂ (SiO ₃) ₄) 14807-96-6 [TALC, RESPIRABLE DUST]		1	Time Weighted Average (TWA):		EH40 WEL

Occupational Exposure LimitsValid for
Ireland

Ingredient [Regulated substance]	ppm	mg/m ³	Value type	Short term exposure limit category / Remarks	Regulatory list
White mineral oil (petroleum) 8042-47-5 [MINERAL OIL USED IN METAL WORKING, INHALABLE FRACTION]		0,2	Time Weighted Average (TWA):		IR_OEL
White mineral oil (petroleum) 8042-47-5 [MINERAL OIL, PURE, HIGHLY & SEVERELY REFINED, INHALABLE FRACTION]		5	Time Weighted Average (TWA):		IR_OEL
Calcium dihydroxide 1305-62-0 [CALCIUM HYDROXIDE]		5	Time Weighted Average (TWA):		IR_OEL
Calcium dihydroxide 1305-62-0 [CALCIUM DIHYDROXIDE]		5	Time Weighted Average (TWA):	Indicative	ECLTV
Talc (Mg ₃ H ₂ (SiO ₃) ₄) 14807-96-6 [TALC, RESPIRABLE DUST]		0,8	Time Weighted Average (TWA):		IR_OEL
Talc (Mg ₃ H ₂ (SiO ₃) ₄) 14807-96-6 [TALC, TOTAL INHALABLE DUST]		10	Time Weighted Average (TWA):		IR_OEL
Zinc oxide 1314-13-2 [ZINC OXIDE, FUME (RESPIRABLE FRACTION)]		2	Time Weighted Average (TWA):		IR_OEL
Zinc oxide 1314-13-2 [ZINC OXIDE, FUME (RESPIRABLE FRACTION)]		10	Short Term Exposure Limit (STEL):		IR_OEL

Predicted No-Effect Concentration (PNEC):

Name on list	Environmental Compartment	Exposure period	Value				Remarks
			mg/l	ppm	mg/kg	others	
Calcium dihydroxide 1305-62-0	aqua (freshwater)					0,49 mg/L	
Calcium dihydroxide 1305-62-0	aqua (marine water)					0,32 mg/L	
Calcium dihydroxide 1305-62-0	aqua (intermittent releases)					0,49 mg/L	
Calcium dihydroxide 1305-62-0	sewage treatment plant (STP)					3 mg/L	
Calcium dihydroxide 1305-62-0	soil				1080 mg/kg		
zinc oxide 1314-13-2	aqua (freshwater)					20,6 µg/L	
zinc oxide 1314-13-2	aqua (marine water)					6,1 µg/L	
zinc oxide 1314-13-2	sewage treatment plant (STP)					100 µg/L	
zinc oxide 1314-13-2	sediment (freshwater)				117,8 mg/kg		
zinc oxide 1314-13-2	sediment (marine water)				56,5 mg/kg		
zinc oxide 1314-13-2	soil				35,6 mg/kg		

Derived No-Effect Level (DNEL):

Name on list	Application Area	Route of Exposure	Health Effect	Exposure Time	Value	Remarks
Calcium dihydroxide 1305-62-0	Workers	Inhalation	Acute/short term exposure - local effects		4 mg/m ³	
Calcium dihydroxide 1305-62-0	Workers	Inhalation	Long term exposure - local effects		1 mg/m ³	
Calcium dihydroxide 1305-62-0	General population	Inhalation	Acute/short term exposure - local effects		4 mg/m ³	
Calcium dihydroxide 1305-62-0	General population	Inhalation	Long term exposure - local effects		1 mg/m ³	
zinc oxide 1314-13-2	Workers	Inhalation	Long term exposure - systemic effects		5 mg/m ³	
zinc oxide 1314-13-2	Workers	dermal	Long term exposure - systemic effects		83 mg/kg bw/day	
zinc oxide 1314-13-2	Workers	inhalation	Long term exposure - local effects		0,5 mg/m ³	
zinc oxide 1314-13-2	General population	Inhalation	Long term exposure - systemic effects		2,5 mg/m ³	
zinc oxide 1314-13-2	General population	dermal	Long term exposure - systemic effects		83 mg/kg bw/day	
zinc oxide 1314-13-2	General population	oral	Long term exposure - systemic effects		0,83 mg/kg bw/day	

Biological Exposure Indices:

None

8.2. Exposure controls:

Engineering controls:

Ensure good ventilation/extraction.

Respiratory protection:

Ensure adequate ventilation.

An approved mask or respirator fitted with an organic vapour cartridge should be worn if the product is used in a poorly ventilated area

Filter type: A (EN 14387)

Hand protection:

Chemical-resistant protective gloves (EN 374).

Suitable materials for short-term contact or splashes (recommended: at least protection index 2, corresponding to > 30 minutes permeation time as per EN 374):

nitrile rubber (NBR; ≥ 0.4 mm thickness)

Suitable materials for longer, direct contact (recommended: protection index 6, corresponding to > 480 minutes permeation time as per EN 374):

nitrile rubber (NBR; ≥ 0.4 mm thickness)

This information is based on literature references and on information provided by glove manufacturers, or is derived by analogy with similar substances. Please note that in practice the working life of chemical-resistant protective gloves may be considerably shorter than the permeation time determined in accordance with EN 374 as a result of the many influencing factors (e.g. temperature). If signs of wear and tear are noticed then the gloves should be replaced.

Eye protection:

Safety glasses with sideshields or chemical safety goggles should be worn if there is a risk of splashing.

Protective eye equipment should conform to EN166.

Skin protection:

Wear suitable protective clothing.

Protective clothing should conform to EN 14605 for liquid splashes or to EN 13982 for dusts.

Advices to personal protection equipment:

The information provided on personal protective equipment is for guidance purposes only. A full risk assessment should be conducted prior to using this product to determine the appropriate personal protective equipment to suit local conditions.

Personal protective equipment should conform to the relevant EN standard.

SECTION 9: Physical and chemical properties**9.1. Information on basic physical and chemical properties**

Appearance	paste paste white
Odor	mild
Odour threshold	No data available / Not applicable
pH	No data available / Not applicable
Initial boiling point	No data available / Not applicable
Flash point	154 °C (309.2 °F); calculated
Decomposition temperature	No data available / Not applicable
Vapour pressure	No data available / Not applicable
Density	No data available / Not applicable
Bulk density	No data available / Not applicable
Viscosity	No data available / Not applicable
Viscosity (kinematic)	No data available / Not applicable
Explosive properties	No data available / Not applicable
Solubility (qualitative) (Solvent: Water)	Insoluble

Solidification temperature	No data available / Not applicable
Melting point	No data available / Not applicable
Flammability	No data available / Not applicable
Auto-ignition temperature	No data available / Not applicable
Explosive limits	No data available / Not applicable
Partition coefficient: n-octanol/water	No data available / Not applicable
Evaporation rate	No data available / Not applicable
Vapor density	No data available / Not applicable
Oxidising properties	No data available / Not applicable

9.2. Other information

No data available / Not applicable

SECTION 10: Stability and reactivity

10.1. Reactivity

Reaction with strong acids.
Reacts with strong oxidants.

10.2. Chemical stability

Stable under recommended storage conditions.

10.3. Possibility of hazardous reactions

See section reactivity

10.4. Conditions to avoid

Stable

10.5. Incompatible materials

See section reactivity.

10.6. Hazardous decomposition products

Oxides of carbon.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

General toxicological information:

The mixture is classified based on the available hazard information for the ingredients as defined in the classification criteria for mixtures for each hazard class or differentiation in Annex I to Regulation (EC) No 1272/2008. Relevant available health/ecological information for the substances listed under Section 3 is provided in the following.

Oral toxicity:

May cause irritation to the digestive tract.

Skin irritation:

Causes skin irritation.

Eye irritation:

Causes serious eye damage.

Acute oral toxicity:

Hazardous components CAS-No.	Value type	Value	Route of application	Exposure time	Species	Method
Calcium dihydroxide 1305-62-0	LD50	> 7.340 mg/kg	oral		rat	OECD Guideline 401 (Acute Oral Toxicity)
zinc oxide 1314-13-2	LD50	> 5.000 mg/kg	oral		rat	OECD Guideline 401 (Acute Oral Toxicity)

Acute inhalative toxicity:

Hazardous components CAS-No.	Value type	Value	Route of application	Exposure time	Species	Method
zinc oxide 1314-13-2	LC50	> 5,7 mg/l	aerosol	4 h	rat	OECD Guideline 403 (Acute Inhalation Toxicity)

Acute dermal toxicity:

Hazardous components CAS-No.	Value type	Value	Route of application	Exposure time	Species	Method
Calcium dihydroxide 1305-62-0	LD50	> 2.500 mg/kg	dermal		rat	OECD Guideline 402 (Acute Dermal Toxicity)

Skin corrosion/irritation:

Hazardous components CAS-No.	Result	Exposure time	Species	Method
Calcium dihydroxide 1305-62-0	irritating	4 h	rabbit	OECD Guideline 404 (Acute Dermal Irritation / Corrosion)
zinc oxide 1314-13-2	not irritating		rabbit	not specified

Serious eye damage/irritation:

Hazardous components CAS-No.	Result	Exposure time	Species	Method
Calcium dihydroxide 1305-62-0	Category 1 (irreversible effects on the eye)		rabbit	OECD Guideline 405 (Acute Eye Irritation / Corrosion)
zinc oxide 1314-13-2	slightly irritating		rabbit	not specified

Respiratory or skin sensitization:

Hazardous components CAS-No.	Result	Test type	Species	Method
zinc oxide 1314-13-2	not sensitising	Guinea pig maximisation test	guinea pig	OECD Guideline 406 (Skin Sensitisation)

Germ cell mutagenicity:

Hazardous components CAS-No.	Result	Type of study / Route of administration	Metabolic activation / Exposure time	Species	Method
Calcium dihydroxide 1305-62-0	negative	bacterial reverse mutation assay (e.g Ames test)	with and without		OECD Guideline 471 (Bacterial Reverse Mutation Assay)
zinc oxide 1314-13-2	negative	bacterial reverse mutation assay (e.g Ames test)	with and without		not specified

SECTION 12: Ecological information**General ecological information:**

The mixture is classified based on the available hazard information for the ingredients as defined in the classification criteria for mixtures for each hazard class or differentiation in Annex I to Regulation (EC) No 1272/2008. Relevant available health/ecological information for the substances listed under Section 3 is provided in the following.

12.1. Toxicity**Ecotoxicity:**

Do not empty into drains / surface water / ground water.
Harmful to aquatic life with long lasting effects.

Hazardous components CAS-No.	Value type	Value	Acute Toxicity Study	Exposure time	Species	Method
Calcium dihydroxide 1305-62-0	LC50	50,6 mg/l	Fish	96 h	Oncorhynchus mykiss	OECD Guideline 203 (Fish, Acute Toxicity Test)
Calcium dihydroxide 1305-62-0	EC50	49,1 mg/l	Daphnia	48 h	Daphnia magna	OECD Guideline 202 (Daphnia sp. Acute Immobilisation Test)
Calcium dihydroxide 1305-62-0	EC50	184,57 mg/l	Algae	72 h	Pseudokirchnerella subcapitata	OECD Guideline 201 (Alga, Growth Inhibition Test)
	NOEC	48 mg/l	Algae	72 h	Pseudokirchnerella subcapitata	OECD Guideline 201 (Alga, Growth Inhibition Test)
Calcium dihydroxide 1305-62-0	EC20	229,2 mg/l	Bacteria	3 h	activated sludge of a predominantly domestic sewage	OECD Guideline 209 (Activated Sludge, Respiration Inhibition Test)
Calcium dihydroxide 1305-62-0	NOEC	32 mg/l	chronic Daphnia	14 d	Crangon septemspinosa	OECD Guideline 202 (Daphnia sp. Chronic Immobilisation Test)
zinc oxide 1314-13-2	LC50	> 1.000 mg/l	Fish		Leuciscus idus	OECD Guideline 203 (Fish, Acute Toxicity Test)
zinc oxide 1314-13-2	NOEC	0,017 mg/l	Algae	72 h	Selenastrum capricornutum (new name: Pseudokirchnerella subcapitata)	OECD Guideline 201 (Alga, Growth Inhibition Test)
	EC50	0,17 mg/l	Algae	72 h	Selenastrum capricornutum (new name: Pseudokirchnerella subcapitata)	OECD Guideline 201 (Alga, Growth Inhibition Test)
zinc oxide 1314-13-2	NOEC	500 mg/l	Bacteria			not specified

12.2. Persistence and degradability**Persistence and Biodegradability:**

No data available.

12.3. Bioaccumulative potential / 12.4. Mobility in soil**Mobility:**

Cured adhesives are immobile.

Bioaccumulative potential:

No data available.

12.5. Results of PBT and vPvB assessment

Hazardous components CAS-No.	PBT/vPvB
Calcium dihydroxide 1305-62-0	Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.
zinc oxide 1314-13-2	Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.

12.6. Other adverse effects

No data available.

SECTION 13: Disposal considerations**13.1. Waste treatment methods**

Product disposal:

Dispose of in accordance with local and national regulations.

Contribution of this product to waste is very insignificant in comparison to article in which it is used

Disposal of uncleaned packages:

After use, tubes, cartons and bottles containing residual product should be disposed of as chemically contaminated waste in an authorised legal land fill site or incinerated.

Disposal must be made according to official regulations.

Waste code

14 06 03 - other solvents and solvent mixtures

The valid EWC waste code numbers are source-related. The manufacturer is therefore unable to specify EWC waste codes for the articles or products used in the various sectors. The EWC codes listed are intended as a recommendation for users. We will be happy to advise you.

SECTION 14: Transport information

14.1. UN number

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.2. UN proper shipping name

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.3. Transport hazard class(es)

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.4. Packing group

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.5. Environmental hazards

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.6. Special precautions for user

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.7. Transport in bulk according to Annex II of Marpol and the IBC Code

not applicable

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

VOC content < 3 %
(2010/75/EC)

15.2. Chemical safety assessment

A chemical safety assessment has not been carried out.

SECTION 16: Other information

The labelling of the product is indicated in Section 2. The full text of all abbreviations indicated by codes in this safety data sheet are as follows:

- H315 Causes skin irritation.
- H318 Causes serious eye damage.
- H335 May cause respiratory irritation.
- H400 Very toxic to aquatic life.
- H410 Very toxic to aquatic life with long lasting effects.

Further information:

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.

Relevant changes in this safety data sheet are indicated by vertical lines at the left margin in the body of this document. Corresponding text is displayed in a different color on shadowed fields.