



Safety Data Sheet according to Regulation (EC) No 1907/2006

Page 1 of 12

LOCTITE SF INI5 known as Loctite INI 5, 35ml En/De

SDS No. : 478309
V003.0

Revision: 16.09.2019
printing date: 26.11.2020

Replaces version from: 18.05.2017

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

LOCTITE SF INI5 known as Loctite INI 5, 35ml En/De

1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use:

Primer

1.3. Details of the supplier of the safety data sheet

Henkel Ltd
Wood Lane End
HP2 4RQ Hemel Hempstead

Great Britain

Phone: +44 1442 278000

Fax-no.: +44 1442 278071

ua-productsafety.uk@henkel.com

1.4. Emergency telephone number

24 Hours Emergency Tel: +44 (0)1442 278497

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification (CLP):

Acute toxicity Category 4

H302 Harmful if swallowed.

Route of Exposure: Oral

Acute toxicity Category 4

H312 Harmful in contact with skin.

Route of Exposure: Dermal

Skin irritation Category 2

H315 Causes skin irritation.

Serious eye irritation Category 2

H319 Causes serious eye irritation.

|| **Chronic hazards to the aquatic environment** Category 4

|| **H413 May cause long lasting harmful effects to aquatic life.**

2.2. Label elements

Label elements (CLP):

Hazard pictogram:**Contains**

Diethyl-phenyl-propyl-dihydropyridine

N-Butylaniline

Aniline

Signal word:

Warning

Hazard statement:

H302+H312 Harmful if swallowed or in contact with skin.

H315 Causes skin irritation.

H319 Causes serious eye irritation.

H413 May cause long lasting harmful effects to aquatic life.

Supplemental information

Contains: Aniline May produce an allergic reaction.

Precautionary statement:

P273 Avoid release to the environment.

Prevention

P280 Wear protective gloves/protective clothing.

Precautionary statement:

P302+P352 IF ON SKIN: Wash with plenty of soap and water.

Response

P337+P313 If eye irritation persists: Get medical advice/attention.

2.3. Other hazards

None if used properly.

Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.

SECTION 3: Composition/information on ingredients**3.2. Mixtures**

Declaration of the ingredients according to CLP (EC) No 1272/2008:

Hazardous components CAS-No.	EC Number REACH-Reg No.	content	Classification
Diethyl-phenyl-propyl-dihydropyridine 34562-31-7	252-091-3	50- 100 %	Acute Tox. 4; Oral H302 Acute Tox. 4; Dermal H312 Skin Irrit. 2; Dermal H315 Eye Irrit. 2 H319 Aquatic Chronic 4 H413
N-Butylaniline 1126-78-9	214-425-6	1- < 5 %	Acute Tox. 4; Oral H302
Aniline 62-53-3	200-539-3	0,1- < 0,2 %	Aquatic Acute 1 H400 Acute Tox. 3; Dermal H311 Skin Sens. 1 H317 STOT RE 1 H372 Muta. 2 H341 Eye Dam. 1 H318 Acute Tox. 3; Inhalation H331 Acute Tox. 3; Oral H301 Carc. 2 H351
Copper naphthenate 1338-02-9	215-657-0	0,1- < 0,25 %	Flam. Liq. 3 H226 Acute Tox. 4; Oral H302 Aquatic Acute 1 H400 Aquatic Chronic 1 H410

For full text of the H - statements and other abbreviations see section 16 "Other information".
Substances without classification may have community workplace exposure limits available.

SECTION 4: First aid measures

4.1. Description of first aid measures

Inhalation:

Move to fresh air. If symptoms persist, seek medical advice.

Skin contact:

Rinse with running water and soap.
Seek medical advice.

Eye contact:

Rinse immediately with plenty of running water (for 10 minutes). Seek medical attention if necessary.

Ingestion:

Rinse out mouth, drink 1-2 glasses of water, do not induce vomiting.
Seek medical advice.

4.2. Most important symptoms and effects, both acute and delayed

SKIN: Redness, inflammation.

SKIN: Rash, Urticaria.

INGESTION: Nausea, vomiting, diarrhea, abdominal pain.

EYE: Irritation, conjunctivitis.

4.3. Indication of any immediate medical attention and special treatment needed

See section: Description of first aid measures

SECTION 5: Firefighting measures**5.1. Extinguishing media****Suitable extinguishing media:**

Carbon dioxide, foam, powder

Extinguishing media which must not be used for safety reasons:

High pressure waterjet

5.2. Special hazards arising from the substance or mixture

In the event of a fire, carbon monoxide (CO), carbon dioxide (CO₂) and nitrogen oxides (NO_x) can be released.

5.3. Advice for firefighters

Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear.

Additional information:

In case of fire, keep containers cool with water spray.

SECTION 6: Accidental release measures**6.1. Personal precautions, protective equipment and emergency procedures**

Avoid skin and eye contact.

6.2. Environmental precautions

Do not let product enter drains.

6.3. Methods and material for containment and cleaning up

For small spills wipe up with paper towel and place in container for disposal.

For large spills absorb onto inert absorbent material and place in sealed container for disposal.

Dispose of contaminated material as waste according to Section 13.

6.4. Reference to other sections

See advice in section 8

SECTION 7: Handling and storage**7.1. Precautions for safe handling**

Use only in well-ventilated areas.

Avoid skin and eye contact.

Prolonged or repeated skin contact should be avoided to minimise any risk of sensitisation.

See advice in section 8

Hygiene measures:

Wash hands before work breaks and after finishing work.

Do not eat, drink or smoke while working.

Good industrial hygiene practices should be observed.

7.2. Conditions for safe storage, including any incompatibilities

Refer to Technical Data Sheet

7.3. Specific end use(s)

Primer

SECTION 8: Exposure controls/personal protection**8.1. Control parameters****Occupational Exposure Limits**Valid for
Great Britain

Ingredient [Regulated substance]	ppm	mg/m ³	Value type	Short term exposure limit category / Remarks	Regulatory list
Aniline 62-53-3 [ANILINE]	1	4	Time Weighted Average (TWA):		EH40 WEL
Aniline 62-53-3 [ANILINE]			Skin designation:	Can be absorbed through the skin.	EH40 WEL

Occupational Exposure LimitsValid for
Ireland

Ingredient [Regulated substance]	ppm	mg/m ³	Value type	Short term exposure limit category / Remarks	Regulatory list
Aniline 62-53-3 [ANILINE]	1	3,8	Time Weighted Average (TWA):		IR_OEL
Aniline 62-53-3 [ANILINE]			Skin designation:	Can be absorbed through the skin.	IR_OEL

Biological Exposure Indices:

None

8.2. Exposure controls:

Engineering controls:

Ensure good ventilation/extraction.

Respiratory protection:

Ensure adequate ventilation.

An approved mask or respirator fitted with an organic vapour cartridge should be worn if the product is used in a poorly ventilated area

Filter type: A (EN 14387)

Hand protection:

Chemical-resistant protective gloves (EN 374).

Suitable materials for short-term contact or splashes (recommended: at least protection index 2, corresponding to > 30 minutes permeation time as per EN 374):

nitrile rubber (NBR; >= 0.4 mm thickness)

Suitable materials for longer, direct contact (recommended: protection index 6, corresponding to > 480 minutes permeation time as per EN 374):

nitrile rubber (NBR; >= 0.4 mm thickness)

This information is based on literature references and on information provided by glove manufacturers, or is derived by analogy with similar substances. Please note that in practice the working life of chemical-resistant protective gloves may be considerably shorter than the permeation time determined in accordance with EN 374 as a result of the many influencing factors (e.g. temperature). If signs of wear and tear are noticed then the gloves should be replaced.

Eye protection:
Wear protective glasses.
Protective eye equipment should conform to EN166.

Skin protection:
Wear suitable protective clothing.
Protective clothing should conform to EN 14605 for liquid splashes or to EN 13982 for dusts.

Advices to personal protection equipment:

The information provided on personal protective equipment is for guidance purposes only. A full risk assessment should be conducted prior to using this product to determine the appropriate personal protective equipment to suit local conditions. Personal protective equipment should conform to the relevant EN standard.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Appearance	liquid
	liquid
	amber
Odor	mild
Odour threshold	No data available / Not applicable
pH	No data available / Not applicable
Melting point	No data available / Not applicable
Solidification temperature	No data available / Not applicable
Initial boiling point	No data available / Not applicable
Flash point	> 93,4 °C (> 200.12 °F)
Evaporation rate	No data available / Not applicable
Flammability	No data available / Not applicable
Explosive limits	No data available / Not applicable
Vapour pressure	9 mm hg
Relative vapour density:	No data available / Not applicable
Density	0,97 g/cm ³
()	
Bulk density	No data available / Not applicable
Solubility	No data available / Not applicable
Solubility (qualitative)	Insoluble
Partition coefficient: n-octanol/water	No data available / Not applicable
Auto-ignition temperature	No data available / Not applicable
Decomposition temperature	No data available / Not applicable
Viscosity	No data available / Not applicable
Viscosity (kinematic)	No data available / Not applicable
Explosive properties	No data available / Not applicable
Oxidising properties	No data available / Not applicable

9.2. Other information

No data available / Not applicable

SECTION 10: Stability and reactivity

10.1. Reactivity

Strong oxidizing agents.
Reaction with strong bases
Reaction with strong acids.

10.2. Chemical stability

Stable under recommended storage conditions.

10.3. Possibility of hazardous reactions

See section reactivity

10.4. Conditions to avoid

Stable under normal conditions of storage and use.

10.5. Incompatible materials

See section reactivity.

10.6. Hazardous decomposition products

Oxides of carbon.

Oxides of nitrogen.

SECTION 11: Toxicological information**11.1. Information on toxicological effects****Acute oral toxicity:**

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Species	Method
N-Butylaniline 1126-78-9	LD50	1.620 mg/kg	rat	not specified
Aniline 62-53-3	Acute toxicity estimate (ATE)	100 mg/kg		Expert judgement
Aniline 62-53-3	LD50	200 - 2.000 mg/kg	rat	EU Method B.1 (Acute Toxicity (Oral))
Copper naphthenate 1338-02-9	LD50	2.000 mg/kg	rat	not specified

Acute dermal toxicity:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Species	Method
Copper naphthenate 1338-02-9	LD50	> 5.000 mg/kg	rabbit	
Copper naphthenate 1338-02-9	LD50	> 7.940 mg/kg	rabbit	

Acute inhalative toxicity:

No substance data available.

No data available.

Skin corrosion/irritation:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result	Exposure time	Species	Method
Diethyl-phenyl-propyl- dihydropyridine 34562-31-7	irritating			Expert judgement

Serious eye damage/irritation:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result	Exposure time	Species	Method
Diethyl-phenyl-propyl- dihydropyridine 34562-31-7	irritating			Expert judgement

Respiratory or skin sensitization:

No substance data available.
No data available.

Germ cell mutagenicity:

No data available.

Carcinogenicity

No data available.

Reproductive toxicity:

No data available.

STOT-single exposure:

No data available.

STOT-repeated exposure::

No data available.

Aspiration hazard:

No data available.

SECTION 12: Ecological information

General ecological information:

Do not empty into drains / surface water / ground water.

12.1. Toxicity

Toxicity (Fish):

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
Aniline 62-53-3	NOEC	4,67 mg/l	28 d	Oryzias latipes	OECD Guideline 204 (Fish, Prolonged Toxicity Test: 14-day Study)
Aniline 62-53-3	LC50	61 - 65 mg/l	48 h	Leuciscus idus	DIN 38412-15
Copper naphthenate 1338-02-9	LC50	0,161 mg/l	96 h	Oncorhynchus mykiss	OECD Guideline 203 (Fish, Acute Toxicity Test)

Toxicity (Daphnia):

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
Aniline 62-53-3	EC50	0,3 mg/l	48 h	Daphnia magna	not specified

Chronic toxicity to aquatic invertebrates

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
Aniline 62-53-3	NOEC	0,0126 mg/l	21 d	Daphnia magna	OECD 211 (Daphnia magna, Reproduction Test)

Toxicity (Algae):

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
Aniline 62-53-3	NOEC	10 mg/l	96 h	Selenastrum capricornutum (new name: Pseudokirchneriella subcapitata)	Algal Assay Procedure (AAP); Bottle Test; U.S. Environm. Prot. Agency (EPA)
Aniline 62-53-3	EC50	19 mg/l	96 h	Selenastrum capricornutum (new name: Pseudokirchneriella subcapitata)	Algal Assay Procedure (AAP); Bottle Test; U.S. Environm. Prot. Agency (EPA)

Toxicity to microorganisms

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
Aniline 62-53-3	EC0	1.000 mg/l	18 h		not specified

12.2. Persistence and degradability

No data available for the product.

Hazardous substances CAS-No.	Result	Test type	Degradability	Exposure time	Method
Aniline 62-53-3	readily biodegradable	aerobic	72 - 90 %	30 d	EU Method C.4-E (Determination of the "Ready" Biodegradability Closed Bottle Test)
Aniline 62-53-3	inherently biodegradable	aerobic	> 90 %	4 d	OECD Guideline 302 B (Inherent biodegradability: Zahn-Wellens/EMPA Test)

12.3. Bioaccumulative potential

No data available for the product.

Hazardous substances CAS-No.	Bioconcentration factor (BCF)	Exposure time	Temperature	Species	Method
Aniline 62-53-3	91	24 h		Pseudokirchneriella subcapitata (reported as Selenastrum capricornutum)	not specified

12.4. Mobility in soil

Cured adhesives are immobile.

Hazardous substances CAS-No.	LogPow	Temperature	Method
Aniline 62-53-3	0,9		not specified

12.5. Results of PBT and vPvB assessment

This mixture does not contain any substances that are assessed to be a PBT or vPvB.

12.6. Other adverse effects

No data available.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Product disposal:

Dispose of in accordance with local and national regulations.

Contribution of this product to waste is very insignificant in comparison to article in which it is used

Disposal of uncleaned packages:

After use, tubes, cartons and bottles containing residual product should be disposed of as chemically contaminated waste in an authorised legal land fill site or incinerated.

Disposal must be made according to official regulations.

Waste code

08 04 09 waste adhesives and sealants containing organic solvents and other dangerous substances

The valid EWC waste code numbers are source-related. The manufacturer is therefore unable to specify EWC waste codes for the articles or products used in the various sectors. The EWC codes listed are intended as a recommendation for users. We will be happy to advise you.

SECTION 14: Transport information

- 14.1. UN number**
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.2. UN proper shipping name**
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.3. Transport hazard class(es)**
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.4. Packing group**
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.5. Environmental hazards**
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.6. Special precautions for user**
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.7. Transport in bulk according to Annex II of Marpol and the IBC Code**
not applicable

SECTION 15: Regulatory information**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture**

VOC content < 3 %
(2010/75/EC)

15.2. Chemical safety assessment

A chemical safety assessment has not been carried out.

SECTION 16: Other information

The labelling of the product is indicated in Section 2. The full text of all abbreviations indicated by codes in this safety data sheet are as follows:

- H226 Flammable liquid and vapor.
- H301 Toxic if swallowed.
- H302 Harmful if swallowed.
- H311 Toxic in contact with skin.
- H312 Harmful in contact with skin.
- H315 Causes skin irritation.
- H317 May cause an allergic skin reaction.
- H318 Causes serious eye damage.
- H319 Causes serious eye irritation.
- H331 Toxic if inhaled.
- H341 Suspected of causing genetic defects.
- H351 Suspected of causing cancer.
- H372 Causes damage to organs through prolonged or repeated exposure.
- H400 Very toxic to aquatic life.
- H410 Very toxic to aquatic life with long lasting effects.
- H413 May cause long lasting harmful effects to aquatic life.

Further information:

This Safety Data Sheet has been produced for sales from Henkel to parties purchasing from Henkel, is based on Regulation (EC) No 1907/2006 and provides information in accordance with applicable regulations of the European Union only. In that respect, no statement, warranty or representation of any kind is given as to compliance with any statutory laws or regulations of any other jurisdiction or territory other than the European Union. When exporting to territories other than the European Union, please consult with the respective Safety Data Sheet of the concerned territory to ensure compliance or liaise with Henkel's Product Safety and Regulatory Affairs Department (ua-productsafety.de@henkel.com) prior to export to other territories than the European Union.

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.

Dear Customer,

Henkel is committed to creating a sustainable future by promoting opportunities along the entire value chain. If you would like to contribute by switching from a paper to the electronic version of SDS, please contact the local Customer Service representative. We recommend to use a non-personal email address (e.g. SDS@your_company.com).

Relevant changes in this safety data sheet are indicated by vertical lines at the left margin in the body of this document. Corresponding text is displayed in a different color on shadowed fields.