

Productname : EMV 35
Ref.Nr.: BDS001663_3_20190508 (EN)

Creationdate : 08.05.19 Version : 3.4
Replaces: BDS001663_20181106

SECTION 1: Identification of the substance/mixture and of the company/undertaking**1.1. Product identifier**

EMV 35
Aerosol

1.2. Relevant identified uses of the substance or mixture and uses advised against

Conduction electric/thermal

1.3. Details of the supplier of the safety data sheet

CRC Industries Europe bvba
Touwslagerstraat 1
9240 Zele
Belgium
Tel.: +32(0)52/45.60.11
Fax.: +32(0)52/45.00.34
E-mail : hse@crcind.com

Subsidiaries		Tel	Fax
CRC Industries Finland Oy	Smedsgatan 3-5 LT4, PL62, 08101 LOJO	+358/(19)32.921	
CRC Industries France	6, avenue du marais, C.S. 90028, 95102 Argenteuil Cedex	01.34.11.20.00	01.34.11.09.96
CRC Industries Deutschland GmbH	Südring 9, D-76473 Iffezheim	(07229) 303 0	(07229)30 32 66
CRC INDUSTRIES IBERIA S.L.U.	GREMIO DEL CUERO-PARC.96, POLIGONO INDUSTRI. DE HONTORIA, 40195 SEGOVIA	0034/921.427.546	0034/921.436.270
CRC Industries Sweden	Laxfiskevägen 16, 433 38 Partille	0046/31 706 84 80	0046/31 27 39 91

1.4. Emergency telephone number

CRC Industries Europe, Belgium: Tel.: +32(0)52/45.60.11 (office hours)

SECTION 2: Hazards identification**2.1. Classification of the substance or mixture****Classification according to Regulation (EC) No 1272/2008**

Physical: Aerosols, category 1
Extremely flammable aerosol.



Productname :	EMV 35	Creationdate :	08.05.19 Version : 3.4
Ref.Nr.:	BDS001663_3_20190508 (EN)	Replaces:	BDS001663_20181106

Pressurised container: May burst if heated.

Classification is based on test data.

Health: Eye irritation, category 2
Causes serious eye irritation.
Specific target organ toxicity - single exposure, category 3
May cause drowsiness or dizziness.

Classification based on calculation method.

Environment: Hazardous to the aquatic environment, chronic category 2
Toxic to aquatic life with long lasting effects.

Classification based on calculation method.

2.2. Label elements

Labelling according to Regulation (EC) No 1272/2008

Product identifier: Contains:
n-butyl acetate
propyl acetate

Hazard pictogram(s):



Signal word: Danger

Hazard statement(s): H222 : Extremely flammable aerosol.
H229 : Pressurised container: May burst if heated.
H319 : Causes serious eye irritation.
H336 : May cause drowsiness or dizziness.
H411 : Toxic to aquatic life with long lasting effects.

Precautionary statement(s): P102 : Keep out of reach of children.
P210 : Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
P211 : Do not spray on an open flame or other ignition source.
P251 : Do not pierce or burn, even after use.
P261 : Avoid breathing dust/fume/gas/mist/vapours/spray.
P271 : Use only outdoors or in a well-ventilated area.
P410/412 : Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F.
P501-2 : Dispose of contents/container to an authorised waste collection point.

Supplemental Hazard information: Repeated exposure may cause skin dryness or cracking.

2.3. Other hazards

No information available

SECTION 3: Composition/information on ingredients

3.1. Substances



Productname : EMV 35
Ref.Nr.: BDS001663_3_20190508 (EN)

Creationdate : 08.05.19 Version : 3.4
Replaces: BDS001663_20181106

Not applicable.

3.2. Mixtures

Hazardous ingredient	Registration number	CAS-nr.	EC-nr	w/w %	Hazard Class and Category	Hazard statement	Notes
dimethyl ether	01-2119472128-37	115-10-6	204-065-8	25-50	Flam. Gas 1, Press. Gas	H220,H280	A
Copper	01-2119480154-42	7440-50-8	231-159-6	<25	Hazardous to the aquatic environment, acute category 1, Hazardous to the aquatic environment, chronic category 1	H400,H410	B,M
propyl acetate	01-2119484620-39	109-60-4	203-686-1 [1]	<20	Flam. Liq. 2, Eye Irrit. 2, STOT SE 3	H225,H319,H336	B
n-butyl acetate	01-2119485493-29	123-86-4	204-658-1	<20	Flam. Liq. 3, STOT SE 3	H226,H336	
1-methoxy-2-propanol; monopropylene glycol methyl ether	01-2119457435-35	107-98-2	203-539-1	5-10	Flam. Liq. 3, STOT SE 3	H226,H336	A
butanone; ethyl methyl ketone	01-2119457290-43	78-93-3	201-159-0	1-5	Flam. Liq. 2, Eye Irrit. 2, STOT SE 3	H225,H319,H336	A
isopentyl acetate	01-2119548408-32	123-92-2	204-662-3	<2.5	Flam. Liq. 3	H226	A
1H-Imidazole-1-ethanol, 2-(8-heptadecenyl)-4,5-dihydro-	01-2119777867-13	95-38-5	202-414-9	<2.5	Skin Corr. 1C, Acute Tox. 4, STOT RE 2, Aquatic Acute 1, Aquatic Chronic 1	H314,H302,H373,H400,H410	

Explanation notes

A : substance with Community workplace exposure limit

B : substance with national established workplace exposure limit

M : M acute = 10

(* Explanation phrases : see chapter 16)

SECTION 4: First aid measures

4.1. Description of first aid measures

Contact with eyes :	If substance has got into eyes, immediately wash out with plenty of water If eye irritation persists: Get medical advice/attention.
Contact with skin :	Take off contaminated clothing and wash before reuse. IF ON SKIN: Wash with plenty of soap and water. If skin irritation occurs: Get medical advice/attention.
Inhalation :	IF INHALED: Remove person to fresh air and keep comfortable for breathing. Call a POISON CENTER or doctor/physician if you feel unwell.
Ingestion :	If swallowed do not induce vomiting because of risk of aspiration into the



Productname :	EMV 35	Creationdate :	08.05.19 Version : 3.4
Ref.Nr.:	BDS001663_3_20190508 (EN)	Replaces:	BDS001663_20181106

lungs. If aspiration is suspected obtain immediate medical attention

4.2. Most important symptoms and effects, both acute and delayed

Inhalation :	Excessive inhalation of solvent vapours may give rise to nausea, headaches and dizziness
Ingestion :	After vomiting of swallowed product aspiration into lungs is likely. Solvents may induce chemical pneumonia. Symptoms : sore throat, abdominal pain, nausea, vomiting
Skin contact :	Irritating to skin Symptoms : redness and pain
Eye contact :	May cause irritation. Symptoms : redness and pain

4.3. Indication of any immediate medical attention and special treatment needed

General Advice :	If you feel unwell, seek medical advice (show the label where possible) If symptoms persist always call a doctor
-------------------------	---

SECTION 5: Firefighting measures

5.1. Extinguishing media

foam, carbon dioxide or dry agent

5.2. Special hazards arising from the substance or mixture

Aerosols may explode if heated above 50°C
Forms hazardous decomposition products
CO,CO2

5.3. Advice for firefighters

Keep container(s) exposed to fire cool, by spraying with water
In case of fire, do not breathe fumes

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Shut off all ignition sources
Ensure adequate ventilation
Wear suitable protective clothing and gloves.

6.2. Environmental precautions



Productname : EMV 35
Ref.Nr.: BDS001663_3_20190508 (EN)
Creationdate : 08.05.19 Version : 3.4
Replaces: BDS001663_20181106

Do not allow to enter public sewers and watercourses

6.3. Methods and material for containment and cleaning up

Absorb spillage in suitable inert material

6.4. Reference to other sections

For further information see section 8

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Keep away from heat and sources of ignition
Take precautionary measures against static discharges
Equipment should be earthed
Use explosion-proof electrical/ventilating/lighting/.../equipment.
Use only non-sparking tools.
Do not breathe aerosols or vapours.
Ensure adequate ventilation
Avoid contact with skin and eyes.
Wash thoroughly after use
Wear protective gloves/protective clothing/eye protection/face protection.

7.2. Conditions for safe storage, including any incompatibilities

Pressurized container : protect from sunlight and do not expose to temperatures exceeding 50°C.
Keep out of reach of children.

7.3. Specific end use(s)

Conduction electric/thermal

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Exposure limits :

Hazardous ingredient	CAS-nr.	method	
EU established exposure limits:			
1-methoxy-2-propanol; monopropylene glycol methyl ether	107-98-2	TWA	100 ppm
		STEL	150 ppm
propyl acetate	109-60-4	TWA	840 mg/m3



Productname : EMV 35
Ref.Nr.: BDS001663_3_20190508 (EN)

Creationdate : 08.05.19 Version : 3.4
Replaces: BDS001663_20181106

		STEL	840 mg/m3
dimethyl ether	115-10-6	TWA	1000 ppm
isopentyl acetate	123-92-2	TWA	50 ppm
		STEL	100 ppm
butanone; ethyl methyl ketone	78-93-3	TWA	200 ppm
		STEL	300 ppm
National established exposure limits, United Kingdom			
1-methoxy-2-propanol; monopropylene glycol methyl ether	107-98-2	TWA	100 ppm
		STEL	150 ppm
propyl acetate	109-60-4	TWA	200 ppm
		STEL	250 ppm
dimethyl ether	115-10-6	TWA	400 ppm
		STEL	500 ppm
n-butyl acetate	123-86-4	TWA	150 ppm
		STEL	200 ppm
Copper	7440-50-8	TWA	1 mg/m3 (dust)
		STEL	2 mg/m3 (dust)
butanone; ethyl methyl ketone	78-93-3	TWA	200 ppm
		STEL	300 ppm
National established exposure limits, Ireland			
1-methoxy-2-propanol; monopropylene glycol methyl ether	107-98-2	TWA	100 ppm
		STEL	150 ppm
propyl acetate	109-60-4	TWA	200 ppm
		STEL	250 ppm
dimethyl ether	115-10-6	TWA	1000 ppm
		STEL	-
n-butyl acetate	123-86-4	TWA	150 ppm
		STEL	200 ppm
isopentyl acetate	123-92-2	TWA	50 ppm
		STEL	100 ppm
butanone; ethyl methyl ketone	78-93-3	TWA	200 ppm
		STEL	300 ppm

8.2. Exposure controls

Control procedures :

Ensure adequate ventilation
 Keep away from heat and sources of ignition
 Take precautionary measures against static discharges

Personal protection :

Take precautions to avoid contact with skin and eyes when handling the product.
 In all cases handle and use the product in accordance with good industrial hygiene practices.
 Ensure adequate ventilation

Inhalation :

In case of insufficient ventilation, wear suitable respiratory equipment.

recommended respiratory protection:

Air purifying respirator equipped with organic gas/vapor cartridge (type A)

hands and skin :

When handling the product wear chemical-resistant gloves (standard EN 374).



Productname :	EMV 35	Creationdate :	08.05.19 Version : 3.4
Ref.Nr.:	BDS001663_3_20190508 (EN)	Replaces:	BDS001663_20181106

	Use a reusable glove with a minimum breakthrough time of 30 minutes. The breakthrough time of the glove should be longer than the total duration of product use. If work lasts longer than the breakthrough time, gloves should be changed part-way through.
Recommended gloves:	Nitrile
eyes :	Wear safety eyewear according to EN 166.
Environmental protection:	Avoid release to the environment. Collect spillage.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

(for aerosols data for the product without propellant)

Apperance : physical state :	DME propelled liquid.
colour :	Copper.
odour :	Solvent.
pH :	Not applicable.
Boiling point/range :	Not available.
Flash point :	< 0 °C (Closed Cup)
Evaporation rate :	Not available.
Explosion limits : upper limit :	Not available.
lower limit :	Not available.
Vapour pressure :	Not available.
Relative density :	1.3 g/cm ³ (@ 20°C).
Solubility in water :	Insoluble in water
Auto-ignition :	> 150 °C
Viscosity :	Not applicable.

9.2. Other information

VOC = volatile organic compounds	738 g/l
----------------------------------	---------

SECTION 10: Stability and reactivity

10.1. Reactivity

No hazardous reactions known if used for its intended purpose

10.2. Chemical stability

Stable

10.3. Possibility of hazardous reactions



Productname : EMV 35
Ref.Nr.: BDS001663_3_20190508 (EN)

Creationdate : 08.05.19 Version : 3.4
Replaces: BDS001663_20181106

No hazardous reactions known if used for its intended purpose

10.4. Conditions to avoid

Avoid overheating

10.5. Incompatible materials

Strong oxidising agent

10.6. Hazardous decomposition products

CO,CO2

SECTION 11: Toxicological information

11.1. Information on toxicological effects

acute toxicity:	based on available data the classification criteria are not met
skin corrosion/irritation:	based on available data the classification criteria are not met
serious eye damage/irritation:	Causes serious eye irritation.
respiratory or skin sensitisation:	based on available data the classification criteria are not met
germ cell mutagenicity:	based on available data the classification criteria are not met
carcinogenicity:	based on available data the classification criteria are not met
toxicity for reproduction:	based on available data the classification criteria are not met
STOT-single exposure:	May cause drowsiness or dizziness.
STOT repeated exposure:	based on available data the classification criteria are not met
aspiration hazard:	based on available data the classification criteria are not met

Information on likely routes of exposure:

Inhalation :	Inhalation of solvent vapours may give rise to nausea, headaches and dizziness
Ingestion :	After vomiting of swallowed product aspiration into lungs is likely. Solvents may induce chemical pneumonia.
Skin contact :	Irritating to skin
Eye contact :	May cause irritation.

Toxicological data :

Hazardous ingredient	CAS-nr.	method	
1-methoxy-2-propanol; monopropylene glycol methyl ether	107-98-2	LD50 oral rat	4016 mg/kg
		LC50 inhal.rat	27596 mg/l
		LD50 derm.rabit	2000 mg/kg
dimethyl ether	115-10-6	LC50 inhal.rat	309 mg/l



Productname : EMV 35
Ref.Nr.: BDS001663_3_20190508 (EN)

Creationdate : 08.05.19 Version : 3.4
Replaces: BDS001663_20181106

n-butyl acetate	123-86-4	LD50 oral rat	10760 mg/kg
		LC50 inhal.rat	> 20 mg/l
		LD50 derm.rabit	> 1400 mg/kg
butanone; ethyl methyl ketone	78-93-3	LD50 oral rat	> 2000 mg/kg

SECTION 12: Ecological information

12.1. Toxicity

Hazardous to the aquatic environment, chronic category 2
Toxic to aquatic life with long lasting effects.

Ecotoxicological data:

Hazardous ingredient	CAS-nr.	method	
1-methoxy-2-propanol; monopropylene glycol methyl ether	107-98-2	LC50 fish	6812 mg/l
		EC50 daphnia	23300 mg/l
dimethyl ether	115-10-6	IC50 algae	154.9 mg/l
		LC50 fish	4.1 mg/l
		EC50 daphnia	4.4 mg/l
n-butyl acetate	123-86-4	IC50 algae	647 mg/l
		LC50 fish	18 mg/l
		EC50 daphnia	44 mg/l

12.2. Persistence and degradability

No experimental data available

12.3. Bioaccumulative potential

No experimental data available

12.4. Mobility in soil

Insoluble in water

12.5. Results of PBT and vPvB assessment

No information available

12.6. Other adverse effects

No experimental data available
GWP (global warming potential): 0



Productname : EMV 35
Ref.Nr.: BDS001663_3_20190508 (EN)

Creationdate : 08.05.19 Version : 3.4
Replaces: BDS001663_20181106

SECTION 13: Disposal considerations**13.1. Waste treatment methods****SECTION 14: Transport information****14.1. UN number**

UN-number : 1950

14.2. UN proper shipping name

Proper shipping name: AEROSOLS

14.3. Transport hazard class(es)

Class: 2.1
ADR/RID - Classification code: 5F

14.4. Packing group

Packing group: Not applicable.

14.5. Environmental hazards

ADR/RID - Environmentally
hazardous: No
IMDG - Marine pollutant: No
IATA/ICAO - Environmentally
hazardous: No

14.6. Special precautions for user

ADR/RID - Tunnelcode: (D)
IMDG - Ems: F-D, S-U
IATA/ICAO - PAX: 203
IATA/ICAO - CAO: 203

14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

Not applicable.

SECTION 15: Regulatory information

Productname : EMV 35	Creationdate : 08.05.19 Version : 3.4
Ref.Nr.: BDS001663_3_20190508 (EN)	Replaces: BDS001663_20181106

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

The Safety Data Sheet is compiled according to the current European requirements.
 Regulation (EC) No 1907/2006 (REACH)
 Regulation (EC) No 1272/2008 (CLP)
 Dir. 2013/10/EU, 2008/47/EC amendment of the aerosol dispenser directive 75/324/EEC.

15.2. Chemical safety assessment

No information available

SECTION 16: Other information

*Explanation hazard statements: H220 : Extremely flammable gas.
 H225 : Highly flammable liquid and vapour.
 H226 : Flammable liquid and vapour.
 H280 : Contains gas under pressure; may explode if heated.
 H302 : Harmful if swallowed.
 H314 : Causes severe skin burns and eye damage.
 H319 : Causes serious eye irritation.
 H336 : May cause drowsiness or dizziness.
 H373 : May cause damage to organs through prolonged or repeated exposure .
 H400 : Very toxic to aquatic life.
 H410 : Very toxic to aquatic life with long lasting effects.

acronyms and synonyms: TWA = time weight average
 STEL = short time exposure limit
 VOC = volatile organic compounds
 PBT = persistant bioaccumulative toxic
 vPvB = very persitant very bioaccumulative

This product should be stored, handled and used in accordance with good industrial hygiene practices and in conformity with any legal regulation.

The information contained herewith is based on the present state of our knowledge and is intended to describe our products from the point of view of safety requirements. It does not guarantee any specific properties.

Apart from any fair dealing for purposes of study, research and review of health, safety and environmental risks, no part of these documents may be reproduced by any process without written permission from CRC.