



Applications

Suitable for automated soldering equipment used for production/manufacturing of small motors, transformers, relays and magnet coils.

Standard

IEC 60317-0-1:2014
IEC 60317-51
NEMA MW 82-C

Insulation Coatings	: Polyurethane 180
Dimensions	: 0.07mm to 1.6mm Gr 2 (2L)

Mechanical Properties (For 0.3mm)

Elongation	: >30%
Springiness	: <50
Adherence – Flexibility	: Excellent
Resistance to Abrasion	: >67.75N

Electrical Properties

Breakdown Voltage	: 7kV
-------------------	-------

Thermal Properties

Temperature Index	: 180
Cut through	: 2min ≥ 230°C
Heat Shock	: 1d, 1/2 h ≥ 200°C

Chemical Properties

Solvent Test	: 4H
Solderability	: 390°
Resistance to Refrigerants	: -

Bare Conductor – Copper Characteristics (Annealed Condition)

Electrical Resistivity @ 20°C	: 0.017241Ωmm ² /m
Temperature Coefficient @ 20°C	: 0.00694°C
Specific Weight	: 8.89 Gr/cm ³
Ultimate Tensile Strength	: 22 – 30 kg/mm ²
Primary Insulation Colour	: Transparent / Natural

Part Number	Bare Copper Conductor						Enamelled Coat		
	Nominal Conductor Diameter	Conductor Tolerance	Cross Sectional Area	Gauge		Nominal Electrical Resistance	Nominal weight of conductor per 1km @ density 8.89 Gr/cm ³	Min. Diameter Increase	Max. overall Diameter
	mm	mm	mm ²	SWG	AWG	Ω/m @ 20°C	Grams	Grade 2 (2L) mm	Grade 2 (2L) mm
ECW0.2	0.2	0.003	0.03142	35/36	32	0.5441	0.27932	0.027	0.239
ECW0.224	0.224	0.003	0.039413	34/35	31	0.4338	0.35038	0.029	0.266
ECW0.25	0.25	0.004	0.049094	33	30	0.334	0.43644	0.032	0.297
ECW0.315	0.315	0.004	0.077941	30	28	0.2193	0.69289	0.035	0.367
ECW0.4	0.4	0.005	0.12568	27/28	26	0.136	1.11729	0.04	0.459
ECW0.5	0.5	0.005	0.196375	25	24	0.08706	1.74577	0.045	0.566
ECW0.56	0.56	0.006	0.246333	24/25	23/24	0.06736	2.18989	0.047	0.63
ECW0.71	0.71	0.007	0.395971	22	21/22	0.04198	3.52017	0.053	0.789
ECW0.80	0.8	0.008	0.50272	21/22	20	0.03401	4.46918	0.056	0.884
ECW1.0	1	0.01	0.7855	19/20	18	0.02176	6.983095	0.063	1.094
ECW1.25	1.25	0.013	1.227344	17/18	16/17	0.01393	10.91108	0.067	1.349
ECW1.5	1.5	0.015	1.767375	16/17	14/15	0.009	15.71196	0.071	1.606

Part Number Table

Description	CSA	AWG	Reel Length (m)	Part Number
Wire, Copper Enamelled, 35 SWG	0.0357mm ²	32AWG	1,850	ECW0.2
Wire, Copper Enamelled, 34 SWG	0.0428mm ²	31AWG	1,430	ECW0.224
Wire, Copper Enamelled, 33 SWG	0.0506mm ²	30AWG	1,120	ECW0.25
Wire, Copper Enamelled, 30 SWG	0.0779mm ²	28AWG	720	ECW0.315
Wire, Copper Enamelled, 27 SWG	0.136mm ²	26AWG	450	ECW0.4
Wire, Copper Enamelled, 25 SWG	0.203mm ²	24AWG	290	ECW0.5
Wire, Copper Enamelled, 24 SWG	0.246mm ²	23AWG	230	ECW0.56
Wire, Copper Enamelled, 22 SWG	0.396mm ²	21AWG	140	ECW0.71
Wire, Copper Enamelled, 21 SWG	0.515mm ²	20AWG	125	ECW0.80
Wire, Copper Enamelled, 19 SWG	0.815mm ²	18AWG	70	ECW1.0
Wire, Copper Enamelled, 18 SWG	1.17mm ²	16AWG	47	ECW1.25
Wire, Copper Enamelled, 16 SWG	2.08mm ²	15AWG	32	ECW1.5

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.