Three Phase AC Filter Capacitors





Application

RoHS Compliant

These capacitors are for use on AC/DC power converters and inverters (drives) that are very common today in the field of power electronics. Traction drives, wind power converters and solar inverters are examples of those applications. Capacitors are usually used in AC filters but also non-sinusoidal and pulsed currents are suitable for them.

Construction

Self-healing process, technology MKP and special metallizing patterns ensure low stray inductance and subsequently very high reliability. Capacitor elements are enclosed in Al cylindrical case filled with non toxic soft resin. Overpressure disconnector assures safe operation and right disconnection at the extreme conditions (high temperature, overloading) and at the end of operating life. three phase units with plastic terminal. Discharge resistors are not used.

Installation instruction

Capacitors should be mounted in vertical position. Max torques are mentioned in table below. Flexible connection cables have to ensure movement of the capacitor top about 20 mm due to right function of the overpressure disconnector.

Characteristics	MP005147	MP005207	MP005208	MP005148	MP005149	MP005150
Capacitance (C _N)	3 × 200μF, ±5%	3 × 65μF, ±5% 3 × 100uF, ±5%		3 × 102uF, ±5%	3 × 55.7µF, ±5%	
Voltage AC rms (sinusoidal) (URMS)	450	450V		80V	600V	850V
Voltage AC (UAC)	640V AC 750		V AC	850V AC	1200V AC	
Voltage DC (Upc)	-				1800V DC	
Non-recurrent surge voltage (u _s)	1480V		-	1480V	2700V	
Maximum RMS Current (Imax)	3 × 80A	3 ×	3 × 43A 3 × 80A		3 × 60A	3 × 80A
Maximum Peak Current (Î)	3 × 8.8kA	3 × 1.4kA	3 × 2.3kA	3 × 3.6kA	3 × 8.7kA	3 × 4.3kA
Maximum Surge Current (is)	3 × 24kA	3 × 3.9kA	3 × 6,8kA	3 × 11kA	3 × 24kA	3 × 12.7kA
Series Resistance (Rs)	3 × 0.6mΩ	3 × 1.1mΩ	3 × 1.3mΩ	3 × 0.8mΩ	3 × 0.55mΩ	3 × 0.5mΩ
Dielectric Dissipation Factor (tan⁵o)	2 × 10 ⁻⁴					
Self Inductance (Ls)	130nH	90nH	110nH 1		30nH	
Thermal Conditions						
Case Temperature (Θ _{min/max})	-40°C to +85°C					
Maximum Hotspot Temperature (Онѕ)	85°C					
Storage Temperature (Ostorage)	-40 to +85°C					
Thermal Resistance (OHS-Ocase) (Rth)	1.6 K/W	3.3 K/W	2.1 K/W	1.9 K/W	1.6 K/W	1.6 K/W
Service Life						
Lifetime Expectancy (h)	150000					
at Hotspot Temperature	+65°C					

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro




Three Phase AC Filter Capacitors



Characteristics	MP005147	MP005207	MP005208	MP005148	MP005149	MP005150
Failure Rate (FIT)	100					
Dimensions						
Diameter "D"	136mm	85mm	110mm	136mm		
Height " H "	261mm	220mm	220mm	220mm	nm 261mm	
Terminal Height	47mm	35mm	35mm	47mm		
Terminal	3 phase, double way, Delta connection					
Weight	3.8kg	1.5kg	2.2kg	3.3kg	3.8kg	
Torques						
Torque for M5 - Screw	- 2.5 Nm -					
Max. Torque for M7 Screw	5 Nm	2.5 Nm	-	5Nm		
Max. Torque for M12 - Bolt	7 Nm					
Test Data (Routine Test)						
Test Voltage Between Terminals (UT/T) (V AC)	675V AC/10s		795V AC/10s		900V AC/10s	1275V AC/10s
Test Voltage Terminals-Case (UT/C) (V AC)	3600V AC /10s 4000V AC /10s					
Drawing Diagram	Dg1	Dg2		Dg1		

Diagram



Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro



Three Phase AC Filter Capacitors



Part Number Table

Description	Drawing	Part Number
AC Filter Capacitor, 3 Phase, 3 × 200µF, 450V	Dg1	MP005147
AC Filter Capacitor, 3 Phase, 3 × 65μF, 450V	Dg2	MP005207
AC Filter Capacitor, 3 Phase, 3 × 65μF, 530V	Dg2	MP005208
AC Filter Capacitor, 3 Phase, 3 × 100µF, 530V	Dg1	MP005148
AC Filter Capacitor, 3 Phase, 3 × 102μF, 600V	Dg1	MP005149
AC Filter Capacitor, 3 Phase, 3 × 55.7μF, 850V	Dg1	MP005150

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

