



QUARTZ-GOLD-LTE4 (EU)

4G Dual LAN Small Footprint Gigabit Ethernet Industrial Router



Key Features

- European 4G / LTE bands
- ARM Cortex A7 900MHz
- 2 x Gigabit Ethernet ports (100/1000Mb)
- Strong resistance to electromagnetic interference
- Built-in watch dog, multi-link detection
- Small footprint industrial design
- Excellent temperature endurance -30 to +75 deg C
- VPN: OpenVPN, PPTP, L2TP, GRE, IPSec
- WAN failover network redundancy
- WiFi: 2.4GHz and 5GHz
- Shock and vibration resistance
- 2 x LAN, 1 x WAN / 1 x LAN

General Description

Siretta's QUARTZ-GOLD router is a high performance industrial router designed for transferring large amounts of data via the European LTE Cat 4 cellular network, with dual built in Gigabit Ethernet ports. The QUARTZ-GOLD's fast data transfer capability reaches up to 150Mbps download and up to 50Mbps upload speed. It also has fall-back to 3G/UMTS communication, should 4G/LTE be unavailable. It is well suited for IoT/mobile broadband applications, offering reliable, secure wireless connectivity.

The QUARTZ-GOLD router has a robust design, encased in a small sized, metal enclosure, making it ideal for deployment in industrial embedded applications. The QUARTZ-GOLD software supports VPN security allowing the router to be used in commercial as

well as industrial applications. The QUARTZ-GOLD router meets many of the needs for management of remote communication and therefore has applications in renewable energy, security, digital signage, transport, street furniture, traffic control, parking systems, environmental monitoring, and many other IoT/mobile broadband applications.

The QUARTZ-GOLD router comes as standard with a single SIM slot, dual port gigabit ethernet capability and optional GNSS capability, which means the router is ideal for asset tracking or access management applications.

Gigabit WAN failover is supported to provide network redundancy for your connected gigabit LAN using the fast LTE Cat 4 cellular network.

Additional Features

- » Supports DHCP server
- » Supports DNS proxy and Dynamic DNS (DNSS)
- » Supports timing operation
- » Supports LED status indication
- » Supports APN and VDPN wireless private network access
- » Supports 802.11n/ac WiFi (optional)
- » Optional GNSS
- » Local and remote management
- » SNMP network management, NTP support
- » WAN supports PPPoE, Static IP, DHCP Client (with 2 x LAN)



QUARTZ-GOLD-LTE4 (EU)

4G Dual LAN Small Footprint Gigabit Ethernet Industrial Router

General Features

- » 6 Bands LTE (European): 700(B28A), 800(B20), 900(B8), 1800(B3), 2100(B1), 2600(B7) MHz
- » 2 Bands UMTS: 900(B8), 2100(B1) MHz

Interfaces

- » 2 x Gigabit Ethernet - configurable (1 x LAN, 1 x LAN/ 1 x WAN)
- » 2 x LTE SMA female antenna interface
- » 1 x standard SIM/R-UIM interface
- » 1 x standard DC power interface
- » 1 x 5 pin terminal block connector
- » 1 x DC power (anti reverse)
- » 1 x RS232 serial interface
- » 2 x RP SMA WiFi interface

Optional Interfaces

- » 1 x GNSS antenna interface
- » 1 x RS485 serial interface

Environmental

- » Dimensions: 103mm x 73.5mm x 23.5mm (without antenna)
- » Weight: 320g (without accessories)
- » Operating Temperature Range: -30 to +75 deg C
- » Storage Temperature Range: -40 to +85 deg C
- » Relative Humidity: <95% Non-condensing

Approvals and Compliance

- » CE
- » RoHS
- » CCC

Power

- » Idle: 165mA @ +12VDC
- » Power supply: 7.5 - 32VDC
- » Online without WiFi: 195mA @ +12VDC
- » Online with WiFi: 235mA @ +12VDC

Network

Network Protocol

- » IPv4 and IPv6 (IPv6 is LAN Only)
- » PPPoE
- » UDP/TCP/ICMP/NTP/DHCP
- » HTTP/HTTPS
- » UPNP
- » SNMP

Network Features

- » LTE/LAN/WLAN failover
- » VLAN
- » Bandwidth management NAT/DMZ
- » IP passthrough/port redirection
- » Static/dynamic routing

Network Monitoring/Control

- » ICMP check
- » Traffic check
- » Traceroute
- » Data capture
- » Bandwidth graph
- » Data traffic graph
- » LinkCONNECT serial gateway
- » Syslog service
- » Remote web access



QUARTZ-GOLD-LTE4 (EU)

4G Dual LAN Small Footprint Gigabit Ethernet Industrial Router

Router Settings

Device Management

- » Local or remote GUI
- » CLI/Telnet command
- » M2M management platform (optional)
- » SSH management

Firewall and Filter

- » IP packet/Domain/MAC filter
- » Keyword filter
- » Access filter
- » Filter, domain name filter

LED Instruction

- » Cellular
- » LAN
- » LAN/WAN
- » WLAN

WLAN Mode

- » Access point
- » AP + WDS
- » Client
- » Wireless Ethernet bridge
- » WDS

VPN

- » IPSec
- » PPTP/L2TP client
- » GRE/IPIP
- » Open-VPN

WiFi (Optional)

- » Standard: IEEE 802.11n/ac

GNSS Tracking (Optional)

- » Sensivity: -160dBm
- » Accuracy: 2.5 CEP
- » Update rate: 1Hz @ 5GHz
- » Time to first fix:
Cold: 27 secs
Hot: 1 sec
- » Protocol: NMEA-0183.2.3V
- » Support: GPS, GLONASS, Galileo, QZSS

WAN Failover Support

- » 1 x Gigabit Ethernet WAN internet interface
- » 1 x Gigabit Ethernet LAN network interface
- » Configurable keep alive update rate
- » Specify customer DNS server/IP address
- » Specify WLAN/LTE fallback

Accessories

If the router is ordered with accessories, you will receive the following:

- » Power supply with multi-region adapters
- » Power interface cable
- » LAN cable
- » Cellular antennas
- » WiFi antennas
- » GPS/GNSS antenna
(only with GPS/GNSS router option)

Models Available

- » Dual WiFi Industrial LTE Gigabit Ethernet Router
QUARTZ-GOLD-W21-LTE (EU) + Accessories - Stock code 61132
QUARTZ-GOLD-W21-LTE (EU) - Stock code 61133
- » Dual WiFi & GNSS Industrial LTE Gigabit Ethernet Router
QUARTZ-GOLD-GW21-LTE (EU) + Accessories - Stock Code 61134
QUARTZ-GOLD-GW21-LTE (EU) - Stock code 61162