

Surge Arrester EC230X

Ordering code: B88069X0660S102

## 2-Electrode-Arrester

DC spark-over voltage 1) 2) 230 V % ± 15 Impulse spark-over voltage - for 99 % of measured values at 100 V/µs < 550 ٧ - typical values of distribution < 500 ٧ at 1 kV/µs - for 99 % of measured values < 700 - typical values of distribution < 600 Nominal impulse discharge current (wave 8/20 µs) 5 kΑ Single impulse discharge current 10 kΑ (wave 8/20 µs) Single impulse discharge current (wave  $10/350 \mu s$ ) 2.5 kΑ 5 Α Nominal alternating discharge current (50 Hz, 1 s) Alternating discharge current (50 Hz, 9 cycles) 20 Α Insulation resistance at 100 V<sub>dc</sub> > 10  $\mathsf{G}\Omega$ pF Capacitance at 1 MHz < 1 V Arc voltage at 1 A ~ 12 Glow to arc transition current ~ 0.6 Α Glow voltage ~ 80 V Weight ~ 1.5 g Operation and storage temperature -40 ... +90 °C 40/90/21 Climatic category (IEC 60068-1) **EPCOS**EC 230 YY O Marking, red - Series EC 230 - Nominal voltage YY - Year of production - Non radioactive 0

Terms in accordance with ITU-T Rec. K.12 and DIN 57845/VDE0845

AB E / AB PM Issue 05, 18.04.2002

<sup>1)</sup> At delivery AQL 0.65 level II, DIN ISO 2859


<sup>2)</sup> In ionized mode



Surge Arrester EC230X

## 2-Electrode-Arrester

Ordering code: B88069X0660S102



Not to scale

Dimensions in mm

Non controlled document

AB E / AB PM Issue 05, 18.04.2002

 $<sup>\</sup>odot$  EPCOS AG 2002. Reproduction, publication and dissemination of this data sheet, enclosures hereto and the information contained therein without EPCOS' prior express consent is prohibited.

Purchase orders are subject to the General Conditions for the Supply of Products and Services of the Electrical and Electronics Industry recommended by the ZVEI (German Electrical and Electronic Manufacturers' Association), unless otherwise agreed.