

Handheld Digital Multimeter



Features

- Auto Ranging and Auto Power-OFF
- Low battery indication
- Data Hold
- MAX Value hold function, Diode check, Continuity

Specifications

Display	: 3-1/2 Digit LCD display with 2000 display counts
Battery	: 9V Battery (6F22 or 1604A Type)
Operating temperature and Humidity	: 0 to +40°C (+32°F to +104°F) and <80% RH
Storage temperature and Humidity	: -10°C to +50°C (+14°F to +122°F) and <70%RH
Safety Class	: IEC 61010-1, CAT III 600V
Dimension	: 140mm (L) × 67mm (W) × 30mm (H)
Accessory	: K-type Temperature Probe [P3400], 9V Battery, Test lead set and User Manual.

Electrical Specification

DC Voltage		
Range	Resolution	Accuracy
200mV	0.1mV	±(0.5% rdg + 2dgt)
2V	0.001V	
20V	0.01V	
200V	0.1V	
600V	1V	±(0.8% rdg + 2dgt)

Over load protection: Spark Gap used to protect that the voltage over 1500V

AC Voltage		
Range	Resolution	Accuracy
2V (40Hz-400Hz)	0.001V	±(0.9% rdg + 3dgt)
20V (40Hz-400Hz)	0.01V	
200V (40Hz-400Hz)	0.1V	
600V (40Hz-200Hz)	1V	±(1.2%) rdg + 3dgt

Over load protection: Spark Gap used to protect High voltage that is over 1500V

Newark.com/exclusive-brands
Farnell.com/exclusive-brands
Element14.com/exclusive-brands



Handheld Digital Multimeter



Resistance		
Resistance Range	Resolution	Accuracy
200Ω	0.1Ω	±(0.8% rdg + 2dgt)
2kΩ	0.001kΩ	
20kΩ	0.01kΩ	
200kΩ	0.1kΩ	
2MΩ	0.001MΩ	±(1.0% rdg + 2dgt)

DC and AC Current rating [40Hz-400Hz]		
DC Current Range	Resolution	Accuracy
200μA	0.1μA	±(1.5% rdg + 3dgt)
2000μA	1μA	
20mA	0.01mA	
200mA	0.1mA	
10A	0.01A	

Over Load protection : Use the fuse (F250mA/250V) at μA /mA range, and use the fuse (F10A/250V) at 10A range.
Max input DC Current : 250mA at 'mA' input terminal and 10A at '10A' input terminal

Frequency (Sensitivity: 0.8V)		
Range	Resolution	Accuracy
20kHz	10kHz	±(1.5% rdg +5dgt)

Part Number Table

Description	Part Number
Digital Multimeter, Handheld, Auto Range	D03124

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. DURATOOL is the registered trademark of Premier Farnell Limited 2019.

Newark.com/exclusive-brands
Farnell.com/exclusive-brands
Element14.com/exclusive-brands

