

Printing date 02.10.2020 Version number 2 Revision: 02.10.2020

## SECTION 1: Identification of the substance/mixture and of the company/undertaking

- · 1.1 Product identifier
- · Trade name: Universal Cleaner RM 626
- 1.2 Relevant identified uses of the substance or mixture and uses advised against No further relevant information available.
- · Application of the substance / the mixture High pressure cleaner
- · 1.3 Details of the supplier of the safety data sheet
- · Manufacturer/Supplier:

### Alfred Kärcher SE & Co. KG

Alfred-Kärcher-Str. 28-40 D - 71364 Winnenden Tel.: +49-7195-14-0

### Kärcher (UK) Ltd.

Kärcher House Brookhill Way Banbury Oxon OX16 3ED Great Britain Tel.: +44-1295-752-000

101.. 144 1233 732 000

Internet: www.karcher.com

· Further information obtainable from:

Department TCD-D Tel.: +49-7195-14-2548 Fax: +49-7195-14-3164

productsafety.management@de.kaercher.com

· 1.4 Emergency telephone number:

For Hazardous Materials [or Dangerous Goods] Incidents Spill, Leak, Fire, Exposure, or Accident Call CHEMTREC Day or Night

Within USA and Canada: 1-800-424-9300

Outside USA and Canada: +1 703-741-5970 (collect calls accepted)

### **SECTION 2: Hazards identification**

- · 2.1 Classification of the substance or mixture
- Classification according to Regulation (EC) No 1272/2008

The product is not classified, according to the CLP regulation.

- · 2.2 Label elements
- · Labelling according to Regulation (EC) No 1272/2008 Void
- · Hazard pictograms Void
- · Signal word Void
- · Hazard statements Void

(Contd. on page 2)



Printing date 02.10.2020 Version number 2 Revision: 02.10.2020

Trade name: Universal Cleaner RM 626

(Contd. of page 1)

· Precautionary statements

P102 Keep out of reach of children.

· 2.3 Other hazards

The product does not contain any organic halogen compounds (AOX), nitrates, heavy metal compounds.

- Results of PBT and vPvB assessment
- · PBT: Not applicable.
- · **vPvB:** Not applicable.

### **SECTION 3: Composition/information on ingredients**

- · 3.2 Chemical characterisation: Mixtures
- · Description: Cleaning agent

· Dangerous components:			
CAS: 68515-73-1 NLP: 500-220-1 Reg.nr.: 01-2119488530-36	alkyl polyglucoside	♦ Eye Dam. 1, H318	1-5%

## · Regulation (EC) No 648/2004 on detergents / Labelling for contents

ggg		
non-ionic surfactants, amphoteric surfactants, preservation agents (PHENOXYETHANOL, BENZISOTHIAZOLINONE (< 0,005%))	<5%	
perfumes		

· Additional information

Specific concentration limits available for Alkylpolygycoside based on test reports (see Section 11). For the wording of the listed hazard phrases refer to section 16.

## **SECTION 4: First aid measures**

- · 4.1 Description of first aid measures
- · General information No special measures required.
- · After inhalation Supply fresh air; consult doctor in case of complaints.
- · After skin contact Rinse with warm water.
- · After eye contact Rinse opened eye for several minutes under running water.
- · After swallowing

Rinse out mouth and then drink plenty of water.

If symptoms persist consult doctor.

 $\cdot$  4.2 Most important symptoms and effects, both acute and delayed

No further relevant information available.

· 4.3 Indication of any immediate medical attention and special treatment needed

No further relevant information available.

- CE



Printing date 02.10.2020 Version number 2 Revision: 02.10.2020

Trade name: Universal Cleaner RM 626

(Contd. of page 2)

## **SECTION 5: Firefighting measures**

- · 5.1 Extinguishing media
- · Suitable extinguishing agents Use fire extinguishing methods suitable to surrounding conditions.
- · For safety reasons unsuitable extinguishing agents Water with full jet.
- · 5.2 Special hazards arising from the substance or mixture No further relevant information available.
- · 5.3 Advice for firefighters
- · Protective equipment: No special measures required.

### **SECTION 6: Accidental release measures**

- · 6.1 Personal precautions, protective equipment and emergency procedures Not required.
- · 6.2 Environmental precautions:

Do not allow product to reach sewage system or any water course.

Inform respective authorities in case of seepage into water course or sewage system.

Dilute with plenty of water.

Do not allow to enter sewers/ surface or ground water.

Do not allow to penetrate the ground/soil.

#### · 6.3 Methods and material for containment and cleaning up:

Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders).

#### · 6.4 Reference to other sections

No dangerous substances are released.

See Section 7 for information on safe handling

See Section 8 for information on personal protection equipment.

See Section 13 for disposal information.

# **SECTION 7: Handling and storage**

- · 7.1 Precautions for safe handling No special measures required.
- · Information about fire and explosion protection: No special measures required.
- · 7.2 Conditions for safe storage, including any incompatibilities
- · Storage
- · Requirements to be met by storerooms and receptacles: No special requirements.
- · Information about storage in one common storage facility: Not required.
- · Further information about storage conditions: None.
- · 7.3 Specific end use(s) No further relevant information available.

GE



Printing date 02.10.2020 Version number 2 Revision: 02.10.2020

Trade name: Universal Cleaner RM 626

(Contd. of page 3)

## **SECTION 8: Exposure controls/personal protection**

- · Additional information about design of technical facilities: No further data; see item 7.
- · 8.1 Control parameters
- · Ingredients with limit values that require monitoring at the workplace:

The product does not contain any relevant quantities of materials with critical values that have to be monitored at the workplace.

- · 8.2 Exposure controls
- · Personal protective equipment
- General protective and hygienic measures

The usual precautionary measures are to be adhered to when handling chemicals.

- · Respiratory protection: Not necessary if room is well-ventilated.
- · Protection of hands: Not required.
- · Material of gloves

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.

Penetration time of glove material

The exact break trough time has to be found out by the manufacturer of the protective gloves and has to be

· Eye protection: Goggles recommended during refilling.

## **SECTION 9: Physical and chemical properties**

- · 9.1 Information on basic physical and chemical properties
- General Information

· Appearance:

Form:

Fluid

Colour:

Yellow

· Odour:

citrus-like

· Odour threshold:

Not determined.

· pH-value at 20 °C:

7.1

· pH-value 1 %:

7.2

· Change in condition

Melting point/freezing point:

0°C

Initial boiling point and boiling range: 100 °C

· Flash point:

Not applicable

· Flammability (solid, gaseous)

Not applicable.

· Ignition temperature:

not applicable

· Decomposition temperature:

Not determined.

(Contd. on page 5)



Printing date 02.10.2020 Version number 2 Revision: 02.10.2020

Trade name: Universal Cleaner RM 626

	(Contd. of pa	
· Auto-ignition temperature:	Product is not selfigniting.	
· Explosive properties:	Product does not present an explosion hazard.	
· Explosion limits:		
Lower:	Not determined.	
Upper:	Not determined.	
· Vapour pressure:	Not determined.	
Density at 20 °C:	1.007 g/cm <sup>3</sup>	
Relative density	Not determined.	
Vapour density	Not determined.	
Evaporation rate	Not determined.	
Solubility in / Miscibility with		
Water:	Fully miscible	
Partition coefficient: n-octanol	/water: Not determined.	
Viscosity:		
dynamic at 20 °C:	663 mPas	
kinematic:	Not determined.	
Solvent content:		
Organic solvents:	0.3 %	
VOC (EC)	0.29 %	
Solids content:	2.9 %	
9.2 Other information	No further relevant information available.	

# **SECTION 10: Stability and reactivity**

- · 10.1 Reactivity corresponds to 10.3
- · 10.2 Chemical stability
- $\cdot$  Thermal decomposition / conditions to be avoided:

No decomposition if used according to specifications.

- · 10.3 Possibility of hazardous reactions No dangerous reactions known
- · 10.4 Conditions to avoid No further relevant information available.
- 10.5 Incompatible materials: No further relevant information available.
- · 10.6 Hazardous decomposition products: No dangerous decomposition products known

GB ·



Printing date 02.10.2020 Version number 2 Revision: 02.10.2020

Trade name: Universal Cleaner RM 626

(Contd. of page 5)

## **SECTION 11: Toxicological information**

- · 11.1 Information on toxicological effects
- · Acute toxicity Based on available data, the classification criteria are not met.
- · Primary irritant effect:
- · Skin corrosion/irritation Based on available data, the classification criteria are not met.
- · Serious eye damage/irritation
- 68515-73-1 Alkylpolyglycoside: Specific concentration limit for H318: 10% (BCOP test, OECD 437)
- · Respiratory or skin sensitisation Based on available data, the classification criteria are not met.
- · CMR effects (carcinogenity, mutagenicity and toxicity for reproduction)
- · Germ cell mutagenicity Based on available data, the classification criteria are not met.
- · Carcinogenicity Based on available data, the classification criteria are not met.
- $\cdot \ \textbf{Reproductive toxicity} \ \text{Based on available data, the classification criteria are not met.}$
- $\cdot$  STOT-single exposure Based on available data, the classification criteria are not met.
- · STOT-repeated exposure Based on available data, the classification criteria are not met.
- · Aspiration hazard Based on available data, the classification criteria are not met.

## **SECTION 12: Ecological information**

- · 12.1 Toxicity
- · Aquatic toxicity:

### 68515-73-1 alkyl polyglucoside

LC50/96 h | 126 mg/l (fish)

EC50/48 h >100 mg/l (Daphnia magna)

- · 12.2 Persistence and degradability No further relevant information available.
- · 12.3 Bioaccumulative potential No further relevant information available.
- · 12.4 Mobility in soil No further relevant information available.
- · Additional ecological information:
- · COD-value: 69 mg O2/g
- · General notes:

The surfactant(s) contained in this preparation complies(comply) with the biodegradability criteria as laid down in Regulation (EC) No.648/2004 on detergents. Data to support this assertion are held at the disposal of the competent authorities of the Member States and will be made available to them, at their direct request or at the request of a detergent manufacturer.

The product does not contain organically bounded halogens (AOX-free).

The product does not contain organic complexing agents.

Do not allow undiluted product or large quantities of it to reach ground water, water course or sewage system.

- · 12.5 Results of PBT and vPvB assessment
- · PBT: Not applicable.

(Contd. on page 7)



Printing date 02.10.2020 Version number 2 Revision: 02.10.2020

Trade name: Universal Cleaner RM 626

(Contd. of page 6)

· vPvB: Not applicable.

· 12.6 Other adverse effects No further relevant information available.

# **SECTION 13: Disposal considerations**

- · 13.1 Waste treatment methods
- · Recommendation

Hand over to hazardous waste disposers.

Small amounts may be diluted with plenty of water and washed away. Dispose of bigger amounts in accordance with Local Authority requirements.

· European waste catalogue

20 01 30 detergents other than those mentioned in 20 01 29

- · Uncleaned packaging:
- Recommendation:

Empty contaminated packagings thoroughly. They may be recycled after thorough and proper cleaning. Non contaminated packagings may be recycled.

· Recommended cleansing agents: Water, if necessary together with cleaning agents.

14.1 UN-Number	
ADR, ADN, IMDG, IATA	Void
14.2 UN proper shipping name	
ADR, ADN, IMDG, IATA	Void
14.3 Transport hazard class(es)	
ADR, ADN, IMDG, IATA	
Class	Void
14.4 Packing group	
ADR, IMDG, IATA	Void
14.5 Environmental hazards:	
Marine pollutant:	No
14.6 Special precautions for user	Not applicable.
14.7 Transport in bulk according to Ann	ex II of
Marpol and the IBC Code	Not applicable.
Transport/Additional information:	Not dangerous according to the above specifications

on page



Printing date 02.10.2020 Version number 2 Revision: 02.10.2020

Trade name: Universal Cleaner RM 626

(Contd. of page 7)

· UN "Model Regulation":

Void

# **SECTION 15: Regulatory information**

- · 15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture
- · Directive 2012/18/EU
- · Named dangerous substances ANNEX I None of the ingredients is listed.
- DIRECTIVE 2011/65/EU on the restriction of the use of certain hazardous substances in electrical and electronic equipment Annex II

None of the ingredients is listed.

· 15.2 Chemical safety assessment: A Chemical Safety Assessment has not been carried out.

### **SECTION 16: Other information**

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship. A product information sheet can be provided if requested.

· Relevant phrases

H318 Causes serious eye damage.

Department issuing SDS: TCD-D

· Contact:

Department TCD-D Tel.: +49-7195-14-2548 Fax: +49-7195-14-3164

productsafety.management@de.kaercher.com

Abbreviations and acronyms:

RID: Règlement international concernant le transport des marchandises dangereuses par chemin de fer (Regulations Concerning the International Transport of Dangerous Goods by Rail)

ICAO: International Civil Aviation Organisation

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)

IMDG: International Maritime Code for Dangerous Goods

IATA: International Air Transport Association

GHS: Globally Harmonised System of Classification and Labelling of Chemicals

EINECS: European Inventory of Existing Commercial Chemical Substances

ELINCS: European List of Notified Chemical Substances

CAS: Chemical Abstracts Service (division of the American Chemical Society)

VOC: Volatile Organic Compounds (USA, EU) PBT: Persistent, Bioaccumulative and Toxic

vPvB: very Persistent and very Bioaccumulative

Eye Dam. 1: Serious eye damage/eye irritation – Category 1

· \* Data compared to the previous version altered.

0.011-288-0

RM 626/5

2.373