

EAGLE5C-AD-TUR-FG

5MP HDCVI FULL-COLOUR ACTIVE DETERRANCE TURRET



Full-color

- 24/7 colour imaging
- Active deterrence with red blue light, siren and alarm out interface
- Built-in mic
- Max. 20 fps@5MP
- 2.8 mm fixed lens
- 40 m illumination distance
- IP67, 12V±30% DC



System Overview

This model supports active deterrence which warns off intruders with a red to blue light and siren even before users are aware of the incident. It is able to alert intruders accurately by SMD Plus or Perimeter Protection of XVRs. This camera is an ideal choice for applications which require intrusion protection and video verification, such as courtyards, offices, warehouses, stores.

Functions

4 Signals over 1 Coaxial Cable

HDCVI technology supports 4 signals to be transmitted over 1 coaxial cable simultaneously, such as video, audio*, data and power. Dual-way data transmission allows the HDCVI camera to interact with the HCVR, such as sending control signal or triggering alarm. Moreover, HDCVI technology supports PoC for construction flexibility.

* Audio input is available for some models of HDCVI cameras.

Long Distance Transmission

HDCVI technology guarantees real-time transmission at long distance without any loss. It supports up to 700m transmission for 5MP HD video over a coaxial cable, and up to 300m over UTP cable.

Simplicity

HDCVI technology inherits the feature of simplicity from traditional analog surveillance systems, making itself the best choice for investment protection. HDCVI systems can seamlessly upgrade the traditional analog system without replacing existing coaxial cabling. The plug and play approach enables full HD video surveillance without the hassle of configuring a network.

Active Deterrence

Active deterrence is to warn off intruders actively with red to blue light and siren even before users are aware of the incidence. Once an intrusion is detected, the red blue light will flash and the siren will buzzer to alert the intruder. The content of siren is configurable.

Full-colour

The camera adopts F1.2 large aperture lens and 1/2.7" high performance sensor. With a high amount of absorbed light and advanced image processing algorithms, the camera can be able to present 24/7 colored imaged that provide colour details to accurately identify people or objects in low light conditions.

Warm Supplemental lights

With two warm supplemental LED lights, the camera is able to provide a colorful and vivid image even in total darkness. It also provides visibility by default, the camera is set to smart light mode, in which the camera can automatically adjust the exposure time and light sensitivity simultaneously to avoid overexposure of objects in the image center. Also, the sensitivity and intensity of the LED lights can be remotely controlled by the OSD menu.

Protection

The camera's outstanding reliability is unsurpassed due to its rugged design. The camera is protected against water and dust with an IP67 rating, making it suitable for indoor or outdoor environments. Supporting ±30% input voltage tolerance, this camera suits even the most unstable power supply conditions. Its 4KV lightning rating provides protection against the camera and its structure from the effects of lightning.

Technical Specification					
Camera					
Image Sensor	1/2.7" CMOS				
Max. Resolution	2592 (H) × 1944 (V)				
Pixel	5MP				
Scanning System	Progressive				
Electronic Shutter Speed	PAL: 1/25 s–1/100000 s NTSC: 1/30 s–1/100000 s				
S/N Ratio	>65 dB				
Min. Illumination	0.005 Lux/F1.2, 0 Lux warm light on				
Illumination Distance	40 m (131.2 ft)				
Illumination Type	Warm light				
Illuminator On/Off Control	Auto; manual				
Illuminator Number	2 (Warm light)				
Pan/Tilt/Rotation Range	Pan: 0°–360° Tilt: 0°–78° Rotation: 0°–360°				
Lens					
Lens Type	Fixed-focal				
Mount Type	M12				
Focal Length	2.8 mm				
Max. Aperture	2.8 mm: F1.2				
Field of View	2.8 mm: H: 98°; V: 71°; D: 129°				
Iris Type	Fixed iris				
Close Focus Distance	2.8 mm: 1.6 m (5.25 ft)				
DORI Distance	Lens	Detect	Observe	Recognize	Identify
	2.8 mm	67.4 m (221.1 ft)	27 m (88.6 ft)	13.5 m (44.3 ft)	6.7 m (22.0 ft)
	3.6 mm	77.8 m (255.3 ft)	31.1 m (102.0 ft)	15.6 m (51.2 ft)	7.8 m (25.6 ft)
Video					
Frame Rate	CVI: 5M@20 fps, 4M@25 fps/30 fps, 1080p@25 fps/30 fps; AHD: 5M@20 fps; TVI: 5M@20 fps; CVBS: 960H				
Resolution	5M (2592 × 1944); 4M (2560 × 1440); 1080p (1920 × 1080); 960H (960 × 576/960 × 480)				
BLC Mode	BLC/HLC/DWDR				
WDR	DWDR				
White Balance	Auto/Manual				
Gain Control	Auto/Manual				
Noise Reduction	2D				
Smart Light	Yes				
Mirror	Off/On				
Privacy Masking	Off/On (8 Area, Rectangle)				
Certifications					
Certifications	CE (EN55032:2015, EN61000-3-2:2014, EN61000-3-3:2013, EN55024:2010+A1:2015, EN 55035:2017, EN50130-4:2011+A1:2014) FCC (CFR 47 FCC Part 15 subpartB, ANSI C63.4-2014) IEC 62368-1:2014 (Second Edition)				
Port					
Video Output	1 BNC output Support CVI/TVI/AHD/CVBS				
Audio Input	Built-in mic				
Alarm out	1ch alarm out				
Active Deterrence					
Red/Blue Light Warning	Flash: 5 s–30 s; frequency: high/medium/low				
Sound Warning	Audio 1/2/3; Volume: high/medium/low; duration: 5 s–30 s; 110 dB				
Power					
Power Supply	12V ±30% DC				
Power Consumption	Max 7.7W (12V DC, warm light on)				
Environment					
Operating Temperature	–40°C to +60°C (–40°F to 140°F); <95% (non-condensation)				
Storage Temperature	–40°C to +60°C (–40°F to 140°F); <95% (non-condensation)				
Ingress Protection	IP67				
Structure					
Casing	Metal				
Camera Dimensions	Φ122.0 mm × 110.9 mm (Φ4.8" × 4.37")				
Net Weight	0.69 kg (1.52 lb)				
Gross Weight	0.95 kg (2.01 lb)				

Dimensions (mm[inch])

