



## Safety Data Sheet according to Regulation (EC) No 1907/2006

Page 1 of 8

LOCTITE SUPERLUBE known as SUPERLUBE GREASE  
12X400GM

SDS No. : 168446  
V003.0  
Revision: 30.04.2018  
printing date: 20.12.2020  
Replaces version from: 08.07.2014

### SECTION 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1. Product identifier

LOCTITE SUPERLUBE known as SUPERLUBE GREASE 12X400GM

#### 1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use:  
Lubricant

#### 1.3. Details of the supplier of the safety data sheet

Henkel Ltd  
Adhesives  
Wood Lane End  
HP2 4RQ Hemel Hempstead

Great Britain

Phone: +44 (1442) 278000  
Fax-no.: +44 (1442) 278071

ua-productsafety.uk@henkel.com

#### 1.4. Emergency telephone number

24 Hours Emergency Tel: +44 (0)1442 278497

### SECTION 2: Hazards identification

#### 2.1. Classification of the substance or mixture

##### Classification (CLP):

The substance or mixture is not hazardous according to Regulation (EC) No 1272/2008 (CLP).

#### 2.2. Label elements

##### Label elements (CLP):

The substance or mixture is not hazardous according to Regulation (EC) No 1272/2008 (CLP).

#### 2.3. Other hazards

None if used properly.

Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.

### SECTION 3: Composition/information on ingredients

#### 3.2. Mixtures

##### General chemical description:

Lubricant

**Declaration of the ingredients according to CLP (EC) No 1272/2008:**

|| Contains no dangerous substances exceeding the limits of the EU-Regulation

**SECTION 4: First aid measures****4.1. Description of first aid measures****Inhalation:**

Move to fresh air. If symptoms persist, seek medical advice.

**Skin contact:**

Rinse with running water and soap.  
Seek medical advice.

**Eye contact:**

Rinse immediately with plenty of running water (for 10 minutes). Seek medical attention if necessary.

**Ingestion:**

Rinse out mouth, drink 1-2 glasses of water, do not induce vomiting.  
Seek medical advice.

**4.2. Most important symptoms and effects, both acute and delayed**

Prolonged or repeated contact may cause skin irritation.

Prolonged or repeated contact may cause eye irritation.

**4.3. Indication of any immediate medical attention and special treatment needed**

See section: Description of first aid measures

**SECTION 5: Firefighting measures****5.1. Extinguishing media****Suitable extinguishing media:**

Carbon dioxide, foam, powder

**5.2. Special hazards arising from the substance or mixture**

In the event of a fire, carbon monoxide (CO), carbon dioxide (CO<sub>2</sub>) and nitrogen oxides (NO<sub>x</sub>) can be released.  
carbon oxides.

**5.3. Advice for firefighters**

Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear.

**Additional information:**

In case of fire, keep containers cool with water spray.

**SECTION 6: Accidental release measures****6.1. Personal precautions, protective equipment and emergency procedures**

Avoid skin and eye contact.  
Ensure adequate ventilation.

**6.2. Environmental precautions**

Do not let product enter drains.

**6.3. Methods and material for containment and cleaning up**

For small spills wipe up with paper towel and place in container for disposal.  
For large spills absorb onto inert absorbent material and place in sealed container for disposal.  
Dispose of contaminated material as waste according to Section 13.

**6.4. Reference to other sections**

See advice in section 8

## SECTION 7: Handling and storage

### 7.1. Precautions for safe handling

Use only in well-ventilated areas.  
 Vapours should be extracted to avoid inhalation.  
 Avoid skin and eye contact.  
 See advice in section 8

#### Hygiene measures:

Wash hands before work breaks and after finishing work.  
 Do not eat, drink or smoke while working.  
 Good industrial hygiene practices should be observed.

### 7.2. Conditions for safe storage, including any incompatibilities

Store in a cool, well-ventilated place.  
 Keep away from heat and direct sunlight.  
 Refer to Technical Data Sheet

### 7.3. Specific end use(s)

Lubricant

## SECTION 8: Exposure controls/personal protection

### 8.1. Control parameters

#### Occupational Exposure Limits

Valid for  
 Great Britain

Ingredient [Regulated substance]	ppm	mg/m <sup>3</sup>	Value type	Short term exposure limit category / Remarks	Regulatory list
Silane, dichlorodimethyl-, reaction products with silica 68611-44-9 [SILICA, AMORPHOUS, RESPIRABLE DUST]		2,4	Time Weighted Average (TWA):		EH40 WEL
Silane, dichlorodimethyl-, reaction products with silica 68611-44-9 [SILICA, AMORPHOUS, INHALABLE DUST]		6	Time Weighted Average (TWA):		EH40 WEL

#### Occupational Exposure Limits

Valid for  
 Ireland

Ingredient [Regulated substance]	ppm	mg/m <sup>3</sup>	Value type	Short term exposure limit category / Remarks	Regulatory list
White mineral oil (petroleum) 8042-47-5 [MINERAL OIL, PURE, HIGHLY & SEVERELY REFINED, INHALABLE FRACTION]		5	Time Weighted Average (TWA):		IR_OEL
Silane, dichlorodimethyl-, reaction products with silica 68611-44-9 [SILICA, AMORPHOUS, TOTAL INHALABLE DUST]		6	Time Weighted Average (TWA):		IR_OEL
Silane, dichlorodimethyl-, reaction products with silica 68611-44-9 [SILICA, AMORPHOUS, RESPIRABLE DUST]		2,4	Time Weighted Average (TWA):		IR_OEL

**Biological Exposure Indices:**

None

**8.2. Exposure controls:**

Engineering controls:  
Ensure good ventilation/extraction.

Respiratory protection:  
Ensure adequate ventilation.  
An approved mask or respirator fitted with an organic vapour cartridge should be worn if the product is used in a poorly ventilated area  
Filter type: A (EN 14387)

Hand protection:  
Chemical-resistant protective gloves (EN 374).  
Suitable materials for short-term contact or splashes (recommended: at least protection index 2, corresponding to > 30 minutes permeation time as per EN 374):  
nitrile rubber (NBR;  $\geq 0.4$  mm thickness)  
Suitable materials for longer, direct contact (recommended: protection index 6, corresponding to > 480 minutes permeation time as per EN 374):  
nitrile rubber (NBR;  $\geq 0.4$  mm thickness)  
This information is based on literature references and on information provided by glove manufacturers, or is derived by analogy with similar substances. Please note that in practice the working life of chemical-resistant protective gloves may be considerably shorter than the permeation time determined in accordance with EN 374 as a result of the many influencing factors (e.g. temperature). If signs of wear and tear are noticed then the gloves should be replaced.

Eye protection:  
Safety glasses with sideshields or chemical safety goggles should be worn if there is a risk of splashing.  
Protective eye equipment should conform to EN166.

Skin protection:  
Wear suitable protective clothing.  
Protective clothing should conform to EN 14605 for liquid splashes or to EN 13982 for dusts.

Advices to personal protection equipment:

The information provided on personal protective equipment is for guidance purposes only. A full risk assessment should be conducted prior to using this product to determine the appropriate personal protective equipment to suit local conditions. Personal protective equipment should conform to the relevant EN standard.

**SECTION 9: Physical and chemical properties****9.1. Information on basic physical and chemical properties**

Appearance	paste white
Odor	None
Odour threshold	No data available / Not applicable
pH	No data available / Not applicable
Melting point	No data available / Not applicable
Solidification temperature	No data available / Not applicable
Initial boiling point	No data available / Not applicable
Flash point	> 200 °C (> 392 °F)
Evaporation rate	No data available / Not applicable
Flammability	No data available / Not applicable
Explosive limits	No data available / Not applicable
Vapour pressure	No data available / Not applicable
Relative vapour density:	No data available / Not applicable
Density ( $\rho$ )	0,89 g/cm <sup>3</sup>
Bulk density	No data available / Not applicable

Solubility	No data available / Not applicable
Solubility (qualitative) (Solvent: Water)	Insoluble
Partition coefficient: n-octanol/water	No data available / Not applicable
Auto-ignition temperature	No data available / Not applicable
Decomposition temperature	No data available / Not applicable
Viscosity	No data available / Not applicable
Viscosity (kinematic)	No data available / Not applicable
Explosive properties	No data available / Not applicable
Oxidising properties	No data available / Not applicable

## 9.2. Other information

No data available / Not applicable

## SECTION 10: Stability and reactivity

### 10.1. Reactivity

Reacts with strong oxidants.

### 10.2. Chemical stability

Stable under recommended storage conditions.

### 10.3. Possibility of hazardous reactions

See section reactivity

### 10.4. Conditions to avoid

Stable

### 10.5. Incompatible materials

See section reactivity.

### 10.6. Hazardous decomposition products

Irritating organic vapours.

## SECTION 11: Toxicological information

### General toxicological information:

Prolonged or repeated contact may cause skin irritation.

Prolonged or repeated contact may cause eye irritation.

### 11.1. Information on toxicological effects

#### Acute oral toxicity:

No data available.

#### Acute dermal toxicity:

No data available.

#### Acute inhalative toxicity:

No data available.

#### Skin corrosion/irritation:

No data available.

**Serious eye damage/irritation:**

No data available.

**Respiratory or skin sensitization:**

No data available.

**Germ cell mutagenicity:**

No data available.

**Carcinogenicity**

No data available.

**Reproductive toxicity:**

No data available.

**STOT-single exposure:**

No data available.

**STOT-repeated exposure::**

No data available.

**Aspiration hazard:**

No data available.

**SECTION 12: Ecological information****General ecological information:**

Do not empty into drains / surface water / ground water.

**12.1. Toxicity****Toxicity (Fish):**

No data available.

**Toxicity (Daphnia):**

No data available.

**Chronic toxicity to aquatic invertebrates**

No data available.

**Toxicity (Algae):**

No data available.

#### **Toxicity to microorganisms**

No data available.

#### **12.2. Persistence and degradability**

The product is not biodegradable.

No substance data available.

#### **12.3. Bioaccumulative potential**

No data available.

No substance data available.

#### **12.4. Mobility in soil**

Cured adhesives are immobile.

No substance data available.

#### **12.5. Results of PBT and vPvB assessment**

This mixture does not contain any substances that are assessed to be a PBT or vPvB.

#### **12.6. Other adverse effects**

No data available.

### **SECTION 13: Disposal considerations**

#### **13.1. Waste treatment methods**

Product disposal:

Dispose of in accordance with local and national regulations.

Disposal of uncleaned packages:

Disposal must be made according to official regulations.

Waste code

08 04 09 waste adhesives and sealants containing organic solvents and other dangerous substances

The valid EWC waste code numbers are source-related. The manufacturer is therefore unable to specify EWC waste codes for the articles or products used in the various sectors. The EWC codes listed are intended as a recommendation for users. We will be happy to advise you.

**SECTION 14: Transport information**

- 14.1. UN number**  
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.2. UN proper shipping name**  
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.3. Transport hazard class(es)**  
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.4. Packing group**  
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.5. Environmental hazards**  
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.6. Special precautions for user**  
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.7. Transport in bulk according to Annex II of Marpol and the IBC Code**  
not applicable

**SECTION 15: Regulatory information****15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture**

VOC content 0 %  
(2010/75/EC)

**15.2. Chemical safety assessment**

A chemical safety assessment has not been carried out.

**SECTION 16: Other information****Further information:**

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.

**Relevant changes in this safety data sheet are indicated by vertical lines at the left margin in the body of this document. Corresponding text is displayed in a different color on shadowed fields.**