
PRO-POWER

TECHNICAL DATA SHEET

RoHS Compliant

2-CORE SPEAKER CABLES MODELS: PP3045-PP3055



Features:

High performance, 2-core speaker cable Suitable for use with PA systems or general A/V applications Stranded, copper conductors (2x 1.50mm² or 2x 2.50mm²)

Black or white, LSHF jacket Reel length: 50m or 100m

Specifications:

| Conductor | Material | Bare cop | Bare copper (OFC) | |
|-----------------------|----------------|--|------------------------|--|
| | Construction | 30x 0.254mm or 50x 0.254m | | |
| | Cross Section | 2x 1.50mm ² or 2x 2.50mm ² | | |
| Insulation | Material | Low Smoke Halogen-Free | | |
| | | (LSHF) | | |
| | Thickness | 0.38mm | | |
| | Diameter | 2x 2.40mm d | 2x 2.40mm or 2x 2.90mm | |
| | Colours | Blue | Red | |
| Ripcord | Material | Nylon | | |
| | Material | Low Smoke Halogen-Free | | |
| Outer Jacket | | (LSHF) | | |
| | Thickness | 0.60mm | | |
| | Diameter | 6.00mm or 7.00mm | | |
| | Colours | Black | White | |
| Operating Temperature | -15°C to +60°C | | | |

Important Notice: This data sheet and its contents (the "Information") belong to pro-POWER. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but pro-POWER assumes no responsibility for its accuracy or completeness, any error in or ormission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or ornitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where pro-POWER was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict pro-POWER's liability for death or personal injury resulting from its negligence.



V1.0

PRO-POWER

TECHNICAL DATA SHEET

RoHS Compliant

Electrical Characteristics:

Conductor resistance: 7.30Ω/km

Product Codes:

| Cross Section | Length | Jacket Colour | Code |
|---------------|--------|---------------|--------|
| 1.50mm² | 50m | White | PP3045 |
| | 100m | | PP3046 |
| 2.50mm² | 50m | vvnite | PP3047 |
| | 100m | | PP3048 |
| 1.50mm² | 50m | Black | PP3052 |
| | 100m | | PP3053 |
| 2.50mm² | 50m | Black | PP3054 |
| | 100m | | PP3055 |

Important Notice: This data sheet and its contents (the "Information") belong to pro-POWER. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but pro-POWER assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where pro-POWER was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict pro-POWER's liability for death or personal injury resulting from its negligence.

