





PRODUCT DATA SHEET

EVERBUILD CLEAR FIX®

PERFECTLY CLEAR, HYBRID POLYMER GRAB ADHESIVE

PRODUCT DESCRIPTION

EVERBUILD CLEAR FIX® is a clear hybrid polymer grab adhesive that has the ability to bond just about everything for both interior and exterior applications. With added UV stabilisers to ensure the product doesn't yellow over time, EVERBUILD CLEAR FIX® is the ideal choice for applications where transparency is required and where a coloured product might otherwise remain visible. It is a versatile product which can be used in almost every application imaginable — even when immersed under water. EVERBUILD CLEAR FIX® is quick-curing, resistant to temperature extremes, overpaintable and totally water and weatherproof.

USES

Bonding in almost every application imaginable. The following are just some examples:

- As a high quality nail replacement adhesive, even to damp surfaces.
- Bonding mirrors to most common substrates.
- Jointing cladding panels.
- Any application requiring high performance, durable bonding of joints.
- Applications where resistance to chemical spillage is required.
- Interior and exterior use.

CHARACTERISTICS / ADVANTAGES

- Incredible initial grab, no slip, and gap-filling properties.
- High bonding strength.
- Can be applied to wet surfaces.
- Totally waterproof & weatherproof.
- Quick curing.
- Solvent free.
- Resistant to temperature extremes (-40°C to +70°C).
- Resistant to chemicals (10% dilute acids/alkalis, petrol, most solvents).
- Excellent primer-less adhesion to most surfaces including metals, some plastics, glass, concrete, plaster, plasterboard, wood, enamel, painted surfaces and more.

PRODUCT INFORMATION

Chemical Base	Hybrid polymer
Packaging	290ml cartridge
Colour	Clear
Shelf Life	12 months in original unopened packaging.
Storage Conditions	Store in cool dry conditions between + 5°C and 25°C.
Density	ca. 1.05 g/cm ³

Product Data Sheet EVERBUILD CLEAR FIX® June 2018, Version 01.01 020513020000000006

Shore A Hardness	40 - 50	
Elongation at Break	>100% (ISO8339)	
Service Temperature	-40°C to +70°C	
Yield	Approximately 11 linear metres per cartridge	
Sagging	Excellent slump resistance	
Ambient Air Temperature	+5°C to +40°C	
Curing Time	1-2 mm per 24 hours in depth	
Skin Time	15-30 mins	

APPLICATION INSTRUCTIONS

SUBSTRATE PREPARATION

All surfaces must be clean and dust free. Wet bonding can be performed with this product for temporary / emergency use but bond performance may be reduced.

APPLICATION METHOD / TOOLS

Cut the tip of the cartridge taking care not to damage the thread. Fix nozzle, cut aperture to required width and apply with a standard sealant gun.

As a nail replacement (panel) adhesive

- Surfaces must be sound, clean, dry and free from dust, grease, loose material etc.
- Prime dusty surfaces with EVERBUILD® PVA BOND diluted 1:4 with water and allow to dry.
- Apply using a standard sealant gun: cut tip of cartridge, apply nozzle and cut an opening to suit the required bead size.
- For bonding heavy items (plasterboard/worktops/ wall panels, etc) apply adhesive all around the edge of the item (30-50mm from edge) and cover the back with beads of adhesive at 300mm intervals. Alternatively, apply adhesive direct to battens and press into place. NOTE: With heavy items, always provide temporary support until the adhesive dries.
- For bonding lightweight items (coving, dado rails, skirting, etc) apply adhesive to back of item in one or two continuous beads and press immediately into place.
- Where gap-filling is required, mark areas where there is a large gap and apply a thicker bead to these areas.
- In all cases, clean up excess adhesive immediately with a cloth/white spirit.

Fixing mirrors

Apply 6mm diameter beads of sealant direct to the back of the mirror in vertical strips, spaced at 30-40mm centres. Immediately place mirror in position and secure with good, even pressure and with a slight twist action. Provide temporary support (tape) until adhesive has dried (24-48 hours). If required, EVERBUILD CLEAR FIX® may also be used to seal around the mirror 24 hours after fixing (to allow for cure).

CLEANING OF TOOLS

Uncured material can be removed by wiping with a cloth dampened with white spirit.

Cured material can be carefully removed by mechanical means.

LIMITATIONS

- Always use in conjunction with mechanical fixings for overhead applications.
- Use in conjunction with mechanical fixings for large mirrors (>0.5m² total area).
- For heavy items, provide temporary support until adhesive has dried.
- In areas of high temperature/UV some darkening/ discolouration may occur. This does not affect the performance of the adhesive.
- Do not seal mirror edges/plastic sheeting until adhesive has cured.
- Do not use on surfaces that bleed oils or plasticizers.
- It is the user's responsibility to determine suitability for use. If in doubt, please contact Technical Services Department for advice.
- Not for use as part of a structural glazing system.
- Not for use in aquarium manufacture. Use AQUA MATE*.
- Not for use in conjunction with bitumen, or asphalt. Use WEATHER MATE®.
- Do not use in conjunction with undiluted bleach, this can cause discoloration of product.
- Not suitable for use in or around chlorinated water.
- Yellowing can occur in the dark.

VALUE BASE

All technical data stated in this Data Sheet are based on laboratory tests. Actual measured data may vary due to circumstances beyond our control.

LOCAL RESTRICTIONS

Note that as a result of specific local regulations the declared data and recommended uses for this product may vary from country to country. Consult the local Product Data Sheet for the exact product data and uses.







ECOLOGY, HEALTH AND SAFETY

For information and advice on the safe handling, storage and disposal of chemical products, users shall refer to the most recent Safety Data Sheet (SDS) containing physical, ecological, toxicological and other safety-related data.

LEGAL NOTES

The information, and, in particular, the recommendations relating to the application and end-use of Sika products, are given in good faith based on Sika's current knowledge and experience of the products when properly stored, handled and applied under normal conditions in accordance with Sika's recommendations. In practice, the differences in materials, substrates and actual site conditions are such that no warranty in respect of merchantability or of fitness for a particular purpose, nor any liability arising out of any legal relationship whatsoever, can be inferred either from this information, or from any written recommendations, or from any other advice offered. The user of the product must test the product's suitability for the intended application and purpose. Sika reserves the right to change the properties of its products. The proprietary rights of third parties must be observed. All orders are accepted subject to our current terms of sale and delivery. Users must always refer to the most recent issue of the local Product Data Sheet for the product concerned, copies of which will be supplied on request.

EVERBUILD BUILDING PRODUCTS LTD

Site 41, Knowsthorpe Way Cross Green Industrial Estate Leeds, LS9 0SW Tel: 0113 240 3456 Web: www.everbuild.co.uk Twitter: @everbuild

SIKA LIMITED

Watchmead
Welwyn Garden City
Hertfordshire, AL7 1BQ
Tel: 01707 394444
Web: www.sika.co.uk
Twitter: @SikaLimited

SIKA IRELAND LIMITED

Ballymun Industrial Estate Ballymun Dublin 11, Ireland Tel: +353 1 862 0709 Web: www.sika.ie Twitter: @Sikalreland

EVERBUILDCLEARFIX-en-GBEVER-(06-2018)-1-1.pdf







