Note: This datasheet may be out of date

Please download the latest datasheet of LQH2HPZ4R7MDR# from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en/products/productdetail?partno=LQH2HPZ4R7MDR%23

#### "#" indicates a package specification code.

# LQH2HPZ4R7MDR#

Size Code 2520 (1008) in mm (in inch), 0.6mm max. Thickness. Low DC resistance design




















< List of part numbers with package codes > LQH2HPZ4R7MDRL



## Appearance & Shape



# Re

## References

Packaging	Specifications	Standard Packing Quantity
L	180Embossed Tape	4000

Mass (typ.)		
1 piece	0.01g	



### **Notices**

When rated current is applied to the products, inductance will be within ±30% of initial inductance value range. Keep the temperature (ambient temperature plus self-generation of heat) under 125°C. When rated current is applied to the products, the self-temperature rise shall be limited to 40°C max. (ambient temperature 85°C). When rated current is applied to the products, the self-temperature rise shall be limited to 20°C max. (ambient temperature 85 °C to 105°C).

1 of 4

#### Attention

- 1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2. This datasheet has only typical specifications because there is no space for detailed specifications
- Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering



LQH2HPZ4R7MDR#

Note: This datasheet may be out of date.  $Please\ download\ the\ latest\ data sheet\ of\ LQH2HPZ4R7MDR\#\ from\ the\ official\ website\ of\ Murata$ Manufacturing Co., Ltd.

http://www.murata.com/en/products/productdetail?partno=LQH2HPZ4R7MDR%23

"#" indicates a package specification code.



## **Specifications**

L size	2.5±0.1mm
W size	2.0±0.1mm
T size	0.55±0.05mm
Size code inch (mm)	1008 (2520)
Inductance	4.7μH±20%
Inductance Test Frequency	1MHz
Rated current (Isat) (Based on Inductance change)	650mA
Rated current (Itemp) (Based on Temperature rise)	650mA(Ambient temp.85°C) 390mA(Ambient temp.105°C)
Max. of DC resistance	0.672Ω
Operating Temperature Range (Self-temperature rise is included)	-40°C to 125°C
Class of magnetic shield	Magnetic Resin
Self resonance frequency (min.)	40MHz
Operating Temperature Range(Self-temperature rise is not included)	-40°C to 105°C
DC Resistance Intermediate Values	0.56Ω±20%
Series	LQH2HPZ_DR

2 of 4

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.



Note: This datasheet may be out of date.

Please download the latest datasheet of LQH2HPZ4R7MDR# from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en/products/productdetail?partno=LQH2HPZ4R7MDR%23


"#" indicates a package specification code.

# LQH2HPZ4R7MDR#




## Characteristic Data


The charts below may show another part number which shares its characteristics.








LQH2HPZ4R7MDR Q





3 of 4

#### Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering




# LQH2HPZ4R7MDR#

Note: This datasheet may be out of date.

Please download the latest datasheet of LQH2HPZ4R7MDR# from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en/products/productdetail?partno=LQH2HPZ4R7MDR%23

"#" indicates a package specification code.



LQH2HPZ4R7MDR Temp. rise

4 of 4

#### Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

