

Midi free-standing Beacons / EvoSIGNAL

Midi TwinFLASH 115-230VAC RD



| | |
|------------------|-----------------------|
| Part No.: | 261.120.60 |
| Series: | EvoSIGNAL Midi |



MECHANICAL DATA

| | |
|------------------------------|-----------------------------|
| Height | 130 mm |
| Diameter | 85 mm |
| Materials | PC PC/ABS |
| Dome colour | Red |
| Housing colour | Grey |
| Protection category | IP66 |
| Connection | Push-in terminal |
| cross-sectional area minimum | 0,25mm ² / 24AWG |
| cross-sectional area maximum | 1,50mm ² / 16AWG |
| Working temperature minimum | -30°C |
| Working temperature maximum | +60°C |
| UL Type Rating | Type 12 |
| Weight with packaging | 200 g |
| Product weight | 159 g |

ELECTRICAL DATA

| | |
|-----------------------------|------------------------------|
| Operating voltage | 115-230V |
| Operating voltage type | AC |
| Operating voltage frequency | 50Hz at 230V 60Hz at 115V |
| Operating voltage tolerance | +/- 10% |
| Rated operational voltage | 230 VAC |
| Rated operational current | 100 mA |
| Rated inrush current | 5,5A |
| Protection class | Protection class 2 |
| Pollution degree | 3 |
| Oversvoltage category | II |
| Isolation voltage | Ui = 250V; Uimp = 2.500V |

OPTICAL DATA

| | |
|------------------------------|----------------------------|
| Light source | LED |
| Light colour | Red |
| Optical signal image | EVS Flash TwinFlash |
| Flash frequency | 1 Hz |
| Service life optical | 50,000 h minimum |
| Pulse- & pause Duration [ms] | 28ON, 164OFF, 28ON, 744OFF |

! For additional installation and mounting information, refer to the appropriate user guide at www.werma.com. This printed copy is for information only and is subject to alteration.

Midi free-standing Beacons / EvoSIGNAL

Midi TwinFLASH 115-230VAC RD



For additional installation and mounting information, refer to the appropriate user guide at www.werma.com. This printed copy is for information only and is subject to alteration.