
COMPACT Splicing Connector; for all conductor types; max. 4 mm<sup>2</sup>; 2-conductor; with levers; transparent housing; Surrounding air temperature: max 85°C (T85); 4,00 mm<sup>2</sup>; transparent



www.wago.com/221-412







#### Item description

Your Benefits:

- Ease of use pull the lever up, insert a conductor and push the lever back down
- Available as 2-, 3- and 5-wire connectors
- Easily terminate conductors from 0.14 to 4 mm<sup>2</sup>
- Connect solid, stranded and fine-stranded conductors
- Time savings for installers and device manufacturers
- Quickly install devices with higher levels of power consumption

Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG

Hansastr. 27 32423 Minden

Phone: +49571 887-0 | Fax: +49571 887-169 Email: info.de@wago.com | Web: www.wago.com Do you have any questions about our products? We are always happy to take your call at +49 (571) 887-44222.

www.wago.com/221-412



- Safely install long cable runs with larger conductor cross sections
- Mounting carrier for installation conforms to standards
- Custom carriers are possible

#### Safety information 1:

in grounded power lines

#### Data

#### Electrical data

# Ratings per IEC/EN 60664-1

Ratings per	EN 60664	
Nominal voltage (II/2)	450 V	
Rated surge voltage (II/2)	4 kV	
Rated current	32 A	
Legend (ratings)	(II / 2) ≙ Overvoltage category II / Pollution degree 2	

# Ratings per UL 1059

Approvals per	UL 486C
Rated voltage UL (Use Group C)	600 V
Rated current UL (Use Group C)	20 A

#### Connection data

CAGE CLAMP <sup>®</sup>
Lever
Copper
4 mm²
0.2 4 mm² / 24 12 AWG
0.2 4 mm² / 24 12 AWG
0.14 4 mm² / 24 12 AWG
11 mm / 0.43 inch
2
1
Side-entry wiring

 $\label{thm:condition} \textbf{Subject to changes. Please also observe the further product documentation!}$ 

WAGO Kontakttechnik GmbH & Co. KG

Hansastr. 27 32423 Minden

Phone: +49571 887-0 | Fax: +49571 887-169 Email: info.de@wago.com | Web: www.wago.com Do you have any questions about our products?

www.wago.com/221-412



# Physical data

Width	13.1 mm / 0.516 inch
Height	8.3 mm / 0.327 inch
Depth	18.6 mm / 0.732 inch

# Material data

Color	transparent
Flammability class per UL94	V2
Color of actuator	orange
Weight	1.7 g

# **Environmental requirements**

Surrounding air temperature (operation)	85 ℃
Continuous operating temperature	105 °C
Temperature marking per EN 60998	T85

#### Commercial data

Product Group	7 (Push Wire Conn.)
Packaging type	BOX
Country of origin	DE
GTIN	4050821808435
Customs tariff number	85369010000

# Approvals / Certificates

# **Country specific Approvals**

Logo	Approval	Additional Approval Text	Certificate name
CCA	CCA DEKRA Certification B.V.	EN 60998	NTR NL- 7642
KEMA	CCA DEKRA Certification B.V.	EN 60998	71- 101731

# Ship Approvals

Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG

Hansastr. 27 32423 Minden

Phone: +49571 887-0 | Fax: +49571 887-169 Email: info.de@wago.com | Web: www.wago.com Do you have any questions about our products?

www.wago.com/221-412



Logo	Approval	Additional Approval Text	Certificate name
ABS.	ABS American Bureau of Shipping	-	18- HG1755093- PDA
DNV-GL	DNV GL Det Norske Veritas, Germanischer Lloyd	EN 60998	TAE000015T
CO LICE THE AMERICAN	<b>LR</b> Lloyds Register	EN 60998	04/20013 (E8)
UL-Approvals			
Logo	Approval	Additional Approval Text	Certificate name
LISTED GROUNDING EQUIP 66/A	UL Underwriters Laboratories Inc.	UL 467	E201573
LISTED WIRE CONNECTOR	UL Underwriters Laboratories Inc.	UL 486C	E69654

# Compatible products

# Jumper

1	Item no.: 221-941  Jumper; for conductor entry; 2-way; insulated; dark gray	www.wago.com/221-941
1	Item no.: 221-941/000-006  Jumper; for conductor entry; 2-way; insulated; blue	www.wago.com/221-941 /000-006
1	Item no.: 221-942  Jumper; for conductor entry; 2-way; insulated; dark gray	www.wago.com/221-942
	Item no.: 221-942/000-006  Jumper; for conductor entry; 2-way; insulated; blue	www.wago.com/221-942 /000-006

# Mounting adapter

 $\label{thm:continuity} \textbf{Subject to changes. Please also observe the further product documentation!}$ 

WAGO Kontakttechnik GmbH & Co. KG

Hansastr. 27 32423 Minden

Phone: +49571 887-0 | Fax: +49571 887-169 Email: info.de@wago.com | Web: www.wago.com Do you have any questions about our products?

www.wago.com/221-412





Item no.: 221-500

Mounting carrier; 221 Series - 4 mm<sup>2</sup>; for DIN-35 rail mounting/screw mounting; orange

www.wago.com/221-500

the plant

Item no.: 221-500/000-006

Mounting carrier; 221 Series - 4 mm<sup>2</sup>; for DIN-35 rail mounting/screw mounting; blue

www.wago.com/221-500

/000-006



Item no.: 221-500/000-053

Mounting carrier; 221 Series - 4 mm<sup>2</sup>; for DIN-35 rail mounting/screw mounting; dark gray-yellow

www.wago.com/221-500

/000-053



Item no.: 221-502

Mounting carrier; for 2-conductor terminal blocks; 221 Series - 4 mm<sup>2</sup>; for screw mounting; white

www.wago.com/221-502



Item no.: 221-502/000-004

Mounting carrier; for 2-conductor terminal blocks; 221 Series - 4 mm<sup>2</sup>; for screw mounting; black

www.wago.com/221-502

/000-004



Item no.: 221-512

Mounting carrier; for 2-conductor terminal blocks; 221 Series - 4 mm<sup>2</sup>; with snap-in mounting foot for horizontal mounting; white

www.wago.com/221-512



Item no.: 221-512/000-004

Mounting carrier; for 2-conductor terminal blocks; 221 Series - 4 mm²; with snap-in mounting foot for horizontal mounting; black

www.wago.com/221-512

/000-004



Item no.: 221-522

Mounting carrier; for 2-conductor terminal blocks; 221 Series - 4 mm<sup>2</sup>; with snap-in mounting foot for vertical mounting; white

www.wago.com/221-522



Item no.: 221-522/000-004

Mounting carrier; for 2-conductor terminal blocks; 221 Series - 4 mm<sup>2</sup>; with snap-in mounting foot for vertical mounting; black

www.wago.com/221-522 /000-004

# Downloads Documentation

# Bid Text

221-412 docx - Datei	23-jan-2019	docx 15.6 kB	Download
221-412 X81 - Datei	19-feb-2019	xml 3.5 kB	Download
Additional Information Technical explanations	3-apr-2019	pdf 2.2 MB	Download

Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG

Hansastr. 27 32423 Minden

Phone: +49571 887-0 | Fax: +49571 887-169 Email: info.de@wago.com | Web: www.wago.com Do you have any questions about our products?

www.wago.com/221-412



#### CAD/CAE-Data

#### **CAD** data

2D/3D Models 221-412 URL Download


#### CAE data

EPLAN Data Portal 221-412 URL Download


ZUKEN Portal 221-412 URL Download

# **Installation Notes**


#### Conductor termination



Strip conductor to 11 mm (0.43 inch).




Termination: Lift the lever to open the clamping unit and insert a stripped conductor.



Then, lower the lever to close the clamp.

#### Application



Wiring fine-stranded conductors in a junction box.



Custom low-voltage lighting system



Lighting distribution in ceiling canopy

Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG Hansastr. 27 32423 Minden

Phone: +49571 887-0 | Fax: +49571 887-169 Email: info.de@wago.com | Web: www.wago.com Do you have any questions about our products? We are always happy to take your call at +49 (571) 887-44222.

www.wago.com/221-412





Pendant light connection in suspended ceilings



COMPACT Splicing Connectors for All Conductor Types, 4 mm² (12 AWG), 221 Series

 $\label{thm:condition} \textbf{Subject to changes. Please also observe the further product documentation!}$ 

www.wago.com/221-412





Compact, lever-operated splicing connectors:

Tool-free connection of up to five stripped, fine-stranded conductors from 0.14 ... 4 mm², as well as solid or stranded conductors from 0.2 ... 4 mm² (24 ... 12 AWG).

#### How these work:

Pull up one of the orange operating levers to open the clamping unit. Then insert the conductor and push the lever back down, flush with the connector housing.

#### Safety:

The specially designed rest position of the lever reliably prevents accidental unclamping of a connected conductor.

Application safety, for any type of conductor (solid, stranded, fine-stranded), is confirmed by approvals like ENEC or UL.

 $\label{thm:continuity} \textbf{Subject to changes. Please also observe the further product documentation!}$ 

WAGO Kontakttechnik GmbH & Co. KG Hansastr. 27 32423 Minden

Phone: +49571 887-0 | Fax: +49571 887-169 Email: info.de@wago.com | Web: www.wago.com Do you have any questions about our products? We are always happy to take your call at +49 (571) 887-44222.