Customer: ROXBURGH ELECTRONICS LIMITED	No. KX-96-0796
	Date: Jan. 29. 1996
Attention:	
Your ref. No:	
Vour Part No:21 1130	•

# SPECIFICATIONS

ALPS:

MODEL \_ RK09K11310KB \_\_\_\_

F.E.C. No: 697-990

Sample No.: 60445575M

RECEIPT STATUS
RECEIVED
By. Date
Signature
Name
Title

ALPS ELECTRIC CO., LTD.

HEAD OFFICE 1-7. YUKIGAYA-OHTSUKA-CHO. OHTA-KU. TOKYO 145 JAPAN DSG'D W. Sato

APP'D C. Maeda.

ENG. DEPT. DIVISION

Sales

#### SPECIFICATIONS

1. THIS SPECIFICATIONS APPLY TO RKO9K1130

POTENT IOMETERS.

2. CONTENTS OF THIS SPECIFICATIONS.

3. MARKING

·MARKING ON ALL UNITS DATE CODE, RESIST. VALUE, TAPER

4. REMARKS

· NOTES

•METHOD OF MARKING
TO BE STAMPED WITH BLACK INK OR LASER MARKING
•This unit uses polycarbonate. To be careful for using this unit in such violent gas atmospheric condition as ammonia amine, alkaline aqueous solution, aromatic hydrocarbon, keton, ester, alky! hydrocarbon, etc.

### SPECIFICATIONS

#### ELECTRICAL

1. Total resistance : 10k \Omega \pm 20%

2. Rated power : 0.05 W

3. Rated voltage

The rated voltage shall be the voltage of D.C. or A.C. (commercial frequency effective value) corresponding to the rated power (dissipation), and be obtained from the following formula. When the obtained rated voltage exceeds the maximum working voltage given in the following, however, the maximum working voltage of the following shall be the rated voltage.

 $E = \sqrt{P \cdot R} (V)$ 

Where

E: Rated voltage (V)

P: Rated power (dissipation) (W)

R: Nominal total resistance  $(\Omega)$ 

Maximum working voltage : 50 V A. C. , 20 V D. C.

4. Residual resistance between terminals

between term. 142, term. 243 : 3000 max.

5. Sliding noise : Less than 100 mV measured by method of JIS C 6443.

6. Insulation resistance : Greater than 100 MQ measured by D. C. 250V.

7. Withstand voltage: More than 1 minute with an application of A.C. 250 V.

8. Taper : E

#### MECHANICAL

1. Overall rotational angle : 280°±5°

2. Operation torque : 10~80 gf·cm

3. Shaft end stop strength : 3 Kgf·cm MIN.

4. Starting torugue : 100 gf·cm MAX.

5. Resistance to soldering heat :

After soldering (Less than 300°C and quicker than 3 seconds) there shall be no evidence of poor contact between resistance element and terminals, or any physical damages as a result of the test.

6. Play of shaft

The resistor shall be mounted by soldering the mounting legs on the panel, and a side thrust of 250 gf·cm at the end of the shaft shall be applied, then the total play of the shaft shall not exceed  $0.8 \times L / 20 \text{ mm p-p}$ .

7. Eccentricity of shaft:

The accentricity of the root of shaft shall not exceed 0.35mm against the center of the mounting position.

8. Robustness of shaft against end thrust :

The shaft shall withstand against end thrust of not less than 5 Kgf for 3 seconds.  $\cdot$ 

9. Robustness of shaft against side thrust :

The shaft shall withstand against side thrust of not less than 4 Kef·cm for 3 seconds on the end of the shaft at right angles to the axis of the shaft after mounting the resistor by soldering.

#### **ENDURANCE**

1. Rotational life : 5,000 cycles min.


#### NOTE

1. The items except above mentioned items shall meet or exceed JIS C 6443. 2. Operating temperature :-10° C $\sim$ +60° C. 3. Storage temperature :-30° C $\sim$ +70° C.

					Au	ALI	PS El	ECTRIC CO., LTD.
					APPD.	СНКО.	OSGO.	TITLE
<del> </del>		<del> </del>	<del> </del> -	<del> </del>	Jul. 13, 193	Jul. 13. '93	Jal. 13. '93	
					S. Aizawa	M Salah	Y. Saitoh	DOCUMENT NO.
SYMB	DATE	APPD	CHKD	DSGD	U. AIZana	M. Jatun	11 0011011	G0445575M



## ALPS ELECTRIC CO., LTD 1-7 YUKIGAYA OTSUKA-CHO OTA-KU TOKYO JAPAN



AT 140° C. W. SHAFT ROTATION FROM FULL C. C. W. POSITION VOLTAGE PERCENT SHALL FALL WITHIN THE LIMITS OF 40~60 PERCENT.

		<del>                                     </del>		<del> </del>	APPD.	CHKO.	DSGD.	NAME
					Jal. 13. '93	Jal. 13. 193	Jal. 13 '93	RESISTANCE TAPER (B)
		ļ			1		}	DOCUMENT NO.
SYMB	DATE	APPD	CHKD	DSGD	K. Magami	K. Sasaki	K. Suzuki	G0445575M

