



## Safety Data Sheet according to (EC) No 1907/2006 as amended

Page 1 of 12

LOCTITE 222

SDS No. : 168430  
V008.1

Revision: 24.09.2020

printing date: 26.04.2021

Replaces version from: 30.03.2020

### SECTION 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1. Product identifier

LOCTITE 222

#### 1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use:

Anaerobic Adhesive

#### 1.3. Details of the supplier of the safety data sheet

Henkel Ltd

Adhesives

Wood Lane End

HP2 4RQ Hemel Hempstead

Great Britain

Phone: +44 (1442) 278000

Fax-no.: +44 (1442) 278071

ua-productsafety.uk@henkel.com

#### 1.4. Emergency telephone number

24 Hours Emergency Tel: +44 (0)1442 278497

### SECTION 2: Hazards identification

#### 2.1. Classification of the substance or mixture

##### Classification (CLP):

Serious eye irritation

Category 2

H319 Causes serious eye irritation.

Specific target organ toxicity - single exposure

Category 3

H335 May cause respiratory irritation.

Target organ: respiratory tract irritation

Chronic hazards to the aquatic environment

Category 3

H412 Harmful to aquatic life with long lasting effects.

#### 2.2. Label elements

##### Label elements (CLP):

##### Hazard pictogram:



Contains

Cumene hydroperoxide

<b>Signal word:</b>	Warning
<b>Hazard statement:</b>	H319 Causes serious eye irritation. H335 May cause respiratory irritation. H412 Harmful to aquatic life with long lasting effects.
<b>Precautionary statement:</b>	"***" ***For consumer use only: P101 If medical advice is needed, have product container or label at hand. P102 Keep out of reach of children. P501 Dispose of contents/container in accordance with national regulation.***
<b>Precautionary statement: Prevention</b>	P261 Avoid breathing vapors. P273 Avoid release to the environment.
<b>Precautionary statement: Response</b>	P337+P313 If eye irritation persists: Get medical advice/attention.

### 2.3. Other hazards

None if used properly.

Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.

## SECTION 3: Composition/information on ingredients

### 3.2. Mixtures

#### General chemical description:

Product based on polyethylene glycol dimethacrylate.

**Declaration of the ingredients according to CLP (EC) No 1272/2008:**

Hazardous components CAS-No.	EC Number REACH-Reg No.	content	Classification
Cumene hydroperoxide 80-15-9	201-254-7 01-2119475796-19	0,25- < 2,5 %	Acute Tox. 4; Dermal H312 STOT RE 2 H373 Acute Tox. 4; Oral H302 Org. Perox. E H242 Acute Tox. 3; Inhalation H331 Aquatic Chronic 2 H411 Skin Corr. 1B H314
N,N-Diethyl-p-toluidine 613-48-9	210-345-0	0,1- < 1 %	Acute Tox. 3; Oral H301 Acute Tox. 3; Dermal H311 Acute Tox. 3; Inhalation H331 STOT RE 2 H373 Aquatic Chronic 3 H412
1,4-Naphthalenedione 130-15-4	204-977-6	0,01- < 0,025 % ( 100 ppm- < 250 ppm)	Acute Tox. 3; Oral H301 Skin Irrit. 2; Dermal H315 Skin Sens. 1 H317 Eye Irrit. 2 H319 Acute Tox. 1; Inhalation H330 STOT SE 3; Inhalation H335 Aquatic Acute 1 H400 Aquatic Chronic 1 H410 M factor (Acute Aquat Tox): 10 M factor (Chron Aquat Tox): 10

**For full text of the H - statements and other abbreviations see section 16 "Other information".  
Substances without classification may have community workplace exposure limits available.**

## SECTION 4: First aid measures

### 4.1. Description of first aid measures

**Inhalation:**

Should not be a problem as product is of low volatility. However, if feeling unwell remove patient to fresh air.

**Skin contact:**

Rinse with running water and soap.  
Obtain medical attention if irritation persists.

**Eye contact:**

Rinse immediately with plenty of running water (for 10 minutes), seek medical attention from a specialist.

**Ingestion:**

Rinse mouth, drink 1-2 glasses of water, do not induce vomiting, consult a doctor.

**4.2. Most important symptoms and effects, both acute and delayed**

EYE: Irritation, conjunctivitis.

RESPIRATORY: Irritation, coughing, shortness of breath, chest tightness.

Prolonged or repeated contact may cause skin irritation.

**4.3. Indication of any immediate medical attention and special treatment needed**

See section: Description of first aid measures

**SECTION 5: Firefighting measures****5.1. Extinguishing media****Suitable extinguishing media:**

Foam, extinguishing powder, carbon dioxide.

**Extinguishing media which must not be used for safety reasons:**

None known

**5.2. Special hazards arising from the substance or mixture**

In the event of a fire, carbon monoxide (CO), carbon dioxide (CO<sub>2</sub>) and nitrogen oxides (NO<sub>x</sub>) can be released.

**5.3. Advice for firefighters**

Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear.

**Additional information:**

In case of fire, keep containers cool with water spray.

**SECTION 6: Accidental release measures****6.1. Personal precautions, protective equipment and emergency procedures**

Ensure adequate ventilation.

Avoid contact with skin and eyes.

Wear protective equipment.

**6.2. Environmental precautions**

Do not empty into drains / surface water / ground water.

**6.3. Methods and material for containment and cleaning up**

For small spills wipe up with paper towel and place in container for disposal.

For large spills absorb onto inert absorbent material and place in sealed container for disposal.

Dispose of contaminated material as waste according to Section 13.

**6.4. Reference to other sections**

See advice in section 8

**SECTION 7: Handling and storage****7.1. Precautions for safe handling**

Use only in well-ventilated areas.

Gloves and safety glasses should be worn

Avoid skin and eye contact.

Prolonged or repeated skin contact should be avoided to minimise any risk of sensitisation.

See advice in section 8

**Hygiene measures:**

Good industrial hygiene practices should be observed.

Do not eat, drink or smoke while working.

Wash hands before work breaks and after finishing work.

**7.2. Conditions for safe storage, including any incompatibilities**

Refer to Technical Data Sheet

**7.3. Specific end use(s)**

Anaerobic Adhesive

**SECTION 8: Exposure controls/personal protection****8.1. Control parameters****Occupational Exposure Limits**Valid for  
Great Britain

Ingredient [Regulated substance]	ppm	mg/m <sup>3</sup>	Value type	Short term exposure limit category / Remarks	Regulatory list
Propane-1,2-diol 57-55-6 [PROPANE-1,2-DIOL, PARTICULATES]		10	Time Weighted Average (TWA):		EH40 WEL
Propane-1,2-diol 57-55-6 [PROPANE-1,2-DIOL, TOTAL VAPOUR AND PARTICULATES]	150	474	Time Weighted Average (TWA):		EH40 WEL

**Occupational Exposure Limits**Valid for  
Ireland

Ingredient [Regulated substance]	ppm	mg/m <sup>3</sup>	Value type	Short term exposure limit category / Remarks	Regulatory list
Propane-1,2-diol 57-55-6 [PROPANE-1,2-DIOL]		10	Time Weighted Average (TWA):		IR_OEL
Propane-1,2-diol 57-55-6 [PROPANE-1,2-DIOL]	150	470	Time Weighted Average (TWA):		IR_OEL

**Predicted No-Effect Concentration (PNEC):**

Name on list	Environmental Compartment	Exposure period	Value				Remarks
			mg/l	ppm	mg/kg	others	
.alpha.,.alpha.-Dimethylbenzyl hydroperoxide 80-15-9	aqua (freshwater)		0,0031 mg/l				
.alpha.,.alpha.-Dimethylbenzyl hydroperoxide 80-15-9	aqua (marine water)		0,00031 mg/l				
.alpha.,.alpha.-Dimethylbenzyl hydroperoxide 80-15-9	aqua (intermittent releases)		0,031 mg/l				
.alpha.,.alpha.-Dimethylbenzyl hydroperoxide 80-15-9	Sewage treatment plant		0,35 mg/l				
.alpha.,.alpha.-Dimethylbenzyl hydroperoxide 80-15-9	sediment (freshwater)				0,023 mg/kg		
.alpha.,.alpha.-Dimethylbenzyl hydroperoxide 80-15-9	sediment (marine water)				0,0023 mg/kg		
.alpha.,.alpha.-Dimethylbenzyl hydroperoxide 80-15-9	Soil				0,0029 mg/kg		

**Derived No-Effect Level (DNEL):**

Name on list	Application Area	Route of Exposure	Health Effect	Exposure Time	Value	Remarks
.alpha.,.alpha.-Dimethylbenzyl hydroperoxide 80-15-9	Workers	inhalation	Long term exposure - systemic effects		6 mg/m3	

**Biological Exposure Indices:**

None

**8.2. Exposure controls:**

Engineering controls:

Ensure good ventilation/extraction.

Respiratory protection:

Ensure adequate ventilation.

An approved mask or respirator fitted with an organic vapour cartridge should be worn if the product is used in a poorly ventilated area

Filter type: A (EN 14387)

Hand protection:

Chemical-resistant protective gloves (EN 374).

Suitable materials for short-term contact or splashes (recommended: at least protection index 2, corresponding to &gt; 30 minutes permeation time as per EN 374):

nitrile rubber (NBR; &gt;= 0.4 mm thickness)

Suitable materials for longer, direct contact (recommended: protection index 6, corresponding to &gt; 480 minutes permeation time as per EN 374):

nitrile rubber (NBR; &gt;= 0.4 mm thickness)

This information is based on literature references and on information provided by glove manufacturers, or is derived by analogy with similar substances. Please note that in practice the working life of chemical-resistant protective gloves may be considerably shorter than the permeation time determined in accordance with EN 374 as a result of the many influencing factors (e.g. temperature). If signs of wear and tear are noticed then the gloves should be replaced.

Eye protection:

Safety glasses with sideshields or chemical safety goggles should be worn if there is a risk of splashing.

Protective eye equipment should conform to EN166.

Skin protection:

Wear suitable protective clothing.

Protective clothing should conform to EN 14605 for liquid splashes or to EN 13982 for dusts.

Advices to personal protection equipment:

The information provided on personal protective equipment is for guidance purposes only. A full risk assessment should be conducted prior to using this product to determine the appropriate personal protective equipment to suit local conditions.

Personal protective equipment should conform to the relevant EN standard.

**SECTION 9: Physical and chemical properties****9.1. Information on basic physical and chemical properties**

Appearance	liquid purple
Odor	characteristic
Odour threshold	No data available / Not applicable
pH (; Conc.: 100 % product)	3,00 - 6,00
Melting point	No data available / Not applicable
Solidification temperature	No data available / Not applicable

Initial boiling point	> 150 °C (> 302 °F)
Flash point	> 100 °C (> 212 °F)
Evaporation rate	No data available / Not applicable
Flammability	No data available / Not applicable
Explosive limits	No data available / Not applicable
Vapour pressure (25 °C (77 °F))	< 0,1300000 mbar
Vapour pressure (50 °C (122 °F))	< 300 mbar
Relative vapour density:	No data available / Not applicable
Density ( $\rho$ )	1,08 g/cm <sup>3</sup>
Bulk density	No data available / Not applicable
Solubility	No data available / Not applicable
Solubility (qualitative) (Solvent: Water)	Slight
Solubility (qualitative) (Solvent: Acetone)	Miscible
Partition coefficient: n-octanol/water	No data available / Not applicable
Auto-ignition temperature	No data available / Not applicable
Decomposition temperature	No data available / Not applicable
Viscosity	No data available / Not applicable
Viscosity (kinematic)	No data available / Not applicable
Explosive properties	No data available / Not applicable
Oxidising properties	No data available / Not applicable

**9.2. Other information**

No data available / Not applicable

## SECTION 10: Stability and reactivity

**10.1. Reactivity**

Peroxides.

**10.2. Chemical stability**

Stable under recommended storage conditions.

**10.3. Possibility of hazardous reactions**

See section reactivity

**10.4. Conditions to avoid**

Stable under normal conditions of storage and use.

**10.5. Incompatible materials**

See section reactivity.

**10.6. Hazardous decomposition products**

Oxides of carbon.

## SECTION 11: Toxicological information

**11.1. Information on toxicological effects****Acute oral toxicity:**

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Species	Method
Cumene hydroperoxide 80-15-9	LD50	382 mg/kg	rat	other guideline:
1,4-Naphthalenedione 130-15-4	LD50	190 mg/kg	rat	not specified

**Acute dermal toxicity:**

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Species	Method
Cumene hydroperoxide 80-15-9	LD50	530 - 1.060 mg/kg	rat	other guideline:
Cumene hydroperoxide 80-15-9	Acute toxicity estimate (ATE)	1.100 mg/kg		Expert judgement

**Acute inhalative toxicity:**

No substance data available.  
No data available.

**Skin corrosion/irritation:**

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result	Exposure time	Species	Method
Cumene hydroperoxide 80-15-9	corrosive		rabbit	Draize Test

**Serious eye damage/irritation:**

No data available.

**Respiratory or skin sensitization:**

No data available.

**Germ cell mutagenicity:**

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result	Type of study / Route of administration	Metabolic activation / Exposure time	Species	Method
Cumene hydroperoxide 80-15-9	positive	bacterial reverse mutation assay (e.g Ames test)	without		OECD Guideline 471 (Bacterial Reverse Mutation Assay)

**Carcinogenicity**

No data available.

**Reproductive toxicity:**

No data available.

**STOT-single exposure:**

No data available.



**STOT-repeated exposure::**

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result / Value	Route of application	Exposure time / Frequency of treatment	Species	Method
Cumene hydroperoxide 80-15-9		inhalation: aerosol	6 h/d 5 d/w	rat	not specified

**Aspiration hazard:**

No data available.

**SECTION 12: Ecological information****General ecological information:**

Do not empty into drains / surface water / ground water.

**12.1. Toxicity****Toxicity (Fish):**

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
Cumene hydroperoxide 80-15-9	LC50	3,9 mg/l	96 h	Oncorhynchus mykiss	OECD Guideline 203 (Fish, Acute Toxicity Test)

**Toxicity (Daphnia):**

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
Cumene hydroperoxide 80-15-9	EC50	18 mg/l	48 h	Daphnia magna	OECD Guideline 202 (Daphnia sp. Acute Immobilisation Test)

**Chronic toxicity to aquatic invertebrates**

No data available.

**Toxicity (Algae):**

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
Cumene hydroperoxide 80-15-9	ErC50	3,1 mg/l	72 h	Pseudokirchneriella subcapitata	OECD Guideline 201 (Alga, Growth Inhibition Test)
1,4-Naphthalenedione 130-15-4	EC50	0,011 mg/l	72 h	Dunaliella bioculata	OECD Guideline 201 (Alga, Growth Inhibition Test)

**Toxicity to microorganisms**

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
Cumene hydroperoxide 80-15-9	EC10	70 mg/l	30 min		not specified

**12.2. Persistence and degradability**

Hazardous substances CAS-No.	Result	Test type	Degradability	Exposure time	Method
Cumene hydroperoxide 80-15-9		no data	0 %	28 d	OECD Guideline 301 B (Ready Biodegradability: CO2 Evolution Test)
1,4-Naphthalenedione 130-15-4	not readily biodegradable.	no data	0 - 60 %		OECD 301 A - F

**12.3. Bioaccumulative potential**

Hazardous substances CAS-No.	Bioconcentration factor (BCF)	Exposure time	Temperature	Species	Method
Cumene hydroperoxide 80-15-9	9,1			calculation	OECD Guideline 305 (Bioconcentration: Flow-through Fish Test)

**12.4. Mobility in soil**

Cured adhesives are immobile.

Hazardous substances CAS-No.	LogPow	Temperature	Method
Cumene hydroperoxide 80-15-9	2,16		not specified
1,4-Naphthalenedione 130-15-4	1,71		not specified

**12.5. Results of PBT and vPvB assessment**

Hazardous substances CAS-No.	PBT / vPvB
Cumene hydroperoxide 80-15-9	Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.
1,4-Naphthalenedione 130-15-4	Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.

**12.6. Other adverse effects**

No data available.

**SECTION 13: Disposal considerations****13.1. Waste treatment methods**

Product disposal:

Dispose of in accordance with local and national regulations.

Contribution of this product to waste is very insignificant in comparison to article in which it is used

Disposal of uncleaned packages:

After use, tubes, cartons and bottles containing residual product should be disposed of as chemically contaminated waste in an authorised legal land fill site or incinerated.

Disposal must be made according to official regulations.

Waste code

08 04 09 waste adhesives and sealants containing organic solvents and other dangerous substances

The valid EWC waste code numbers are source-related. The manufacturer is therefore unable to specify EWC waste codes for the articles or products used in the various sectors. The EWC codes listed are intended as a recommendation for users. We will be happy to advise you.

## SECTION 14: Transport information

### 14.1. UN number

ADR	Not dangerous goods
RID	Not dangerous goods
ADN	Not dangerous goods
IMDG	Not dangerous goods
IATA	Not dangerous goods

### 14.2. UN proper shipping name

ADR	Not dangerous goods
RID	Not dangerous goods
ADN	Not dangerous goods
IMDG	Not dangerous goods
IATA	Not dangerous goods

### 14.3. Transport hazard class(es)

ADR	Not dangerous goods
RID	Not dangerous goods
ADN	Not dangerous goods
IMDG	Not dangerous goods
IATA	Not dangerous goods

### 14.4. Packing group

ADR	Not dangerous goods
RID	Not dangerous goods
ADN	Not dangerous goods
IMDG	Not dangerous goods
IATA	Not dangerous goods

### 14.5. Environmental hazards

ADR	not applicable
RID	not applicable
ADN	not applicable
IMDG	not applicable
IATA	not applicable

### 14.6. Special precautions for user

ADR	not applicable
RID	not applicable
ADN	not applicable
IMDG	not applicable
IATA	not applicable

### 14.7. Transport in bulk according to Annex II of Marpol and the IBC Code

not applicable

## SECTION 15: Regulatory information

### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

VOC content < 3 %  
(2010/75/EC)

### 15.2. Chemical safety assessment

A chemical safety assessment has not been carried out.

**SECTION 16: Other information**

The labelling of the product is indicated in Section 2. The full text of all abbreviations indicated by codes in this safety data sheet are as follows:

- H242 Heating may cause a fire.
- H301 Toxic if swallowed.
- H302 Harmful if swallowed.
- H311 Toxic in contact with skin.
- H312 Harmful in contact with skin.
- H314 Causes severe skin burns and eye damage.
- H315 Causes skin irritation.
- H317 May cause an allergic skin reaction.
- H319 Causes serious eye irritation.
- H330 Fatal if inhaled.
- H331 Toxic if inhaled.
- H335 May cause respiratory irritation.
- H373 May cause damage to organs through prolonged or repeated exposure.
- H400 Very toxic to aquatic life.
- H410 Very toxic to aquatic life with long lasting effects.
- H411 Toxic to aquatic life with long lasting effects.
- H412 Harmful to aquatic life with long lasting effects.

**Further information:**

This Safety Data Sheet has been produced for sales from Henkel to parties purchasing from Henkel, is based on Regulation (EC) No 1907/2006 and provides information in accordance with applicable regulations of the European Union only. In that respect, no statement, warranty or representation of any kind is given as to compliance with any statutory laws or regulations of any other jurisdiction or territory other than the European Union. When exporting to territories other than the European Union, please consult with the respective Safety Data Sheet of the concerned territory to ensure compliance or liaise with Henkel's Product Safety and Regulatory Affairs Department (ua-productsafety.de@henkel.com) prior to export to other territories than the European Union.

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.

Dear Customer,

Henkel is committed to creating a sustainable future by promoting opportunities along the entire value chain. If you would like to contribute by switching from a paper to the electronic version of SDS, please contact the local Customer Service representative. We recommend to use a non-personal email address (e.g. SDS@your\_company.com).

**Relevant changes in this safety data sheet are indicated by vertical lines at the left margin in the body of this document. Corresponding text is displayed in a different color on shadowed fields.**