NSMANN®	Material - Safety - Data Sheet (MSDS)	No
	Ansmann Lithium-Ion Batteries single cells and multi-cell battery packs	1
Date of issue:2011 - 06 - 10Revision no:13Revision date:2021 - 03 - 26Editor:Ansmann AG	for their information only. The information and recommendations set forth herein	-
Product and Supplier Ide	ntification	
Product name: Type: Models / types: Electrochemical system:	Ansmann Li-Ion Battery; Ansmann Li-Polymer Battery Rechargeable Li-Ion battery Prismatic and round cells negative electrode: graphite; positive electrode: metall oxide (proprietary)	
Supplier: Germany Address: Phone / Fax: Home / email:	ANSMANN AG Industriestraße 10; 97959 Assamstadt; Germany + 49 (0) 6294 42040 / + 49 (0) 6294 420444 ansmann.de / info@ansmann.de	
Subsidiaries:		
United Kingdom Address: Phone / Facsimile: email:	ANSMANN UK LTD. Units 11-12, RO24, Harlow Business Park, Harlow, Essex. CM19 5QB. UK +44 (0) 870 609 2233 / +44 (0) 870609 2234 UK@ansmann.de	
Hong Kong Address:	ANSMANN Energy Int. LTD. Unit 3117-18, 31/F; Tower 1; Millenium City 1; No. 388 Kwun Tong Road; Kwun Tong, kowloon; Hong-Kong hongkong@ansmann.de	
China Address:	HuiZhou City ANSMANN Trading Co. LTD Da Lian Industrial Park, Rengtu Village Ruhu Town Huicheng District, 516169 Huizhou City Guangdong, China china@ansmann.de	
Sweden Address:	ANSMANN Nordic AB Victor Hasselblads Gata 11, 421 31 Västra Frölunda, Sweden nordic@ansmann.de	
France Address:	Ansmann Energy France 5, Place Copernic; Immeuble Boréal - Courcouronnes; F-91023 Evry Cedex; France	
EMERGENCY CONTACT:	For chemical emergency (spill, leak, fire, exposure or accident) call phone no.: +49 6294 4204 0	
Hazards Identification		
not hazardous when used acc is maintained. Do not short circuit, puncture,	patteries described in this Product Safety Data Sheet are sealed units which are cording to the recommendations of the manufacturer and as long as their integrity incinerate, crush, immerse in water, force discharge or expose to temperatures temperature range of the product. Risk of fire or explosion.	

exposure only in case of abuse (mechanical, thermal, electrical) which leads to the activation of safety valves and/or the rupture of the battery container. Electrolyte leakage, electrode materials reaction with moisture/water

or battery vent/explosion/fire may follow, depending upon the circumstances.



for Ansmann Lithium-Ion Batteries

single cells and multi-cell battery packs

No.5

2/7

3. Composition and Informations on Ingredients

Each cell consists of a hermetically sealed metallic container containing a number of chemicals and materials of construction of which the following could potentially be hazardous upon release.

Ingredient	Content	CAS No.	Hazard Categories	Hazard Statements
metal oxide compounds e.g. Li-Ni, Li-Mn, Li-Co, Li-FePo	20 - 50%	(proprietary)	Skin Sens. 1; Acute Tox. 1 Resp. Sens. 1; Carc. 1B STOT RE 1; Aquatic Chronic 3	H317, H330 H334, H350 H372, H412
Organic Solvents	10 - 20%			
EA (Ethyl-Acetate)		141-78-6	Flam. Liq 1; Eye Irrit. 2; STOT S	E 3 H225, H319, H336
EC (Ethylene Carbonate)		96-49-1	Acute Tox. 4; Eye Irrit. 2; STOT	RE 2 H302, H319, H373
DMC (Di Methyl Carbonate		616-38-6	Flam. Liq. 2	H225
EMC (Ethyl Methyl Carb.)		623-53-0	Flam. Liq. 2	H225
DEC (Diethylcarbonate)		105-58-8	Flam. Liq. 3	H226
Lithium-Hexa-Fluoro Phosphate (LiPF ₆)	1 - 3%	21324-40-3	Acute Tox. 3; Asp. TOX. 1	H301, H314
Polyvinylidene Fluoride (PVDF)	< 5%	24937-79-9	n/a	n/a
Styrene Butadiene Rubber (SBR)	< 5%	9003-55-8	n/a	n/a
Copper (Cu)	2 - 11%	7440-50-8	Flam. Sol. 1	H228
Aluminium (Al)	2 - 10%	7429-90-5	Flam Sol.1; Water-react. 3	H228, H261
Carbon (C) (Graphite)	10 - 30%	7440-44-0	n/a	n/a
stainless steel	0 - 35%	n/a	n/a	n/a

4. First Aid Measures

In case of accumulator breakage or burst, please evacuate employees from the contaminated area and ensure maximal ventilation in order to break-up corrosive gas, smoke and unpleasant odors. If it occurs, by accident, following measures must be taken:

Inhalation	Remove from exposure, rest and keep warm. In severe cases obtain medical attention.
Skin Contact	Wash off skin thoroughly with water. Remove contaminated clothing and wash before re-use. In severe cases obtain medical attention.
Eye Contact	Irrigate thoroughly with water for at least 15 minutes. Obtain medical attention.
Ingestion	Wash out mouth thoroughly with water and give plenty of water to drink. Obtain medical attention.
Further treatment	All cases of eye contamination, persistent skin irritation and casualities who have swallowed this substance or been affected by breathing its vapours should be seen by a doctor.



Ansmann Lithium-Ion Batteries single cells and multi-cell battery packs

3/7

5.				
5.	Fire Fighting Measures			
	Suitable extinguishing media:	Dry powder is applicable for burning lithium ion batteries. Metal fire extinction powder, rock salt or dry sand are suitable if only a few batteries are involved.		
	Extinguishing media with limited suitability:	Carbon dioxide (CO2) is only applicable for incipient fire. Do not use water.		
	Special protection equip- ment during fire-fighting:	Contamination cloth including self-contained breathing apparatus.		
	Special hazard:	Cells may explode and release metal parts.		
		At contact of electrolyte with water traces of hydrofluoric acid may be formed. In this case avoid contact and take care for good ventilation.		
		At contact of changed anode material with water extremely flammable hydrogen gas is generated.		
	Attention:	Do not let used extinguishing media penetrate into surface water or ground water. If necessary, thicken water or foam with suitable solids. Dispose off properly.		
	Accidental Release Meas	sures		
	Person related measures:	Wear personal protective equipment adapted to the situation (protection gloves, face protection, breathing protection).		
	Environmental protection measures:	Bind released ingredients with powder (rock salt, sand). Dispose off according to the local law and rules. Avoid leached substances to penetrate into the earth, canalization or water.		
	Treatment for cleaning:	If battery casing is dismantled, small amounts of electrolyte may leak. Package the battery tightly including ingredients together with lime, sand or rock salt. Then clean with water.		
	Precautions for safe Handling and Use			
	Storage:	Store in a cool (preferable below 30°C), well ventilated area, away from moisture, sources of heat, open flames, food and drink. Elevated temperatures can result in shortened battery life. Temperautes above 70°C may result in battery leakage and rupture. Keep adequate clearance between walls and batteries. Since short circuit can cause burn, leakage and rupture hazard, keep batteries in original packaging until use and do not jumble them. Preferred storage at 30 50% of nominal battery capacity. A fire alarm is recommended in case of storage of large amounts.		
	Storage: Handling:	Store in a cool (preferable below 30°C), well ventilated area, away from moisture, sources of heat, open flames, food and drink. Elevated temperatures can result in shortened battery life. Temperautes above 70°C may result in battery leakage and rupture. Keep adequate clearance between walls and batteries. Since short circuit can cause burn, leakage and rupture hazard, keep batteries in original packaging until use and do not jumble them. Preferred storage at 30 50% of nominal battery capacity.		
	-	 Store in a cool (preferable below 30°C), well ventilated area, away from moisture, sources of heat, open flames, food and drink. Elevated temperatures can result in shortened battery life. Temperautes above 70°C may result in battery leakage and rupture. Keep adequate clearance between walls and batteries. Since short circuit can cause burn, leakage and rupture hazard, keep batteries in original packaging until use and do not jumble them. Preferred storage at 30 50% of nominal battery capacity. A fire alarm is recommended in case of storage of large amounts. Do not crush, pierce, short (+) and (-) battery terminals with conductive (i.e. metal) goods, which would end up into excessive heating. Do not directly heat or solder. Do not throw batteries into fire or water. Do not disassemble, mutilate or mechanically abuse cells and batteries. Avoid deep discharge. Follow manufacturers recommendations regarding maximum recommended 		

	N-MANN [®]	Material - Safety - Data Sheet (MSDS)	No.5	
		Ansmann Lithium-Ion Batteries single cells and multi-cell battery packs	4/7	
8.	Special Protection Informa	ation		
	Ventilation Requirements:	Not necessary under normal conditions. Room ventilation may be required in areas where there are open or leaking batteries.		
	Respiratory Protection:	Not necessary under normal conditions. Avoid exposure to electrolyte fumes from open or leaking battery. In all fire situations, use self-contained breathing apparatus	n	
	Eye Protection:	Not necessary under normal conditions. Wear safety glasses with side shields if handling an open or leaking battery.		
	Hand Protection:	Not necessary under normal conditions. Use neoprene or natural rubber gloves if handling an open or leaking battery		
9.	Physical and Chemical Properties			
	Note: The following points are not applicable unless in case of leaking or damaged batteries with exposed internal components.			
	Appearance:	Cylindrical or prismatic shape		
	Odour:	Odourless (unless in case of damaged product with leaking electrolyte)		
	Flashpoint:	Not applicable		
	Flammability:	Not applicable		
	Relative density:	> 2 g/cm3		
	Solubility (water):	Not applicable unless individual components exposed		
	Solubility (other):	Not applicable		
10.	Stability and Reactivity	d Reactivity		
	Product is stable under conditions described in Section 7.			
	Conditions to avoid:	Heat above 70° or incinerate. Deform. Mutilate. Crush. Pierce. Disassemble. Short circuit. Expose over a long period to humid conditions.		
	Materials to avoid:	Strong mineral acids, alkali solutions, strong oxidising materials and conductive materials		
	Hazardous decomposition products:	HF, CO, CO2		
11.	Toxicological Information			
	Signs & symptoms:	None, unless battery ruptures. In the event of exposure to internal contents, corrosive fumes will be very irritating to skin, eyes and mucous membranes. Overexposure can cause symptoms of non-fibrotic lung injury and membrane irritation.		
	Inhalation:	Lung irritant		
	Skin contact:	Skin irritant		
	Eye contact:	Eye irritant		
	Ingestion:	Tissue damage to throat and gastro-respiratory tract if swallowed		
	Medical conditions generally aggravated by exposure:	In the event of exposure to internal contents, eczema, skin allergies, lung injuries, asthma and other respiratory disorders may occure.		



Ansmann Lithium-Ion Batteries single cells and multi-cell battery packs

5/7

12. **Ecological Information**

Ansmann lithium ion batteries do not contain heavy metals as defined by the European directives 2006/66/EC Article 21.

Mercury has not been "intentionally introduced (as distinguished from mercury that may be incidentally present in other materials)" in the sense of the U.S.A. "Mercury-Containing and Rechargeable Battery Management Act" (May 13, 1996)

The Regulation on MercuryContent Limitation for Batteries promulgated on 1997-12-31 by the China authorities including the State Administration of Light Industry and the State Environmental Protection Administration defines 'low mercury' as 'mercury content by weight in battery as less than 0.025%', and 'mercury free' as mercury content by weight in battery as less than 0.0001%'. And therefore: Ansmann lithium ion batteries belong to the category mercury-free battery (mercury content lower than 0.0001%).

13. **Disposal Considerations**

USA: Lithium-Ion batteries are classified by the federal government as non-hazardous waste and are safe for disposal in the normal municipal waste stream. These batteries, however, do contain recyclable materials and are accepted for recycling by the Rechargeable Battery Recycling Corporation's (RPBC) Battery Recycling Program. Please go to the RPBC website at www.rbrc.org (www.call2recycle.org) for additional information.

In the European Union, manufacturing, handling and disposal of batteries is regulated on the basis of the DIRECTIVE 2006/66/EC OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL of 6 September 2006 on batteries and accumulators and waste batteries and accumulators and repealing Directive 91/157/EEC. Customers find detailed information on disposal in their specific countries using the web site of the European Portable Batteries Association (http://www.epbaeurope.net/legislation national.html)

Importers and users outside EU should consider the local law and rules

In order to avoid short circuit and heating, used lithium ion batteries should never be stored or transported in bulk. Proper measures against short circuit are:

- Storage of batteries in original packaging
- Coverage of the terminals
- Embedding in dry sand

14. **Transport Information**

ADR	
UN-Number:	3480
description	Lithium ion batteries
class:	9
packaging order:	P903
special provision:	188; 230; 310; 348; 376; 377;387; 636
tunnel forbitten code:	E
UN-Number:	3481
description	Lithium ion batteries contained in equipment / packed with equipment
class:	9
packaging order:	P903
special provision:	188; 230; 310; 348; 360; 376; 377; 387; 390; 670
tunnel forbitten code:	E
ΙΑΤΑ	
UN-Number:	3480
description	Lithium ion batteries
class:	9
packaging order:	965
section:	II, IB,IA
special provision:	A88; A99; A154; A164; A183; A201; A206; A213; A331; A334; A802
UN-Number:	3481
description	Lithium ion batteries contained in equipment
class:	9



Ansmann Lithium-Ion Batteries single cells and multi-cell battery packs

No.5

6/7

		single cells and multi-cell battery packs		0/7
	packaging order: section: special provision:	967 II, I A48; A88; A99; A154; A164; A	A181; A185; A206; A213	
	UN-Number: description class:	3481 Lithium ion batteries packed v 9	vith equipment	
	packaging order: section: special provision:	966 II, I A88; A99; A154; A164; A181;	A185; A206; A213	
	IMDG-Code			
	UN-Number: description class:	3480 Lithium ion batteries 9		
packaging order: P903 special provision: 188; 230; 310; 348; 376; 377; 384; 3		384; 387		
	UN-Number: description class:	3481 Lithium ion batteries containe 9	d in equipment / packed with equipment	
	packaging order: special provision:	P903 188; 230; 310; 348; 360; 376;	377; 384; 387; 390	
	existing quality assurance proc	1 st of January 2013 it is necessary to produce both, lithium cells and lithium batteries under an		
	- ADR (2021):		1.7 (e)	
	- IATA (2021, 62 nd edition			
	- IMDG-Code 2021 (Am	endment 40-20): 2.9.4	(5.)	
	Ansmann hereby declare that all lithium cells and batteries of the Ansmann product range are produced according the above named quality assurance program.			
15.	Regulatory Information			
	Regulations specifically applicable to the product: - ACGIH and OSHA: see exposure limits of the internal ingredients of the battery in section 3. - IATA/ICAO (air transportation): UN 3480 or UN 3481 - Transportation within the US-DOT, 49 Code of Federal Regulations (special provision 188 - IMDG (sea transportation) : UN 3480 or UN 3481(special provision 188, 230) REACH regulation (1907/2006/EC) Duty to communicate information on substances in articles (REACH, Article 33): The product contain the following substance of very high concern (SVHC) in a concentration below 0.1wt%: 1,3-propanesultone (CAS 1120-71-4), 0.04wt% Thus, our product fulfill the requirements of REACH annex XVII (limitations)			
l				



for Ansmann Lithium-Ion Batteries single cells and multi-cell battery packs

7/7

16. Other Information

Full text of Hazard Statements referred to under section 3

H225	Highly flammable liquid and vapour
H226	Flammable liquid and vapour
H228	Flammable solid
H261	In contact with water releases flammable gases
H301	Toxic if swallowed
H302	Harmful if swallowed
H314	Causes severe skin burns and eye damage
H317	May cause an allergig skin reaction
H319	Causes serious eye irritation
H330	Fatal if inhaled
H334	May cause allergy or asthma symptoms or breating difficulties if inhaled
H350	May cause cancer
H372	Causes damage to organs
H412	Harmful to aquatic life with long lasting effects

This information has been compiled from sources considered to be dependable and is, to the best of our knowledge and belief, accurate and reliable as of the date compiled. However, no representation, warranty (either expressed or implied) or guarantee is made to the accuracy, reliability or completeness of the information contained herein.

This information relates to the specific materials designated and may not be valid for such material used in combination with any other materials or in any process. It is the user's responsibility to satisfy himself as to the suitability and completeness of this information for his particular use.

Ansmann AG does not accept liability for any loss or damage that may occur, whether direct, indirect, incidental or consequential, from the use of this information. Ansmann AG does not offer warranty against patent infringement.