


Terminal Block

4 Way, 20A

multicomp PRO



Specifications:



Current Rating	: 20A (300V AC)
Minimum Withstanding Insulation Voltage	: 2,000V AC
Insulation Resistance	: > 2,000MW (500V DC)
Operating Temperature	: -40°C to +105°C
Wire range	: 12AWG to 22AWG
Screw torque	: 12lb-inch
Connector Mounting	: Panel
Pitch Spacing	: 9.5mm
No. of Contacts	: 4
Contact Material	: Brass
Contact Plating	: Tin
Terminal Type	: Screw
Wire Area Size Max	: 3.3mm ²
Termination Method	: Vertical

Terminal Block

4 Way, 20A

multicomp **PRO**

Diagram



Dimensions

L	S
55.2	48

Dimensions : Millimetres

Number	Description	Material	Plating/Finish	Colour
1	Insulating Body	PC	-	Black
2	Terminal	Brass	Tin Plated	-
3	Screw	Steel	Ni Plated	

Part Number Table

Description	Part Number
Terminal Block - 4 Way 20A	T64 4WAY

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
Element14.com/multicomp-pro

multicomp **PRO**