


# PRODUCT DATASHEET

## PANEL VALUE 1200x600 TPB 65 W 4000 K WT

PANEL VALUE 1200x600 TPB | Square recessed panel luminaires with TP(B) rated diffuser, 1200 x 600 mm



---

### AREAS OF APPLICATION

- Direct replacement for luminaires with fluorescent lamps
- Offices, conference rooms
- Reception areas, foyers, corridors, elevators
- Suitable for recessed ceiling systems with grid size of 1200 x 600 mm

---

### PRODUCT BENEFITS

- Value for money luminaire
- Low flicker light thanks to special electronic control gear
- External driver for extended flexibility and easy installation
- Emergency lighting possible with LEDVANCE Emergency Conversion Box

---

### PRODUCT FEATURES

- Lifetime (L70/B50): 50,000 h (at 25 °C)
- Extruded aluminum frame
- Polystyrene diffuser (TP(B) rated)



**TECHNICAL DATA**

Electrical data

Nominal wattage	65.00 W
Operating mode	External LED driver
Nominal voltage	220...240 V
Mains frequency	50/60 Hz
Power factor $\lambda$	$\geq 0.95$
Inrush current	13.2 A
Total harmonic distortion	< 20 %
Inrush current time $T_{h50}$	300 $\mu$ s

Luminaire control gear data

ECG - Output ripple current	$\leq 5$ %
Max. no. of lum. on circuit break. B16 A	14
Max. no. of lum. on circuit break. C10 A	14
Max. no. of lum. on circuit break. C16 A	22


Photometrical data

Color temperature	4000 K
Color rendering index Ra	>80
Light color (designation)	Cool White
Luminous flux	5800 lm
Luminous efficacy	90 lm/W
Standard deviation of color matching	5 sdc <sub>m</sub>

Light technical data

Beam angle	90.00 °
------------	---------

Dimensions & weight



<b>Length</b>	1195 mm
<b>Width</b>	595.0 mm
<b>Height</b>	34.0 mm
<b>Product weight</b>	3600.00 g
<b>Mounting width</b>	580.0 mm
<b>Mounting length</b>	1180.0 mm

### Colors & materials

<b>Product color</b>	White
<b>Housing color</b>	White
<b>Body material</b>	Aluminum
<b>Light emitting surface material</b>	Polystyrene

### Temperatures & operating conditions

<b>Ambient temperature range</b>	-10...+45 °C
----------------------------------	--------------

### Lifespan

<b>Number of switching cycles</b>	25000
<b>Lifespan L70/B50 at 25 °C</b>	50000 h
<b>Lifespan L80/B10 at 25 °C</b>	50000 h
<b>Lifespan L90/B10 at 25 °C</b>	50000 h

### Additional product data

<b>Mounting type</b>	Surface/Recessed
<b>Mounting location</b>	Ceiling / Wall
<b>Product remark</b>	Available from November 2019

### Capabilities

<b>Dimmable</b>	No
<b>Type of connection</b>	Screwless terminal
<b>LED module replaceable</b>	Not replaceable

### Certificates & standards

<b>Type of protection</b>	IP20
<b>Protection class</b>	II
<b>Protection class IK (shock resistance)</b>	IK02
<b>Glow Wire Test according to IEC 695-2-1</b>	650 °C
<b>Photobiological safety group EN62778</b>	RG 0
<b>TP rating</b>	TP(b)

---

**EQUIPMENT / ACCESSORIES**

- Accessories for several mounting options available
- External control gear included

---

**LOGISTICAL DATA**

Product code	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Gross weight	Volume
4058075384361	Folding carton box 1	602 mm x 40 mm x 1248 mm	4303.00 g	30.05 dm <sup>3</sup>
4058075384378	Shipping carton box 3	1267 mm x 142 mm x 634 mm	14880.00 g	114.07 dm <sup>3</sup>

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

---

**DISCLAIMER**

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.