

190A.G - HIGH-PERFORMANCE END CUTTERS



Standards :

NF ISO 5748, ISO 5748, DIN ISO 5748, ASME B107.500

Description :

- Cutting edges designed to cleanly cut all types of wire: soft wires and modern materials to a maximum piano wire specification of: - 190A.16G : 2.0mm 210 kg/mm² - 190A.20G : 2.5mm 200 kg/mm² • High Mechanical advantage due to off-set rivet and cutting edge geometry reducing effort.

References :

	B [MM]	C [MM]	D MAXI [MM]	E [MM]	H [MM]	L [MM]	[G]
190A.16G	28	6,5	2,0	11,5	23	160	170
190A.20G	31	7,5	2,5	13,5	29	200	310