

## 187A.G - COMBINATION PLIERS



### Standards :

NF ISO 5746, ISO 5746, DIN ISO 5746, ASME B107.500

### Description :

- Serrated flat and and oval pipe/cable gripping surfaces combined with a high performance cutting edges.
- Cutting edges designed to cleanly cut all types of wire: soft wires and modern materials to a maximum piano wire specification of: - 187A.16G : 1.8mm 215 kg/mm<sup>2</sup> - 187A.18G : 2.0mm 210 kg/mm<sup>2</sup> - 187A.20G : 2.2mm 205 kg/mm<sup>2</sup>
- High Mechanical advantage due to off-set rivet and cutting edge geometry reducing effort.
- High durability carbon alloy steel, with induction hardened cutting edges.
- Mono-Material ergonomic grips maintaining accessibility benefits of classic dip grips, resistant to workshop chemical agents
- Varnish finish to help prevent rusting.

### References :

|  | B [MM] | C [MM] | E [MM] | E1 [MM] | L [MM] | [G] |
|---|--------|--------|--------|---------|--------|-----|
| 187A.16G  | 21     | 34     | 21     | 9,5     | 165    | 195 |
| 187A.20G  | 26     | 42     | 26     | 11,5    | 205    | 300 |
| 187A.18G  | 23     | 36     | 23     | 10,0    | 185    | 225 |