



ATP - PROTWIST® SCREWDRIVERS FOR PHILLIPS® HEAD SCREWS – Round Blades



Description:

- Inline Hardening Process – +100% Tip Life and +100% Bar Strength.
- Handle Material - Softer for more Comfort and still Chemical Resistant.
- Blade " tri-coating " treatment (Zinc-Nickel-Chromium) - 4x Corrosion Resistance.
- Handle 'Channel' - +10% Torque.
- Laser Marking - gives virtually Permanent Marking.
- CNC tip machining - gives better Screw Fit increasing Torque Transfer and Reducing Wear.

References:

	Pozidriv No	d [mm]	d1xL1 [mm]	L [mm]	L2 [mm]	W [g]
ATP0x75	PH0	25	3 x 75	178.0	103	45
ATP1x75	PH1	30	4.5 x 75	184.0	109	73
ATP1x100	PH1	30	4.5 x 100	209.0	109	76
ATP1x250	PH1	30	4.5 x 250	359.0	109	99
ATP2x100	PH2	36	6 x 100	220.0	120	120
ATP2x125	PH2	36	6 x 125	245.0	120	126
ATP2x250	PH2	36	6 x 250	370.0	120	153
ATP2x400	PH2	36	6 x 400	520.0	120	186
ATP3x150	PH3	40	8 x 150	275.0	125	194
ATP4x200	PH4	40	10 x 200	325.0	125	277

NF ISO 8764-1, NF ISO 8764-2, ISO 8764-1, ISO 8764-2, DIN ISO 8764-1, DIN ISO 8764-2, ASME B107.600