



G CJ-KIT-X7-DE-B

**Class2 Automotive AEC-Q200
Qualified Soft Termination**

No	Murata P/N	Size (mm/inch)	TC Code	Rated Voltage	Cap.	Tol.	Thickness (mm)	Qty
1	G CJ188R71H104KA12	1608M/0603	X7R	50Vdc	0.1μF	±10%	0.9max	20
2	G CJ188R71H224KA01	1608M/0603	X7R	50Vdc	0.22μF	±10%	0.9max	20
3	G CJ188R71E105KA01	1608M/0603	X7R	25Vdc	1μF	±10%	0.9max	20
4	G CJ188R70J225KE01	1608M/0603	X7R	6.3Vdc	2.2μF	±10%	0.9max	20
5	G CJ188C70J475KE02	1608M/0603	X7S	6.3Vdc	4.7μF	±10%	1max	20
6	G CJ21BR71H474KA12	2012M/0805	X7R	50Vdc	0.47μF	±10%	1.45max	20
7	G CJ21BR71H105KA01	2012M/0805	X7R	50Vdc	1μF	±10%	1.45max	20
8	G CJ21BC72A105KE02	2012M/0805	X7S	100Vdc	1μF	±10%	1.5max	20
9	G CJ21BR71A225KA01	2012M/0805	X7R	10Vdc	2.2μF	±10%	1.45max	20
10	G CJ21BR71C225KA13	2012M/0805	X7R	16Vdc	2.2μF	±10%	1.45max	20
11	G CJ21BR71E225KA01	2012M/0805	X7R	25Vdc	2.2μF	±10%	1.45max	20
12	G CJ21BR71C475KA01	2012M/0805	X7R	16Vdc	4.7μF	±10%	1.45max	20
13	G CJ21BR71A106KE01	2012M/0805	X7R	10Vdc	10μF	±10%	1.45max	20
14	G CJ21BC71C106KE02	2012M/0805	X7S	16Vdc	10μF	±10%	1.5max	20
15	G CJ31CR71H225KA12	3216M/1206	X7R	50Vdc	2.2μF	±10%	1.9max	20
16	G CJ31CC72A225KE01	3216M/1206	X7S	100Vdc	2.2μF	±10%	1.9max	20
17	G CJ31CR71E475KA12	3216M/1206	X7R	25Vdc	4.7μF	±10%	1.9max	20
18	G CJ31CC71H475KA01	3216M/1206	X7S	50Vdc	4.7μF	±10%	1.9max	20
19	G CJ31CC71E106KA15	3216M/1206	X7S	25Vdc	10μF	±10%	2max	20
20	G CJ31CR70J226KE01	3216M/1206	X7R	6.3Vdc	22μF	±10%	1.9max	20
21	G CJ31CR71A226KE01	3216M/1206	X7R	10Vdc	22μF	±10%	1.9max	20
22	G CJ32DC72A475KE01	3225M/1210	X7S	100Vdc	4.7μF	±10%	2.3max	20
23	G CJ32EC71H106KA01	3225M/1210	X7S	50Vdc	10μF	±10%	2.8max	20
24	G CJ32ER71C226KE01	3225M/1210	X7R	16Vdc	22μF	±10%	2.8max	20
25	G CJ32EC71E226KE02	3225M/1210	X7S	25Vdc	22μF	±10%	2.85max	20
26	G CJ32ER70J476KE01	3225M/1210	X7R	6.3Vdc	47μF	±10%	2.8max	20