



GJM022-KIT-TTOL-DE

01005 High Q Tight Tolerance

No	Murata P/N	Size (mm/inch)	TC Code	Rated Voltage	Cap.	Tol.	Thickness (mm)	Qty
1	GJM0225C1ER20WB01	0402M/01005	COG	25Vdc	0.2pF	±0.05pF	0.22max	50
2	GJM0225C1ER30WB01	0402M/01005	COG	25Vdc	0.3pF	±0.05pF	0.22max	50
3	GJM0225C1ER40WB01	0402M/01005	COG	25Vdc	0.4pF	±0.05pF	0.22max	50
4	GJM0225C1ER50WB01	0402M/01005	COG	25Vdc	0.5pF	±0.05pF	0.22max	50
5	GJM0225C1ER60WB01	0402M/01005	COG	25Vdc	0.6pF	±0.05pF	0.22max	50
6	GJM0225C1ER70WB01	0402M/01005	COG	25Vdc	0.7pF	±0.05pF	0.22max	50
7	GJM0225C1ER80WB01	0402M/01005	COG	25Vdc	0.8pF	±0.05pF	0.22max	50
8	GJM0225C1ER90WB01	0402M/01005	COG	25Vdc	0.9pF	±0.05pF	0.22max	50
9	GJM0225C1E1R0BB01	0402M/01005	COG	25Vdc	1.0pF	±0.1pF	0.22max	50
10	GJM0225C1E1R1BB01	0402M/01005	COG	25Vdc	1.1pF	±0.1pF	0.22max	50
11	GJM0225C1E1R2BB01	0402M/01005	COG	25Vdc	1.2pF	±0.1pF	0.22max	50
12	GJM0225C1E1R3BB01	0402M/01005	COG	25Vdc	1.3pF	±0.1pF	0.22max	50
13	GJM0225C1E1R4BB01	0402M/01005	COG	25Vdc	1.4pF	±0.1pF	0.22max	50
14	GJM0225C1E1R5BB01	0402M/01005	COG	25Vdc	1.5pF	±0.1pF	0.22max	50
15	GJM0225C1E1R6BB01	0402M/01005	COG	25Vdc	1.6pF	±0.1pF	0.22max	50
16	GJM0225C1E1R7BB01	0402M/01005	COG	25Vdc	1.7pF	±0.1pF	0.22max	50
17	GJM0225C1E1R8BB01	0402M/01005	COG	25Vdc	1.8pF	±0.1pF	0.22max	50
18	GJM0225C1E1R9BB01	0402M/01005	COG	25Vdc	1.9pF	±0.1pF	0.22max	50
19	GJM0225C1E2R0BB01	0402M/01005	COG	25Vdc	2.0pF	±0.1pF	0.22max	50
20	GJM0225C1E2R1BB01	0402M/01005	COG	25Vdc	2.1pF	±0.1pF	0.22max	50
21	GJM0225C1E2R2BB01	0402M/01005	COG	25Vdc	2.2pF	±0.1pF	0.22max	50
22	GJM0225C1E2R3BB01	0402M/01005	COG	25Vdc	2.3pF	±0.1pF	0.22max	50
23	GJM0225C1E2R4BB01	0402M/01005	COG	25Vdc	2.4pF	±0.1pF	0.22max	50
24	GJM0225C1E2R5BB01	0402M/01005	COG	25Vdc	2.5pF	±0.1pF	0.22max	50
25	GJM0225C1E2R6BB01	0402M/01005	COG	25Vdc	2.6pF	±0.1pF	0.22max	50
26	GJM0225C1E2R7BB01	0402M/01005	COG	25Vdc	2.7pF	±0.1pF	0.22max	50
27	GJM0225C1E2R8BB01	0402M/01005	COG	25Vdc	2.8pF	±0.1pF	0.22max	50
28	GJM0225C1E2R9BB01	0402M/01005	COG	25Vdc	2.9pF	±0.1pF	0.22max	50
29	GJM0225C1E3R0BB01	0402M/01005	COG	25Vdc	3.0pF	±0.1pF	0.22max	50
30	GJM0225C1E3R1BB01	0402M/01005	COG	25Vdc	3.1pF	±0.1pF	0.22max	50
31	GJM0225C1E3R2BB01	0402M/01005	COG	25Vdc	3.2pF	±0.1pF	0.22max	50
32	GJM0225C1E3R3BB01	0402M/01005	COG	25Vdc	3.3pF	±0.1pF	0.22max	50
33	GJM0225C1E3R4BB01	0402M/01005	COG	25Vdc	3.4pF	±0.1pF	0.22max	50

34	GJM0225C1E3R5BB01	0402M/01005	COG	25Vdc	3.5pF	±0.1pF	0.22max	50
35	GJM0225C1E3R6BB01	0402M/01005	COG	25Vdc	3.6pF	±0.1pF	0.22max	50
36	GJM0225C1E3R7BB01	0402M/01005	COG	25Vdc	3.7pF	±0.1pF	0.22max	50
37	GJM0225C1E3R8BB01	0402M/01005	COG	25Vdc	3.8pF	±0.1pF	0.22max	50
38	GJM0225C1E3R9BB01	0402M/01005	COG	25Vdc	3.9pF	±0.1pF	0.22max	50
39	GJM0225C1E4R0BB01	0402M/01005	COG	25Vdc	4.0pF	±0.1pF	0.22max	50
40	GJM0225C1E4R1BB01	0402M/01005	COG	25Vdc	4.1pF	±0.1pF	0.22max	50
41	GJM0225C1E4R2BB01	0402M/01005	COG	25Vdc	4.2pF	±0.1pF	0.22max	50
42	GJM0225C1E4R3BB01	0402M/01005	COG	25Vdc	4.3pF	±0.1pF	0.22max	50
43	GJM0225C1E4R4BB01	0402M/01005	COG	25Vdc	4.4pF	±0.1pF	0.22max	50
44	GJM0225C1E4R5BB01	0402M/01005	COG	25Vdc	4.5pF	±0.1pF	0.22max	50
45	GJM0225C1E4R6BB01	0402M/01005	COG	25Vdc	4.6pF	±0.1pF	0.22max	50
46	GJM0225C1E4R7BB01	0402M/01005	COG	25Vdc	4.7pF	±0.1pF	0.22max	50
47	GJM0225C1E4R8BB01	0402M/01005	COG	25Vdc	4.8pF	±0.1pF	0.22max	50
48	GJM0225C1E4R9BB01	0402M/01005	COG	25Vdc	4.9pF	±0.1pF	0.22max	50
49	GJM0225C1E5R0BB01	0402M/01005	COG	25Vdc	5.0pF	±0.1pF	0.22max	50
50	GJM0225C1E5R1BB01	0402M/01005	COG	25Vdc	5.1pF	±0.1pF	0.22max	50
51	GJM0225C1E5R6BB01	0402M/01005	COG	25Vdc	5.6pF	±0.1pF	0.22max	50
52	GJM0225C1E6R0BB01	0402M/01005	COG	25Vdc	6.0pF	±0.1pF	0.22max	50
53	GJM0225C1E6R2BB01	0402M/01005	COG	25Vdc	6.2pF	±0.1pF	0.22max	50
54	GJM0225C1E6R8BB01	0402M/01005	COG	25Vdc	6.8pF	±0.1pF	0.22max	50
55	GJM0225C1E7R0BB01	0402M/01005	COG	25Vdc	7.0pF	±0.1pF	0.22max	50
56	GJM0225C1E7R5BB01	0402M/01005	COG	25Vdc	7.5pF	±0.1pF	0.22max	50
57	GJM0225C1E8R0BB01	0402M/01005	COG	25Vdc	8.0pF	±0.1pF	0.22max	50
58	GJM0225C1E8R2BB01	0402M/01005	COG	25Vdc	8.2pF	±0.1pF	0.22max	50
59	GJM0225C1E9R0BB01	0402M/01005	COG	25Vdc	9.0pF	±0.1pF	0.22max	50
60	GJM0225C1E9R1BB01	0402M/01005	COG	25Vdc	9.1pF	±0.1pF	0.22max	50
61	GJM0225C1E100GB01	0402M/01005	COG	25Vdc	10pF	±2%	0.22max	50
62	GJM0225C1E110GB01	0402M/01005	COG	25Vdc	11pF	±2%	0.22max	50
63	GJM0225C1E120GB01	0402M/01005	COG	25Vdc	12pF	±2%	0.22max	50
64	GJM0225C1E130GB01	0402M/01005	COG	25Vdc	13pF	±2%	0.22max	50
65	GJM0225C1E150GB01	0402M/01005	COG	25Vdc	15pF	±2%	0.22max	50
66	GJM0225C1E160GB01	0402M/01005	COG	25Vdc	16pF	±2%	0.22max	50
67	GJM0225C1E180GB01	0402M/01005	COG	25Vdc	18pF	±2%	0.22max	50
68	GJM0225C1E200GB01	0402M/01005	COG	25Vdc	20pF	±2%	0.22max	50
69	GJM0225C1E220GB01	0402M/01005	COG	25Vdc	22pF	±2%	0.22max	50