

## Han® S-HSI w. MC M8-red



Image is for illustration purposes only. Please refer to product description.

Part number	09 93 001 0102
Specification	Han® S-HSI w. MC M8-red
HARTING eCatalogue	<a href="https://b2b.harting.com/09930010102">https://b2b.harting.com/09930010102</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han® S
Type of hood/housing	Screw mounted housing
Description of hood/housing	incl. male contact with M8 bolt termination

### Version

Locking type	Single locking lever
Number of contacts	1
Field of application	Energy Storage Systems

### Technical characteristics

Rated current	200 A
Rated voltage	1,500 V
Rated impulse voltage	8 kV
Pollution degree	2
Insulation resistance	$>10^8 \Omega$
Contact resistance	$\leq 0.3 \text{ m}\Omega$
Tightening torque	11 Nm
Wrench size	9
Limiting temperature	-40 ... +125 °C
Number of relockings	$\geq 500$



Pushing Performance

## Technical characteristics

Degree of protection acc. to IEC 60529	IP40 mated condition IP20 unmated condition (1500 V DC; 1000 V AC)
--	---

## Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
Material (hood/housing)	Polyamide (PA)
Colour (hood/housing)	RAL 3001 (signal red)
Material flammability class acc. to UL 94	V-0

## Specifications and approvals

Specifications	EN 60664-1 IEC 61984
Approvals	UL 1973 UL 4128 UL 9540

## Commercial data

Packaging size	1
Net weight	20 g
Country of origin	China
European customs tariff number	85389099
eCl@ss	27440202 Shell for industrial connectors