

**Productname :** SERVISOL LABEL REMOVER 130 **Creationdate :** 23.04.21 Version : 2.1  
**Ref.Nr.:** UDS000370\_3\_20210423 (EN) **Replaces:** UDS000370\_20170629

**SECTION 1: Identification of the substance/mixture and of the company/undertaking****1.1. Product identifier**

**SERVISOL LABEL REMOVER 130**  
Aerosol

**1.2. Relevant identified uses of the substance or mixture and uses advised against**

Cleaners - Heavy duty

**1.3. Details of the supplier of the safety data sheet**

CRC Industries UK Ltd.  
Wylds Road  
Castlefield Industrial Estate  
TA6 4DD Bridgwater Somerset  
United Kingdom  
Tel.: +44 1278 727200  
Fax.: +44 1278 425644  
E-mail : hse.uk@crcind.com

Subsidiaries		Tel	Fax
CRC Industries Deutschland GmbH	Südring 9, D-76473 Iffezheim	(07229) 303 0	(07229)30 32 66

**1.4. Emergency telephone number**

(+44)(0)1278 72 7200 (office hours)

**SECTION 2: Hazards identification****2.1. Classification of the substance or mixture****Classification according to Regulation (EC) No 1272/2008**

<b>Physical:</b>	Aerosols, category 1 Extremely flammable aerosol. Pressurised container: May burst if heated.
Classification is based on test data.	
<b>Health:</b>	Skin irritation, category 2 Causes skin irritation. Skin sensitization, category 1 May cause an allergic skin reaction. Specific target organ toxicity - single exposure, category 3 May cause drowsiness or dizziness.



<b>Productname :</b>	SERVISOL LABEL REMOVER 130	<b>Creationdate :</b>	23.04.21 Version : 2.1
<b>Ref.Nr.:</b>	UDS000370_3_20210423 (EN)	<b>Replaces:</b>	UDS000370_20170629




Classification based on calculation method.

**Environment:** Hazardous to the aquatic environment, acute category 1  
Very toxic to aquatic life with long lasting effects.

Classification based on calculation method.

## 2.2. Label elements

### Labelling according to Regulation (EC) No 1272/2008

<b>Product identifier:</b>	Contains: Hydrocarbons, C9-C11, n-alkanes, isoalkanes, cyclics, < 2% aromatics Orange, sweet, extract
<b>Hazard pictogram(s):</b>	  
<b>Signal word:</b>	Danger
<b>Hazard statement(s):</b>	H222 : Extremely flammable aerosol. H229 : Pressurised container: May burst if heated. H315 : Causes skin irritation. H317 : May cause an allergic skin reaction. H336 : May cause drowsiness or dizziness. H410 : Very toxic to aquatic life with long lasting effects.
<b>Precautionary statement(s):</b>	P102 : Keep out of reach of children. P210 : Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. P211 : Do not spray on an open flame or other ignition source. P251 : Do not pierce or burn, even after use. P261 : Avoid breathing dust/fume/gas/mist/vapours/spray. P271 : Use only outdoors or in a well-ventilated area. P410/412 : Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F. P501-2 : Dispose of contents/container to an authorised waste collection point.

**Regulation (EC) No 648/2004 on detergents:** aliphatic hydrocarbons > 30 %

## 2.3. Other hazards

No information available

## SECTION 3: Composition/information on ingredients

### 3.1. Substances

Not applicable.

### 3.2. Mixtures

Hazardous ingredient	Registration	CAS-	EC-nr	w/w	Hazard Class and	Hazard statement	Notes
----------------------	--------------	------	-------	-----	------------------	------------------	-------



**Productname :** SERVISOL LABEL REMOVER 130 **Creationdate :** 23.04.21 Version : 2.1  
**Ref.Nr.:** UDS000370\_3\_20210423 (EN) **Replaces:** UDS000370\_20170629

	number	nr.		%	Category		
Hydrocarbons, C9-C11, n-alkanes, isoalkanes, cyclics, < 2% aromatics	01-2119463258-33	-	(919-857-5)	30-60	Flam. Liq. 3, Asp. Tox. 1, STOT SE 3	H226,H304,H336	B,Q
Hydrocarbons,C3-4-rich, petroleum distillate Petroleumgas (1,3-butadiene < 0.1%)	01-2119485926-20	68512-91-4	270-990-9	10-30	Press. Gas, Flam. Gas 1	H280,H220	K,G
Orange, sweet, extract	01-2119493353-35	8028-48-6	232-433-8	10-30	Flam. Liq. 3, Skin Irrit. 2, Skin Sens. 1, Asp. Tox. 1, Aquatic Acute 1, Aquatic Chronic 1	H226,H315,H317,H304,H400,H410	

**Explanation notes**

B : substance with national established workplace exposure limit

G : exempted from the obligation to register in accordance with art.2(7) of REACH Regulation No 1907/2006

K : not classified as carcinogen, less than 0.1% w/w 1,3-butadiene (Einecs-nr. 203-450-8)

Q : The CAS-no is only an indicative identifier to be used outside the EU for global inventory entries.

(\* Explanation phrases : see chapter 16)

**SECTION 4: First aid measures****4.1. Description of first aid measures**

<b>Contact with eyes :</b>	If substance has got into eyes, immediately wash out with plenty of water Seek medical advice
<b>Contact with skin :</b>	Remove contaminated clothing immediately and drench affected skin with plenty of water. Then wash with soap and water Seek medical advice
<b>Inhalation :</b>	IF INHALED: Remove person to fresh air and keep comfortable for breathing. Call a POISON CENTER or doctor/physician if you feel unwell.
<b>Ingestion :</b>	If swallowed do not induce vomiting because of risk of aspiration into the lungs. If aspiration is suspected obtain immediate medical attention

**4.2. Most important symptoms and effects, both acute and delayed**

<b>Inhalation :</b>	Excessive inhalation of solvent vapours may give rise to nausea, headaches and dizziness
<b>Ingestion :</b>	After vomiting of swallowed product aspiration into lungs is likely. Solvents may induce chemical pneumonia. Symptoms : sore throat, abdominal pain, nausea, vomiting
<b>Skin contact :</b>	Irritating to skin May cause sensitisation by skin contact. Symptoms : redness and pain
<b>Eye contact :</b>	May cause irritation. Symptoms : redness and pain

**4.3. Indication of any immediate medical attention and special treatment needed**

<b>General Advice :</b>	If you feel unwell, seek medical advice (show the label where possible) If symptoms persist always call a doctor
-------------------------	---



<b>Productname :</b>	SERVISOL LABEL REMOVER 130	<b>Creationdate :</b>	23.04.21 Version : 2.1
<b>Ref.Nr.:</b>	UDS000370_3_20210423 (EN)	<b>Replaces:</b>	UDS000370_20170629

## SECTION 5: Firefighting measures

### 5.1. Extinguishing media

foam, carbon dioxide or dry agent

### 5.2. Special hazards arising from the substance or mixture

Aerosols may explode if heated above 50°C  
Forms hazardous decomposition products  
CO,CO2

### 5.3. Advice for firefighters

Keep container(s) exposed to fire cool, by spraying with water  
In case of fire, do not breathe fumes

## SECTION 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

Shut off all ignition sources  
Ensure adequate ventilation  
Wear protective gloves/protective clothing/eye protection/face protection.

### 6.2. Environmental precautions

Do not allow to enter public sewers and watercourses

### 6.3. Methods and material for containment and cleaning up

Absorb spillage in suitable inert material

### 6.4. Reference to other sections

For further information see section 8

## SECTION 7: Handling and storage

### 7.1. Precautions for safe handling

Keep away from heat and sources of ignition  
Take precautionary measures against static discharges  
Equipment should be earthed  
Use explosion-proof electrical/ventilating/lighting/.../equipment.  
Use only non-sparking tools.  
Do not breathe aerosols or vapours.  
Ensure adequate ventilation



**Productname :** SERVISOL LABEL REMOVER 130 **Creationdate :** 23.04.21 Version : 2.1  
**Ref.Nr.:** UDS000370\_3\_20210423 (EN) **Replaces:** UDS000370\_20170629

Do not get in eyes, on skin, or on clothing.  
Wear protective gloves/protective clothing/eye protection/face protection.  
Contaminated work clothing should not be allowed out of the workplace.

## 7.2. Conditions for safe storage, including any incompatibilities

Pressurized container : protect from sunlight and do not expose to temperatures exceeding 50°C.  
Keep out of reach of children.

## 7.3. Specific end use(s)

Cleaners - Heavy duty

# SECTION 8: Exposure controls/personal protection

## 8.1. Control parameters

### Exposure limits :

No information available

## 8.2. Exposure controls

<b>Control procedures :</b>	Ensure adequate ventilation Keep away from heat and sources of ignition Take precautionary measures against static discharges
<b>Personal protection :</b>	Take precautions to avoid contact with skin and eyes when handling the product. Ensure adequate ventilation
<b>inhalation :</b>	In case of insufficient ventilation, wear suitable respiratory equipment.
recommended respiratory protection:	Air purifying respirator equipped with organic gas/vapor cartridge (type A)
<b>hands and skin :</b>	When handling the product wear chemical-resistant gloves (standard EN 374). The breakthrough time of the glove should be longer than the total duration of product use. If work lasts longer than the breakthrough time, gloves should be changed part-way through.
Recommended gloves:	Nitrile
<b>eyes :</b>	Wear safety eyewear according to EN 166.
<b>Environmental protection:</b>	Avoid release to the environment. Collect spillage.

# SECTION 9: Physical and chemical properties

## 9.1. Information on basic physical and chemical properties

(for aerosols data for the product without propellant)

**Appearance : physical state :** Propane/butane propelled liquid.  
**colour :** Colorless.  
**odour :** Citrus.



**Productname :** SERVISOL LABEL REMOVER 130 **Creationdate :** 23.04.21 Version : 2.1  
**Ref.Nr.:** UDS000370\_3\_20210423 (EN) **Replaces:** UDS000370\_20170629

pH : Not applicable.  
Boiling point/range : 145 °C  
Flash point : 36 °C  
Evaporation rate : Not available.  
Explosion limits : upper limit : 9.4 %  
lower limit : 0.6 %  
Vapour pressure : Not available.  
Relative density : 0.795 g/cm3 (@ 20°C).  
Solubility in water : Insoluble in water  
Auto-ignition : > 200 °C  
Viscosity : Not available.

## 9.2. Other information

VOC = volatile organic compounds 703 g/l

## SECTION 10: Stability and reactivity

### 10.1. Reactivity

No hazardous reactions known if used for its intended purpose

### 10.2. Chemical stability

Stable

### 10.3. Possibility of hazardous reactions

No hazardous reactions known if used for its intended purpose

### 10.4. Conditions to avoid

Avoid overheating

### 10.5. Incompatible materials

Strong oxidising agent

### 10.6. Hazardous decomposition products

CO,CO2

## SECTION 11: Toxicological information

### 11.1. Information on toxicological effects

acute toxicity: based on available data the classification criteria are not met



**Productname :** SERVISOL LABEL REMOVER 130 **Creationdate :** 23.04.21 Version : 2.1  
**Ref.Nr.:** UDS000370\_3\_20210423 (EN) **Replaces:** UDS000370\_20170629

**skin corrosion/irritation:** Causes skin irritation.  
**serious eye damage/irritation:** based on available data the classification criteria are not met  
**respiratory or skin sensitisation:** May cause an allergic skin reaction.  
**germ cell mutagenicity:** based on available data the classification criteria are not met  
**carcinogenicity:** based on available data the classification criteria are not met  
**toxicity for reproduction:** based on available data the classification criteria are not met  
**STOT-single exposure:** May cause drowsiness or dizziness.  
**STOT repeated exposure:** based on available data the classification criteria are not met  
**aspiration hazard:** based on available data the classification criteria are not met

**Information on likely routes of exposure:**

**Inhalation :** Inhalation of solvent vapours may give rise to nausea, headaches and dizziness  
**Ingestion :** After vomiting of swallowed product aspiration into lungs is likely. Solvents may induce chemical pneumonia.  
**Skin contact :** May cause sensitisation by skin contact.  
**Eye contact :** Irritating to skin  
May cause irritation.

**Toxicological data :**

Hazardous ingredient	CAS-nr.	method	
Hydrocarbons, C9-C11, n-alkanes, isoalkanes, cyclics, < 2% aromatics	-	LD50 oral rat	>5000 mg/kg
		LC50 inhal.rat	4951 mg/m3
		LD50 derm.rabit	>5000 mg/kg

**SECTION 12: Ecological information****12.1. Toxicity**

Hazardous to the aquatic environment, acute category 1  
Very toxic to aquatic life with long lasting effects.

**Ecotoxicological data:**

No information available

**12.2. Persistence and degradability**

No information available

**12.3. Bioaccumulative potential**

No information available



**Productname :** SERVISOL LABEL REMOVER 130 **Creationdate :** 23.04.21 Version : 2.1  
**Ref.Nr.:** UDS000370\_3\_20210423 (EN) **Replaces:** UDS000370\_20170629

**12.4. Mobility in soil**

Insoluble in water

**12.5. Results of PBT and vPvB assessment**

No information available

**12.6. Other adverse effects**

No information available  
GWP (global warming potential): 1

**SECTION 13: Disposal considerations****13.1. Waste treatment methods**

**National regulations :** Disposal should be in accordance with local, state or national legislation

**SECTION 14: Transport information****14.1. UN number**

UN-number : 1950

**14.2. UN proper shipping name**

Proper shipping name: AEROSOLS

**14.3. Transport hazard class(es)**

Class: 2.1  
ADR/RID - Classification code: 5F

**14.4. Packing group**

Packing group: Not applicable.

**14.5. Environmental hazards**

ADR/RID - Environmentally hazardous: No  
IMDG - Marine pollutant: No  
IATA/ICAO - Environmentally hazardous: No

**14.6. Special precautions for user**



<b>Productname :</b>	SERVISOL LABEL REMOVER 130	<b>Creationdate :</b>	23.04.21 Version : 2.1
<b>Ref.Nr.:</b>	UDS000370_3_20210423 (EN)	<b>Replaces:</b>	UDS000370_20170629

ADR/RID - Tunnelcode:	(D)
IMDG - Ems:	F-D, S-U
IATA/ICAO - PAX:	203
IATA/ICAO - CAO	203

**14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code**

Not applicable.

**SECTION 15: Regulatory information****15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture**

The Safety Data Sheet is compiled according to the current European requirements.  
Regulation (EC) No 1907/2006 (REACH)  
Regulation (EC) No 1272/2008 (CLP)  
Dir. 2013/10/EU, 2008/47/EC amendment of the aerosol dispenser directive 75/324/EEC.

**15.2. Chemical safety assessment**

No information available

**SECTION 16: Other information**

\*Explanation hazard statements: H220 : Extremely flammable gas.  
H226 : Flammable liquid and vapour.  
H280 : Contains gas under pressure; may explode if heated.  
H304 : May be fatal if swallowed and enters airways.  
H315 : Causes skin irritation.  
H317 : May cause an allergic skin reaction.  
H336 : May cause drowsiness or dizziness.  
H400 : Very toxic to aquatic life.  
H410 : Very toxic to aquatic life with long lasting effects.

acronyms and synonyms: TWA = time weight average  
STEL = short time exposure limit  
VOC = volatile organic compounds  
PBT = persistent bioaccumulative toxic  
vPvB = very persistent very bioaccumulative

This product should be stored, handled and used in accordance with good industrial hygiene practices and in conformity with any legal regulation.  
The information contained herewith is based on the present state of our knowledge and is intended to describe our products from the point of view of safety requirements. It does not guarantee any specific properties.  
Apart from any fair dealing for purposes of study, research and review of health, safety and environmental risks, no part of these documents may be reproduced by any process without written permission from CRC.

