Note: This datasheet may be out of date.

Please download the latest datasheet of #A914BYW-4R7M=P3 from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en/products/productdetail?partno=%23A914BYW-4R7M%3dP3

#A914BYW-4R7M=P3






















References

Packaging	Specifications	Standard Packing Quantity
=P3	330Embossed Tape	2000

Mass (typ.)		
1 piece	0.138g	



Notices

Rated current (Isat) is specified when the decrease of the initial inductance value at 30%. Rated current (Itemp) is specified when temperature of the inductor is raised 40°C by DC current.

1 of 4

Attention

- 1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2. This datasheet has only typical specifications because there is no space for detailed specifications.
- Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.



Note: This datasheet may be out of date.

Please download the latest datasheet of #A914BYW-4R7M=P3 from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en/products/productdetail?partno=%23A914BYW-4R7M%3dP3

#A914BYW-4R7M=P3



Specifications

L size	5.2mm
W size	5.2mm
T size	2.0mm
Size code inch (mm)	2020 (5252)
Inductance	4.7μH±20%
Inductance Test Frequency	0.1MHz
Rated current (Isat) (Based on Inductance change)	1140mA
Rated current (Itemp) (Based on Temperature rise)	1300mA
Max. of DC resistance	0.087Ω
Operating Temperature Range (Self-temperature rise is included)	-40°C to 85°C
Class of magnetic shield	Ferrite Core
Series	D52LC

2 of 4

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.




#A914BYW-4R7M=P3




Characteristic Data


The charts below may show another part number which shares its characteristics.








#A914BYW-4R7M=P3 |Z|



#A914BYW-4R7M=P3 Q



3 of 4

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering




#A914BYW-4R7M=P3

Note: This datasheet may be out of date.

Please download the latest datasheet of #A914BYW-4R7M=P3 from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en/products/productdetail?partno=%23A914BYW-4R7M%3dP3



#A914BYW-4R7M=P3 Temp. rise

4 of 4

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

