

7-1197423-9 ✓ ACTIVE

Raychem

TE Internal #: 959025-000

Portable Crimp Tools, Commercial Crimp Tooling, Not Releasable,
Not Adjustable, Fixed In Tool, Manual, Crimp Tool

[View on TE.com >](#)



Application Tooling > Portable Crimp Tools



Tool Grade: **Commercial Crimp Tooling**

Ratchet Configuration: **Not Releasable, Not Adjustable**

Die Sets Type: **Fixed In Tool**

Certification: **Cannot be Certified**

Power Type: **Manual**

Features

Other

Crimp Form-Wire Barrel Type	Open Barrel - Other
Tool Grade	Commercial Crimp Tooling
Ratchet Configuration	Not Releasable, Not Adjustable
Die Sets Type	Fixed In Tool
Certification	Cannot be Certified
Power Type	Manual
Tool Type	Crimp Tool

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Out of Scope - excluded from Halogen requirements

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 992013-000
AD-1386-CALIBRATION-GAUGE

Customers Also Bought



TE Part #206126-1
CPC SERIES 2



TE Part #204512-2
RECEIPT ASSY,SZ 1,AMPLIMITE



TE Part #1-1630019-6
Power Resistors: Aluminum Housed, HSA



TE Part #2151017-1
OCEAN_2.0_APPLICATIONATOR-S-048F080F




TE Part #2151024-1
OCEAN_2.0_Applicationator-S-090F130F



TE Part #2151030-1
OCEAN_2.0_APPLICATIONATOR-S-062F110F



TE Part #D369-P66-NS1
369 6 WAY PLUG, CRIMP, SKT



TE Part #2160023004
55A0111-22-2



Documents

Product Drawings

[AD-1377-S-SPEC-CRIMP-TOOL](#)

English

Datasheets & Catalog Pages

[Raychem Application Tooling](#)

English

[Crimp Term Whitepaper-Use the Right Tool 1-1773953-1](#)

English

[CRIMPING WHERE FORM MEETS FUNCTION](#)

English