INDUCTORS

⊗TDK

Inductors for power circuits Wound ferrite VLBU series



VLBU1024660F type

FEATURES

O Large current and lower DCR were achieved by the connecting wire-less structure.

O This is a narrow inductor for multiphase applications.

○ Operating temperature range: -40 to +125°C (including self-temperature rise)

APPLICATION

○ Servers, BTS, VRM, others

PART NUMBER CONSTRUCTION

VLBU	1024660	R07	М	F	
Series name	L×W×H dimensions 10.2x4.6x6.0 mm max.	Inductance (μH)	Inductance tolerance	Internal code	

CHARACTERISTICS SPECIFICATION TABLE

L		Measuring frequency	DC resista	nce	Rated currer	nt*	Part No.
					Isat	Itemp	
(nH)	Tolerance	(kHz)	(m Ω)typ.	Tolerance	(A)typ.	(A)typ.	
70	±20%	100	0.23	±10%	93	70	VLBU1024660R07MF
120	±20%	100	0.23	±10%	55	70	VLBU1024660R12MF
* Dated surrents smaller value of either last ar literan							

* Rated current: smaller value of either lsat or Itemp.

Isat: When based on the inductance change rate (20% below the nominal value, under an environment of 20°C)

Itemp: When based on the temperature increase (temperature increase of 40°C by self heating)

Measurement equipment


Measurement item	Product No.	Manufacturer		
L	IM3536	HIOKI		
DC resistance	RM3545	HIOKI		
Rated current Isat	3260+3265B	Wayne Kerr Electronics		
de Environtent en en en en entre en de service en entre				

* Equivalent measurement equipment may be used.




VLBU1024660F type

L FREQUENCY CHARACTERISTICS



Measurement equipment		
Product No.	Manufacturer	
4294A	Keysight Technologies	
* Equivalent measurement equipment may be used.		

■ INDUCTANCE VS. DC BIAS CHARACTERISTICS





A Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use. (2/4) Please note that the contents may change without any prior notice due to reasons such as upgrading.

20200313

VLBU1024660F type


SHAPE & DIMENSIONS





Dimensions in mm

PACKAGING STYLE




Dimensions in mm

11.5±0.1 1.75±0.1

(6.3)


RECOMMENDED LAND PATTERN



Dimensions in mm

RECOMMENDED REFLOW PROFILE





Туре	А	В	K	

(10.5)

PACKAGE QUANTITY

VLBU1024660F

TAPE DIMENSIONS


Package quantity	600 pcs/reel

(4.8)

TEMPERATURE RANGE, INDIVIDUAL WEIGHT

Operating temperature range*	Storage temperature range**	Individual weight	
-40 to +125 °C -40 to +125 °C 1.16 g			
* Operating temperature range includes self-temperature rise.			

** The storage temperature range is for after the assembly.



A Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use. Please note that the contents may change without any prior notice due to reasons such as upgrading. (3/4)

20200313

inductor_commercial_power_vlbu1024660f_en.

REMINDERS FOR USING THESE PRODUCTS

Before using these products, be sure to request the delivery specifications.

SAFETY REMINDERS

Please pay sufficient attention to the warnings for safe designing when using this products.

A REM					
 The storage period is within 6 months. Be sure to follow the storage conditions (temperature: 5 to 30°C, humidity: 10 to 75% RH o less). If the storage period elapses, the soldering of the terminal electrodes may deteriorate. 					
	Do not use or store in locations where there are conditions such as gas corrosion (salt, acid, alkali, etc.).				
	guo concolon (car, acia, anan, oto.).				
 Before soldering, be sure to preheat components. The preheating temperature should be set so that the temperature does not exceed 150°C. 	e difference between the solder temperature and chip temperature				
Soldering corrections after mounting should be within the range of the conditions determined in the specifications. If overheated, a short circuit, performance deterioration, or lifespan shortening may occur.					
When embedding a printed circuit board where a chip is mounted to a set, be sure that residual stress is not given to the chip due to the overall distortion of the printed circuit board and partial distortion such as at screw tightening portions.					
Self heating (temperature increase) occurs when the power is turned ON, so the tolerance should be sufficient for the set thermal design.					
 Carefully lay out the coil for the circuit board design of the non-mag A malfunction may occur due to magnetic interference. 	netic shield type.				
\bigcirc Use a wrist band to discharge static electricity in your body through	the grounding wire.				
\bigcirc Do not expose the products to magnets or magnetic fields.					
\bigcirc Do not use for a purpose outside of the contents regulated in the definition of the contents regulated in the definition of the content	elivery specifications.				
ment, industrial robots) under a normal operation and use condition The products are not designed or warranted to meet the requirement ity require a more stringent level of safety or reliability, or whose fait person or property.	nent, personal equipment, office equipment, measurement equip-				
 (1) Aerospace/aviation equipment (2) Transportation equipment (cars, electric trains, ships, etc.) (3) Medical equipment (4) Power-generation control equipment (5) Atomic energy-related equipment (6) Seabed equipment (7) Transportation control equipment When designing your equipment even for general-purpose application tection circuit/device or providing backup circuits in your equipment. 	 (8) Public information-processing equipment (9) Military equipment (10) Electric heating apparatus, burning equipment (11) Disaster prevention/crime prevention equipment (12) Safety equipment (13) Other applications that are not considered general-purpose applications s, you are kindly requested to take into consideration securing pro- 				

A Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use. (4/4) Please note that the contents may change without any prior notice due to reasons such as upgrading.