



# Surface Mount Technology Prototyping Eurocard

multicomp **PRO**



RoHS  
Compliant

## Description

The Oktapad® Surface Mount Technology (SMT) series of Prototyping Eurocards, comprises 3U eurocards - single height, single and double sided, which have been developed to enable the introduction of the Wiring Technique to Surface Mount Technology (SMT). The circuit boards have been designed as experimental development boards, to combine the assembly and wiring of Surface Mount Devices (SMD's) with conventional components. All circuit boards contain popular Surface Mount Device (SMD) footprints with fan-outs to easy-to-wire solder pads. The single height, double sided boards repeat the SMT pattern on both sides. The colander ground plane covers the remaining component side copper pad or strip sections. There are fixing holes to attach a 'piggy-back' board, should the need arise.

## Features

- Combined with Stripboard format
- Single height, double sided PCB or PWB
- Facilitates wiring of Surface Mount Devices (SMDs) and conventional devices
- Silkscreen reference component side
- Popular SMD footprints
- SMD leads fan out to easy-to-wire solder pads
- SMD Pattern both sides
- Colander ground plane covers remaining component side
- Hole matrix on 2.54mm × 2.54mm
- Hole size 1.02mm
- Provision for 'piggy back' board – 4 x fixing holes
- DIN 41612 connector mounting holes at one end – 32/64/96 way
- Material epoxy glass or FR4
- Board thickness 1.6mm
- Connector pattern to DIN41612
- Copper Thickness 1oz/ft<sup>2</sup> or 35 microns or 305g/m<sup>2</sup>
- Compatible DIN 41494
- Protective Coating OSP - organic solderability preservatives (anti tarnish)

## Part Number Table

Description	Part Number
Single Height Single Sided Eurocard, 3U – 100mm × 160mm Stripboard Format	MP005898

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro  
Farnell.com/multicomp-pro  
Element14.com/multicomp-pro

multicomp **PRO**