

## C4AQPLU4330M19J

C4AQ M, Film, Metallized Polypropylene, Automotive DC Link, 3.3 uF, 5%, 1200 VDC, 85°C, Lead Spacing = 27.5mm



Click [here](#) for the 3D model.

### Dimensions

L	32mm +0.5/-0.7mm
H	19mm +0.2/-0.7mm
T	31mm +0.3/-0.7mm
S	27.5mm +/-0.4mm
LL	6mm +0/-2mm
F	0.8mm +/-0.05mm

### Packaging Specifications

Packaging	Bulk, Box
Packaging Quantity	80

### General Information

Series	C4AQ M
Dielectric	Metallized Polypropylene
Style	Radial
RoHS	Yes
Lead	Wire Leads
Qualifications	AEC-Q200, IEC61071, EN61071, VDE0560
AEC-Q200	Yes
Miscellaneous	Rth = 30 C/W.

### Specifications

Capacitance	3.3 uF
Capacitance Tolerance	5%
Voltage DC	1200 VDC
Temperature Range	-55/+105°C
Rated Temperature	85°C
Dissipation Factor	0.02% (10 kHz 25C)
Insulation Resistance	9.1 MOhms
Max dV/dt	90 V/us
Resistance	10.5 mOhms (10kHz 70C)
Ripple Current	9.1 Amps Irms (10kHz 70C), 297 Amps Ipk
Inductance	16 nH