


Date revision	symbol	Kai	Revised	Record	Thing	Revised No.	Design	Review	Approval
2015. 5.27		New number				GK2013-000-50	Kobayashi Ito		



■ Finish

1. 1. Female

Electric pressure resistance: AC900V, 1 minute
 Insulation resistance: DC500V, 1000MΩ or more
 Contact resistance: 1A or less, 8mΩ or less

2. 2. Samadhi Case

Den Pressure: AC300V (DC420V)
 Den Flow: 2A

3. 3. Wire connection hole diameter: φ0.8 mm

4. Wire connection method: Soldering


5. table Show: PRC05 ... TMW

6. Compatible cable finished outer diameter range

Code ⑩ Sleeve	cable	Compatible cable
	Introductory port size	Finished outer diameter range
At the time of application	φ4.0	φ2.8-φ3.8
When not applied	φ5.2	φ4.0-φ5.0

Soldering side Seen more

Contact symbol (3/1)



Note

The ▽ mark in the figure indicates the connector guide position.

Reference diagram
'18.11.22
Engineering Department

12	Special set screw with slip	Steel	Nickel plating 1	
11	sleeve	Vinyl chloride-1		Attachments
Ten	Phillips pan head machine screw	Brass	Nickel plating 2	
9	Rear shell	Brass	Nickel plating 1	
8 #	22S socket contact	Phosphor bronze	nickel base gold plating 3	
7	Ferrule	Brass	Nickel plating 1	
6	F type rear insulator	PPS resin-1		
5	F type front insulator	PPS resin-1		
Four	spring	Steel	Nickel plating 1	
	gasket	Silicon rubber-1		
2	Slide ring	Brass	Nickel plating 1	
1	Insert shell	Brass	Nickel plating 1	

2015. 5.27	G K2 013-000-50								
From date	line	Record	Thing	No.	Design and technical inspection	Approval name	EPRC05-P3F		
1	2/1	mm	three	Horn					
Edition	Shaku	Degree	Rank	Law			Figure number	1	
Tajimi Electric Co., Ltd.					2015: 5:27	2015: 5:27	2015: 6:11	2015: 6:17	EPRC05-1003 1