

Han 1A-M12-f D-coded, latch



Image is for illustration purposes only. Please refer to product description.

Part number	09 10 004 3101
Specification	Han 1A-M12-f D-coded, latch
HARTING eCatalogue	https://b2b.harting.com/09100043101

Identification

Category	Inserts
Series	Han® 1A

Version

Termination method	Crimp termination
Gender	Female
Locking type	Snap-in latches
Size	1 A
Shielding	With cable tie
Number of contacts	4
further contacts	+ shielding

Details	<p>Please order crimp contacts separately. Order separately the hoods/housings for an IP65 performance. Contact insert not compatible with 09 10 000 0800 (bulkhead mounted housing, angled)</p>
Details	<p>A Han® 1A configuration that only consists of inserts (with or without strain relief, 09 10 000 5300) is an unenclosed connector according to IEC 61984. In this case protection against electric shock must be provided by the installation methods of the user.</p> <p>Contact inserts must not be coupled or decoupled under electrical load. Contact inserts must not be powered-up in the un-mated condition.</p>

Technical characteristics

Conductor cross-section	0.13 ... 0.82 mm ²
Rated current	4 A



Pushing Performance

Technical characteristics

Rated voltage	48 V AC 60 V DC
Rated impulse voltage	1.5 kV
Pollution degree	3
Transmission characteristics	Cat. 5 Class D up to 100 MHz
Data rate	100 Mbit/s
Insulation resistance	$>10^8 \Omega$
Limiting temperature	-30 ... +90 °C
Mating cycles	≥ 100
Degree of protection acc. to IEC 60529	IP20

Material properties

Material (insert)	Polyamide (PA)
Colour (insert)	RAL 9005 (jet black)
Material (seal)	NBR
Colour (seal)	Black
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

Specifications and approvals

Specifications	EN 45545-2 R22: HL1, HL2, HL3
	EN 45545-2 R23: HL1, HL2, HL3
	EN 45545-2 R24: HL1, HL2, HL3
	IEC 61373 Category 1 Class B
	EN 60664-1
	IEC 61984
Approvals	DNV GL



Pushing Performance

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076
	CSA-C22.2 No. 182.3 ECBT8.E235076
	Please contact your local HARTING subsidiary for further information.

Commercial data

Packaging size	1
Net weight	30 g
Country of origin	Romania
European customs tariff number	85366990
eCl@ss	27440205 Contact insert for industrial connectors