



### TECHNICAL INFORMATION

Watts:	10
Lumens:	720
Shape:	Round
Input Power:	AC:200-240V, 50/60Hz
Long Life:	30,000 Hours
Unit Color:	White
Body Type:	PC
LED Chip Type:	SMD-Samsung Chip
CRI:	>80
Operation Temperature:	-20°C to +45°C
Dimmable:	No
Beam Angle:	120°
Color:	4000K
Dimension:	Ø260x90mm
Sensor Type:	Microwave
Detection Distance:	3-6m


### BULKHEAD SENSOR+EMERGENCY | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide extended multi-year warranty on our products, as well as detailed support.

*One brand, endless solutions..*

SKU: 817 - 930 940

[View more details](#)



IP65  
RATING



3 YEAR  
WARRANTY



SAVE UP TO  
85%  
ENERGY

### FEATURES

- Fitted with high efficiency Samsung LED Chips that offer up to 85% in energy savings
- These IP65 LED bulkheads are equipped with Ni-Cad batteries that automatically charges while in use.
- (3) hrs on emergency situations - Green LED Charging indicator
- Including battery protection circuit & inhibiting mode
- Designed with Microwave sensor featuring Corridor function, day light sensor, dimmable function and many more
- 100% PC for endurance & durability - Quick connector for easy wiring
- Suitable for open areas constantly exposed to dust and moisture like parking lots, corridors, airports, and malls

### PACKAGING

Gross Weight (Kgs): 1.236  
Unit CBM: 0.00905  
Dimension: Ø260x90mm

### MASTER BOX PACKAGING

Box Qty: 10  
Length (Box) mm: 280  
Width (Box) mm: 100  
Height (Box) mm: 280

### LISTING DETAILS

Commodity Code: 9405403990  
EanCode: 3800157637770

CE/EMC CE/LVD

