## Plug, SMA Solder, RG405/U





## **Specifications:**

Connector Type : SMA Coaxial
Body Style : Straight Plug
Coaxial Termination : Solder
Impedance : 50Ω
Frequency Max. : DC-18 GHz


RG Cable Type : RG-405, 0.085" Semi-Rigid

Contact Plating : Gold

Bodies : Brass per JIS-C3604. Centre Contact : Brass per JIS-C3604.


Insulation : PTFE per ASTM D1457 and ASTM D1710.


Connector interface per MIL-STD-348A. Part to be clean and free of burrs





Description	Material	Finish
Shell	Brass	Gold 3µ" Min.
Gasket	Silicone	
Washer	Stainless Steel	None
Insulation	PTFE	
Body	Brass	Gold 3μ" Min.
Centre Contact		Gold 50µ" Min.





**Stripping Dimension** 

## **Part Number Table**

Description	Part Number
Plug, SMA, Solder, RG405/U	MP-19-55V-3-TGG

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

