

FM Series

Miniature Toroidal - Single Primary

multicomp PRO



Description

A high quality range of miniature open style toroidal transformers with flying leads. Featuring a single primary winding tapped at 115 and 230V 50/60Hz, and dual secondary windings. Secondary windings can be connected in series or parallel or used independently.

Features

- High quality construction.
- Low radiated magnetic field, suitable for sensitive electronics.
- Double insulated primary leads.
- Resin filled centre with M4 clear mounting hole.
- Flexible lead outs can be trimmed to any length without the need of enamel removal.
- Suitable for use in low power equipment.
- Designed, tested and manufactured in accordance with EN60742, EN60065 and EN60950.
- 100% electrical and flash tested.

Specification Table

Load (VA)	Regulation % typical	Iron Loss Watts	Copper Loss Watts	Temperature rise (°C)	Efficiency % typical	Diameter	Height	Weight (kg)	Part Number
1.6	21	0.09	0.4	10	76%	42	23	0.13	MCFM16/07
									MCFM16/09
									MCFM16/12
									MCFM16/15
									MCFM16/22
3.2	20	0.09	0.8	16	79%	43	24	0.14	MCFM32/07
									MCFM32/09
									MCFM32/12
									MCFM32/15
									MCFM32/18
5	18	0.11	1.1	18	81%	50	24	0.17	MCFM50/07
									MCFM50/09
									MCFM50/12
									MCFM50/15
									MCFM50/18
									MCFM50/22
7	19	0.13	1.6	25	80%	51	24	0.19	MCFM70/07
									MCFM70/09

Dimensions : Millimetres

Newark.com/multicomp-pro
 Farnell.com/multicomp-pro
 Element14.com/multicomp-pro

multicomp PRO

FM Series

Miniature Toroidal - Single Primary

multicomp PRO

Load (VA)	Regulation % typical	Iron Loss Watts	Copper Loss Watts	Temperature rise (°C)	Efficiency % typical	Diameter	Height	Weight (kg)	Part Number
7	19	0.13	1.6	25	80%	51	24	0.19	MCFM70/12
									MCFM70/15
									MCFM70/18
									MCFM70/22

Figures given above are maximums for any given VA

Dimensions : Millimetres

Maximum ambient temperature 40°C.

Overall temperature rating Class A (105°C).

Secondary voltage tolerance $\pm 1\%$ at nominal input and full resistive load.

No mounting screw supplied.

All leads 150mm long, stripped and tinned for last 6.0mm.

Note: Under no circumstances should both ends of any fixing bolt be allowed to come simultaneously in contact with metal chassis or framework so that an electrical path is formed through the bolt in the centre of the transformer via the external framework. This would constitute a shorted turn and would cause irreparable damage.

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
 Farnell.com/multicomp-pro
 Element14.com/multicomp-pro

multicomp PRO