



## Specifications:

Material	: Low Density Polyethylene
Reel Length	: 10m
Max. Operating Temperature	: +70°C
Melting Point (LDPE)	: 113°C

## Part Number Table

Description	Nominal Bore Diameter	Part Number
Spiral Wrap, Natural, 10m, 4-25mm	3.2	KS6N
Spiral Wrap, Natural, 10m, 7.5-30mm	7.5	KS10N
Spiral Wrap, Natural, 10m, 12-35mm	12	KS15N
Spiral Wrap, Natural, 10m, 15-50mm	15	KS19N
Spiral Wrap, Natural, 10m, 20-10mm	20	KS24N
Spiral Wrap, Black, 10m, 4-25mm	3.2	KSR6BK
Spiral Wrap, Black, 10m, 7.5-30mm	7.5	KSR10BK
Spiral Wrap, Black, 10m, 12-35mm	12	KSR15BK
Spiral Wrap, Black, 10m, 15-50mm	15	KSR19BK
Spiral Wrap, Black, 10m, 20-10mm	20	KSR24BK

Dimensions : Millimetres

**Important Notice** : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-POWER is the registered trademark of Premier Farnell Limited 2019.