

## har-flex hy st F 9.05 8+36 THR PL1 200pc




Image is for illustration purposes only. Please refer to product description.

Part number	15 82 836 2701 000
Specification	har-flex hy st F 9.05 8+36 THR PL1 200pc
HARTING eCatalogue	<a href="https://b2b.harting.com/15828362701000">https://b2b.harting.com/15828362701000</a>

### Identification

Category	Connectors
Series	har-flex®
Identification	Hybrid
Element	Female connector
Description of the contact	Straight
Features	Termination method of power contacts: THR

### Version

Termination method	Reflow soldering termination (SMT)
Connection type	Motherboard to daughtercard Mezzanine
Number of contacts	44
Number of signal contacts	36
Number of power contacts	8
Performance level	1
Pack contents	200 pieces on reel

### Technical characteristics

Contact spacing (mating side)	1.27 mm
	2.54 mm
Stacking height	9.05 mm
Rated voltage	acc. to IEC 60664-1
Rated voltage	50 V AC
	120 V DC



Pushing Performance

## Technical characteristics

Rated impulse voltage	1.5 kV
Pollution degree	2
Clearance distance	≥0.4 mm Signal contacts
	≥0.94 mm Power contacts
	≥0.7 mm Signal to power contacts
Creepage distance	≥0.4 mm PCB: Signal contacts
	≥0.94 mm PCB: Power contacts
	≥0.7 mm PCB: Signal to power contacts
	≥0.4 mm Connector: Signal contacts
	≥1.89 mm Connector: Power contacts
	≥2.09 mm Connector: Signal to power contacts
Insulation resistance	>10 <sup>10</sup> Ω
Contact resistance	≤25 mΩ
Limiting temperature	-55 ... +125 °C
Mating cycles	≥500
Test voltage U <sub>r.m.s.</sub>	0.5 kV Signal
	0.84 kV Signal / Power
	0.84 kV Power / Power
Isolation group	IIIa (175 ≤ CTI < 400)
Moisture Sensitivity Level (MSL)	1 acc. to ECA/IPC/JEDEC J-STD-020D
Process Sensitivity Level (PSL)	R0 acc. to ECA/IPC/JEDEC J-STD-020D
Coplanarity of contacts	0.12 mm

## Material properties

Material (insert)	Liquid crystal polymer (LCP)
Colour (insert)	Black
Material (contacts)	Copper alloy
Surface (contacts)	Au over Pd/Ni Mating side
	Tin plated Termination side
Material flammability class acc. to UL 94	V-0

## Commercial data


Packaging size	1
Country of origin	China
European customs tariff number	85366990
eCl@ss	27460201 PCB connector (board connector)



Pushing Performance

Current carrying capacity

The current carrying capacity of the connectors is limited by the thermal load capability of the contact element material including the connections and the insulating parts. The derating curve is therefore valid for currents which flow constantly (non-intermittent) through each contact element of the connector evenly, without exceeding the allowed maximum temperature. Measuring and testing techniques acc. to IEC 60512-5-2



Derating curve 80%