


Part Number: 1905X25X

| Type | Size | Rating | Description |
|------|------|--------|------------------------------|
| LED | M8 | 12Vdc | LED Recessed Panel Indicator |

Dimensions (mm)



| Part # | Colour | Current (mA) | Intensity (mcd) |
|----------|--------|--------------|-----------------|
| 1905X253 | Red | 25 | 60 |
| 1905X251 | Green | 25 | 50 |
| 1905X252 | Yellow | 25 | 50 |
| 1905X257 | Blue | 20 | 90 |
| 1905X25W | White | 7 | 800 |

Bezel types - X=0 satin chrome / X=1 black chrome / X=2 matt chrome

Notes:

- 1 Electrical & optical data are measured at an ambient temperature of 25°C
- 2 Luminous intensity at DC
- 3 Storage temperature -25 °C to +80°C
- 4 Application temperature -20 °C to +60°C
- 5 Due to component tolerances, colour temperature variations may be observed
- 6 The terminals are not qualified for soldering
- 7 Sealed to IP67 above panel when supplied gasket used
- 8 The plastic(polycarbonate) has limited chemical resistance
- 9 RoHS & REACH SVHC compliant