


Part Number: G502

Type	Size	Rating	Description
Incandescent	G11	6.5V 300mA	G-3½ Miniature Bayonet Lamp



Dimensions in millimetres

TEST VOLTS	CURRENT (mA)			LIGHT OUTPUT (Lm)			LIFE Hours
	Min.	Nom.	Max.	Min.	Nom.	Max.	
6.5	270	300	330	10	12	14	4,000

Notes:

- 1 **Base Type** BA9s/13 Nickel plated brass in accordance with BS EN 60061-1
- 2 **Filament Shape** C-2R
- 3 **Lamp Marking** CML 6.5V 300mA
- 4 **Bead colour** White or clear
- 5 **Environmental** RoHS & REACH SVHC compliant