

IDEAL TEST & MEASUREMENT CATALOG





For over 90 years, IDEAL INDUSTRIES, INC. has been enhancing the productivity and safety of electrician's who test, measure, or troubleshoot electrical systems. In 2021 we released a new line of testers with the professional electrician in mind. See our new additions in this catalog.

CIRCUIT TRACERS1 - 3
CIRCUIT BREAKER FINDERS4 - 9
CIRCUIT ANALYZER6 - 7
CLAMP / FORK METERS8 - 13
Clamp Meters
DIGITAL MULTIMETERS14 - 17
VOLTAGE / CONTINUITY TESTERS18 - 19
RECEPTACLE TESTERS 20 - 2

NON-CONTACT VOLTAGE TESTERS	22 - 24
INFRARED THERMOMETERS	S 25
SPECIALTY TESTERS	
3-Phase	26 - 27
Insulation	26 - 27
Ground Resistance	
Digital Light Meter	26 - 27
ACCESSORIES	
Test Leads	28 - 29
Carrying Cases	30

Replacement Parts......31



Scan this QR code with your smartphone to learn more about the new line.

SURETRACETM CIRCUIT TRACER

Your IDEAL troubleshooting solution. Designed **to find** everything, while saving you time and money. Scan this QR code with your smart-phone to see a video and learn more about the testers.



KIT OPTIONS AND PARTS

KIT OPTIONS	61-959 Receiver with Super-Bright OLED Rotating Display (90° increments) and inductive clamp and battery pack	61-957 Receiver with Super-Bright OLED Rotating Display (90° increments)	61-955 Receiver with Rotating Red LED Display (180° increments)
INDIVIDUAL COMPONENTS	61-959	61-957	61-955
RC-959 Receiver with Super-Bright OLED Display	✓	✓	<u> </u>
RC-955 Receiver with Red LED Display	_	_	~
TR-955 Transmitter Rated for Use on Circuits from 0 to 600V AC/DC	~	~	~
IC-958 BP-958 Inductive Clamp and Battery Pack For use on 0 to 120V circuits carrying less than 5 Amps.	✓	_	_
TL-956 Test Lead Set	✓	✓	~
CR-959 Cradle for RC-959 and RC-955 Receivers	Sold Separately	Sold Separately	Sold Separately

CIRCUIT TRACER RECEIVERS FEATURES



0-600V AC or DC Lead Set included.

CIRCUIT TRACER TRANSMITTER FEATURES



7 CertainCircuit™

After the correct breaker has been identified and tripped, the transmitter senses the loss of power and sends a different signal back to the receiver at the panel to give the user confidence that the right circuit has been de-energized.



Energized



De-energized

Traces de-energized circuits



Inductive Clamp for when direct contact with alligator clips is not possible



TR-955



Inductive Clamp & Battery Pack (For use on circuits carrying up to 120V AC w/less than 5 Amps) IC-958 | BP-958

Cradle

(For use on RC-955 & RC-959 Receivers) **CR-959**









Tracer Test Lead Set TL-956 (includes the following)

- 1. 3 Ft. Lead Adapter for Transmitter (set of 2)
- 2. 25 ft. Lead Adapter for Transmitter
- 3. Alligator Clips (set of 2)
- 4. Blade Prongs
- 5. Prong for Lead Adapters
- 6. Outlet Plug Adapter for Transmitter

CIRCUIT BREAKER

FINDERS

Scan this QR code with your smartphone to see a video and learn more about the testers.



FEATURES




















TL-532A Test Lead & Adapter Kit

CIRCUIT BREAKER FINDER SPECIFICATIONS



CIRCUIT BREAKER FINDER SELECTION GUIDE	Mario Commission of the Commis	
TRANSMITTER FEATURES	61-534	61-532
CAT Rating (Safety)	CAT II 300V	CAT II 300V
Listing	UL 1436	UL 1436
Line Voltage	Line Powered (120V AC only)	Line Powered (120V AC only)
Supply Frequency	47-63Hz	47-63Hz
Weight	50g (approx.)	50g (approx.)
Pulse Amplitude	18A (approx.) @ 120V	18A (approx.) @ 120V
Pulse Rate	4mS every 17ms (@ 60Hz)	4mS every 17ms (@ 60Hz)
Power Consumption	200mW max. @ 120V AC	200mW max. @ 120V
Operating Temperature	32° - 122°F (0 to 50°C)	32° - 122°F (0 to 50°C)
GFCI	✓	_
Polarity Indication	✓	_
RECEIVER FEATURES		
Visual and Audible Indicators	✓	✓
Low Battery Indication	✓	✓
Auto Power Off (after 10 mins. of no activity)	✓	✓
Battery Type (included)	9V	9V
Weight	0.2 lbs. (w/o battery)	0.2 lbs. (w/o battery)
Warranty	2-Year*	2-Year*
ACCESSORIES		
Light Socket and 3-prong to 2-prong Adapters, Alligator Clips	TL-532A	TL-532A

SURETEST®CIRCUIT ANALYZER

FEATURES

Scan this QR code with your smartphone to see a video and learn more about the tester.





61-164Circuit Analyzer







True RMS Line Voltage



Displays Voltage Drop at 12, 15 & 20 Amps



Displays Impedance of hot, neutral & ground



Displays H N G polarity



Detects and Displays false or "bootleg" ground



Displays neutral to ground voltage



Trips GFCI at 6mA or 30mA





Estimated Load on Line in Amps

CIRCUIT ANALYZER SPECIFICATIONS

SURETEST® CIRCUIT ANALYZER SPECIFICATIONS







	61-164		
	Description	Range & Resolution	Accuracy
TRANSMITTER FEATURES			
CAT Rating (Safety)	CAT III 300V	_	
Listing	cULus	_	
AC Voltage (Note: The 61-164 is protected to 265V AC but should be unplugged immediately if plugged into a mis-wired outlet. It is intended for use on 120V AC circuits only.) Do not press any buttons.	_	85.0 - 265.0 VAC (Unplug if 240V AC is displayed and correct wiring.)	1.0%
Frequency	_	45.0 - 65.0 Hz	1.0%
Impedance	_	0.00 - 3.00 Ω	5.0%
Neutral Ground Voltage	_	0.0 - 24.0V AC	2.0%
% Voltage Drop 12A, 15A, 20A Load Tests	_	0.1% - 50.0%	5.0%
GFCI mA Trip Level & Time to Trip in Milliseconds	_	6.0 - 9.0 mA 0.0 - 6500 mS	2.0%
Warranty	2-Year*	_	
ACCESSORIES		Part No.	
Ground Continuity Adapter (For checking grounding of cabinets, etc.)	etc.) 61-175		
Isolated Ground Adapter (For determining whether receptacle has an isolated ground.)	an 61-176		
Alligator Clip Adapter (For connection to circuits other than outlets.)	61-183		
1' Extension Cord (included)	61-182		
Nylon Carrying Case (included)		61-179	

IMPORTANT: This circuit analyzer is intended for use by qualified electricians. Follow the NFPA 70E Standard for Electrical Safety in the Workplace when using this tester. Always consult the instruction manual provided with the tester for operational limitations and procedures associated with a specific tester.



61-183Alligator Clip Adapter for 61-164
Circuit Analyzer



61-175Ground Continuity
Adapter for 61-164
Circuit Analyzer



61-176Isolated Ground
Adapter for 61-164
Circuit Analyzer



61-1821' Extension Cord for 61-164
Circuit Analyzer

CLAMP/FORK METER VS. MULTIMETER



Safety - A fork meter allows you to measure AC or DC current (depending on the model) by positioning the fork around a conductor, which is much safer than making direct contact with a live circuit.

Productivity - During a measurement, it is not necessary to shut off the circuit carrying current, which improves productivity.

Limited to 200A AC/DC Measurement

No Fuse Protection required



Safety - A clamp meter allows you to measure AC or DC current (depending on the model) by positioning the clamp jaw around a conductor, which is much safer than making direct contact with a live circuit.

Productivity - During a measurement, it is not necessary to shut off the circuit carrying current, which improves productivity. This allows isolation of a conductor being tested in a bundle of conductors.

Limited to 2000A AC/DC Measurement (Hard Clamp)

No Fuse Protection required

Multimeters measure current differently than a fork or clamp meter. To measures current with a multimeter:


• You must insert the multimeter into the circuit to get the current to flow THROUGH the meter and are making direct contact with the live circuit.

To properly conduct a current measurement in accordance with Electrical Safety-related Work Practices (ESWP) you must:

- de-energize the circuit, disconnect the circuit, insert the meter into the circuit, re-energize the circuit to test current
- AND THEN... repeat the whole process again to "remove" the meter from the circuit after the test.

Limited to 10A AC/DC Measurement

Fuse Protection required (due to current pass-through)





FORK METERS



61-415 | 61-405



Patented TightSight®
Backlit Display eliminates need
to bend or twist conductors or
place your head near or in the
panel and allows you to easily
read the bottom display when
taking measurements







TIGHTSIGHT® CLAMP METERS





61-775
1000A AC/DC
Clamp Meter
TightSight® w/Backlight
CAT IV 600V | CAT III 1000V





61-765 660A AC/DC Clamp Meter TightSight® w/Backlight CAT IV 600V | CAT III 1000V





61-757
600A AC/DC
Clamp Meter
TightSight® w/Backlight
& Flashlight
CAT IV 600V | CAT III 1000V





61-747 400A AC/DC Clamp Meter TightSight® w/Backlight & Flashlight CAT III 600V





61-415
200A AC/DC
Split Jaw Meter
TightSight® w/Backlight
& Flashlight
CAT IV 600V | CAT III 1000V

CONVENTIONAL CLAMP METERS

CLAMP METER ACCESSORIES



61-744 600A AC Clamp Meter 4000 Count & Flashlight CAT III 600V



61-737 400A AC Clamp Meter 4000 Count w/Backlight CAT III 600V



61-405 200A AC Split Jaw Meter w/Backlight & Flashlight CAT III 600V



TL-757Test Leads
w/Alligator Clips



TC-757 Thermocouple



UMHS-757Universal Magnetic
Hanging Strap



C-757Nylon Carrying Case

IMPORTANT: The clamp meters on this page are intended for use by qualified electricians. Follow the NFPA 70E Standard for Electrical Safety in the workplace when using this tester. Always consult the instruction manual provided with the tester for operational limitations and procedures associated with a specific tester.

CLAMP METER SPECIFICATIONS

CLAMP METER SELECTION GUIDE	TALL TOUT		NEW	NEW
	61-775	61-765	61-757	61-747
FEATURES				
CAT Rating (Safety)	CAT IV 600V CAT III 1000V	CAT IV 600V CAT III 1000V	CAT IV 600V CAT III 1000V	CAT III 600V
Listing	cULus, CE, RCM	cULus, CE, RCM	cULus, CE, RCM	cULus, CE, RCM
Drop Protection			6.6 ft. (2m)	6.6 ft. (2m)
Clamp/Jaw Opening	2.0 in. (50.8mm)	1.5 in. (38mm)	1.4 in. (35.5mm)	1.4 in. (35.5mm)
AC Voltage (Volts)	750V	750V	600V	600V
DC Voltage (Volts)	750V	750V	1000V	600V
AC Current (Amps)	1000A	660A	600A	400A
DC Current (Amps)	1000A	660A	600A	400A
Ohms (Resistance)	999.9Ω	999.9Ω	60ΜΩ	40ΜΩ
AC Millivolts	_	_	6000	4000
DC Millivolts	_		6000	4000
True RMS	V	<u> </u>	✓	✓
High Voltage Alarm	✓	<u> </u>	ACV/DCV >30V	ACV/DCV >30V
Audible Continuity	✓	<u> </u>	✓	✓
Visual Continuity	✓	✓	✓	V
Backlight	✓	✓	✓	✓
Temperature	-	-	-40°F ~ 1832°F -40°C ~ 1000°C	-40°F ~ 1832°F -40°C ~ 1000°C
Low Impedance (LoZ)	_		Yes	_
NCV	-	<u> </u>	40-600V	40-600V
Auto Ranging	✓	<u> </u>	✓	✓
Range Hold	-	-	V	V
Data Hold	✓	✓	✓	✓
Relative	✓	✓	✓	✓
Diode Test	_	_	✓	✓
Capacitance Test	✓	✓	6.000mF	4.000mF
Frequency / Duty Cycle	✓	✓	10Hz~9.999KHz	10Hz~9.999KHz
Max / Min	V	✓	✓	✓
Magnetic Strap Mount	_	_	V	✓
Test Probe Holder	_	_	V	V
Flashlight	_	_	V	V
Auto-Power Off (APO)	✓	V	V	V
APO Disable	V	<u> </u>	V	V
Low Battery Indication	V	<u> </u>	V	V
Battery Type (included)	1 x 9 Volt	1 x 9 Volt	3 x 1.5V AAA	3 x 1.5V AAA
Bottom LCD Display	✓ ✓	✓ ✓	✓ × 1.5 × 7 · 0 · 0	✓ × 1.5 × 7 € € €
LCD Display Count	9999	9999	6000	4000
Warranty	2-Year*	2-Year*	2-Year*	2-Year*
ACCESSORIES				

CLAMP METER SPECIFICATIONS

CLAMP METER SELECTION GUIDE	1888	NEW	NEW	NEW
	61-744	61-737	61-415	61-405
FEATURES			CAT IV 600V	
CAT Rating (Safety)	CAT III 600V	CAT III 600V	CAT IV 600V CAT III 1000V	CAT III 600V
Listing	cULus, CE, RCM	cULus, CE, RCM	cULus, CE, RCM	cULus, CE, RCM
Drop Protection		3.3 ft. (1m)	6.6 ft. (2m)	3.3 ft. (1m)
Clamp/Jaw Opening	1.45 in. (36.5mm)	1.4 in. (35.5mm)	0.75 in. (19mm)	0.75 in. (19mm)
AC Voltage (Volts)	600V	600V	1000	1000
DC Voltage (Volts)	600V	600V	1000	1000
AC Current (Amps)	600A	400A	200	200
DC Current (Amps)			200 60MΩ	
Ohms (Resistance) AC Millivolts	401/122	4000	221000	001v12 2
DC Millivolts		4000	V	
	_	4000	V	V
True RMS	_	-	-	-
High Voltage Alarm Audible Continuity	-	ACV/DCV >30V	ACV/DCV >30V	ACV/DCV >30V
-		V	V	V
Visual Continuity	_	V	V	V
Backlight	_	-40°F ~ 1832°F	V	V
Temperature	_	-40°C ~ 1000°C	_	_
Low Impedance (LoZ)	_	_	_	_
NCV	70-600V	40-600V	40-600V	40-600V
Auto Ranging	✓	✓	✓	✓
Range Hold	✓	✓	✓	✓
Data Hold	✓	✓	✓	✓
Relative	_	✓	✓	✓
Diode Test	_	✓	✓	✓
Capacitance Test	_	400.0µF	6.000mF	6.000mF
Frequency / Duty Cycle	_	10Hz~9.999KHz	_	_
Max / Min	-	✓	✓	✓
Magnetic Strap Mount	_	✓	✓	✓
Test Probe Holder	_	✓	✓	V
Flashlight	_	_	✓	✓
Auto-Power Off (APO)	✓	✓	V	✓
APO Disable	_	_	✓	✓
Low Battery Indication	✓	V	V	✓
Battery Type (included)	2 x 1.5V AAA	3 x 1.5V AAA	2 x 1.5V AAA	2 x 1.5V AAA
Bottom LCD Display	_	_	✓	_
LCD Display Count	4000	4000	6000	6000
Warranty	2-Year*	2-Year*	2-Year*	2-Year*
ACCESSORIES				
Leads, Case & Batteries	Leads only	Included	Included	Included
Thermocouple	_	Included	_	_

MULTIMETER VS. CLAMP/FORK METER



Safety - A fork meter allows you to measure AC or DC current (depending on the model) by positioning the fork around a conductor, which is much safer than making direct contact with a live circuit.

Productivity - During a measurement, it is not necessary to shut off the circuit carrying current, which improves productivity.

Limited to 200A AC/DC Measurement

No Fuse Protection required



Safety - A clamp meter allows you to measure AC or DC current (depending on the model) by positioning the clamp jaw around a conductor, which is much safer than making direct contact with a live circuit.

Productivity - During a measurement, it is not necessary to shut off the circuit carrying current, which improves productivity. This allows isolation of a conductor being tested in a bundle of conductors.

Limited to 2000A AC/DC Measurement (Hard Clamp)

No Fuse Protection required

Multimeters measure current differently than a fork or clamp meter. To measures current with a multimeter:


• You must insert the multimeter into the circuit to get the current to flow THROUGH the meter and are making direct contact with the live circuit.

To properly conduct a current measurement in accordance with Electrical Safety-related Work Practices (ESWP) you must:

- de-energize the circuit, disconnect the circuit, insert the meter in the circuit, re-energize the circuit to test current
- AND THEN... repeat the whole process again to "remove" the meter from the circuit after the test.

Limited to 10A AC/DC Measurement

Fuse Protection required (due to current pass-through)



DIGITAL MULTIMETERS



DIGITAL MULTIMETERS



61-357 1000V Auto Range TRMS 6000 Count Display Multimeter w/NCVT, Temp, Bar Graph & LoZ CAT IV 600V | CAT III 1000V



61-347 1000V Auto Range TRMS 6000 Count Display Multimeter w/NCVT, & Temp CAT IV 600V | CAT III 1000V



61-337 600V Auto Range Multimeter w/NCVT & Temp CAT III 600V



61-327 600V Manual Range Multimeter w/NCVT CAT III 600V











ACCESSORIES



TL-757 Test Leads



UMHS-757 Universal Magnetic Hanging Strap



F-11A-347357 Fuse for 61-357 & 61-347



F-600mA-347357 Fuse for 61-357 & 61-347



F-10A-337 Fuse for 61-337



F-400mA-337 Fuse for 61-337



TC-757 Thermocouple



C-357 Nylon Carrying Case



Scan this QR code with your smartphone to see a video and learn more

about the testers.



DIGITAL MULTIMETERS FEATURES

DIGITAL MULTIMETER SELECTION GUIDE	NEW	NEW	NEW	NEW
	61-357	61-347	61-337	61-327
FEATURES				
CAT Rating (Safety)	CAT IV 600V CAT III 1000V	CAT IV 600V CAT III 1000V	CAT III 600V	CAT III 600V
Listing	cULus, CE, RCM	cULus, CE, RCM	cULus, CE, RCM	cULus, CE, RCM
Drop Protection	6.6 ft. (2m)	6.6 ft. (2m)	3.3 ft. (1m)	3.3 ft. (1m)
Ingress Protection	IP52	IP52	_	_
AC Voltage (Volts)	1000V	1000V	600V	600V
DC Voltage (Volts)	1000V	1000V	600V	600V
AC Current (Amps)	10A	10A	10A	_
DC Current (Amps)	10A	10A	10A	-
Ohms (Resistance) AC Millivolts	60MΩ 6000	60MΩ 6000	40MΩ 4000	4MΩ
DC Millivolts	6000	6000	4000	4000
AC Milliamps	6000	6000	4000	4000
·				_
DC Milliamps AC Microamps	6000 6000	6000 6000	4000 4000	_
DC Microamps	6000	6000	4000	_
True RMS	✓	✓	-	_
High Voltage Alarm	ACV/DCV >30V	ACV/DCV >30V	ACV/DCV >30V	ACV/DCV >30V
Audible Continuity	ACV/DCV >50V	ACV/DCV >30V	ACV/DCV >50V	ACV/DCV >30 V
	V	V	V	
Visual Continuity	V	✓	V	
Backlight	-40 ~ 1832°F	-40 ~ 1832°F	-40 ~ 1832°F	V
Temperature	-40 ~ 1000°C	-40 ~ 1652 F -40 ~ 1000°C	-40 ~ 1832 F -40 ~ 1000°C	-
Low Impedance (LoZ)	✓	_	_	_
NCV	V	V	V	-
Auto Ranging	V	✓	✓	_
Range Hold	✓	✓	✓	-
Data Hold	✓	✓	✓	✓
Diode Test	✓	✓	✓	✓
Capacitance Test	6000 µF	6000 μF	4000 μF	_
Frequency / Duty Cycle	10Hz - 9.99 KHz	10Hz - 9.99 KHz	10Hz - 9.99 KHz	10Hz - 9.99 KHz
Max / Min	✓	✓	✓	_
Magnetic Strap Mount	✓	✓	✓	✓
Test Probe Holder	✓	✓	✓	✓
Auto-Power Off	✓	✓	✓	✓
APO Disable	✓	✓	✓	✓
Low Battery Indication	V	V	✓	✓
Battery Type (included)	3 x 1.5V AAA	3 x 1.5V AAA	3 x 1.5V AAA	3 x 1.5V AAA
LCD Display Count	6000	6000	4000	2000
Lead Warning	✓	✓	✓	_
Fuse Notification	✓	✓	✓	_
Bar Graph	✓	_	_	_
Battery Test	_	_	_	✓
Warranty	2-Year*	2-Year*	2-Year*	2-Year*
Accessories				
Leads, Case & Temp. Sensor	Included	Included	Included	Leads Only
Thermocouple	Included	Included	Included	_

VOLTAGE TESTERS



Scan this QR code with your smartphone to see a video and learn more about the testers.







UMHS-757 Universal Magnetic Hanging Strap (61-557)



TL-757 Test Leads









VOLTAGE TESTERS FEATURES



61-557

Voltage and Continuity Tester
w/LCD, GFCI, Flashlight & NCVT
6-600V AC/DC
CAT IV 600V



61-547
8 Level AC/DC Voltage Indicator
with Polarity Indicator
12-600V DC | 24-600V AC
CAT III 600V



61-076Vol-Con® Voltage/Continuity Tester
5-600V AC/DC
CAT III 600V



61-065Vol-Test® Voltage Tester
100-600V AC/DC
CAT III 600V

















VOLTAGE TESTER SELECTION GUIDE











	61-557	61-547	61-076	61-065
FEATURES				
CAT Rating (Safety)	CAT IV 600V	CAT III 600V	CAT III 600V	CAT III 600V
Listing Preferred	cULus, CE	cULus, CE	cULus	cULus
Drop Protection	6.6 ft. (2m)	6.6 ft. (2m)		
Ingress Protection	IP42	IP42	_	_
AC Voltage (Volts)	6 ~ 600	24 ~ 600	5 ~ 600	100 ~ 600
DC Voltage (Volts)	6 ~ 600	12 ~ 600	5 ~ 600	100 ~ 600
High Voltage Alarm	ACV >36 or DCV >50V	ACV/DCV >48V	-	_
Audible Continuity	✓	_	_	_
Visual Continuity	✓	_	✓	_
Backlight	✓	_	_	_
Low Impedance (LoZ)	✓	_	V	✓
NCV	90-600V AC	_	_	_
Auto Ranging	✓	-	_	_
Magnetic Strap Mount	✓	✓	_	_
Test Probe Holder	✓	✓	✓	✓
Flashlight	✓	_	_	_
Auto-Power Off (APO)	✓	_	_	_
Low Battery Indicator	✓	_	_	_
Battery Type (included)	3 x 1.5V AAA	_	4 x 1.5V LR44	_
LCD Display Count	600	_	_	_
Backlight	✓	_	_	_
DC Polarity Indication	✓	✓	V	_
Leads	Removable	Fixed	Removable	Removable
GFCI Test	✓	_	_	_
Display	LCD	Neon Lamps	Indicator Movement	Indicator Movement
Warranty	2-Year*	2-Year*	2-Year*	2-Year*
ACCESSORIES				
Test Leads	TL-757	_	61-070	61-070
Magnetic Hanging Strap	UMHS-757	UMHS-757	_	_

RECEPTACLE TESTERS

Scan this QR code with your smartphone to learn more about the testers.



FEATURES







On/Off ButtonConfirms Tester
is Working



Green Lights Indicate Correct Wiring



Red Lights
Indicate Incorrect
Wiring



LEDs Easily VisiblePlugged in or rotated to fit receptacles.

RECEPTACLE TESTER FEATURES



61-517
120V AC GFCI
Receptacle/Voltage
Tester
CAT II 150V AC



61-051 E-Z Check® Plus GFCI Circuit Tester



61-035 E-Z Check® Circuit Tester



61-501GFCI Receptacle
Tester













2-Year*



11

1-Year

RECEPTACLE TESTER SELECTION GUIDE	NEW NEW	THE SECOND	The state of the s	
	61-517	61-051	61-035	61-501
FEATURES				
Voltage Rating	120V AC	120V AC	120V AC	120V AC
Polarity Indication	✓	V	✓	V
GFI Trip	V	V	_	V
UL Listed	✓	V	/	V
Made in the USA	_	V	V	_
Premium Neon Lamps	_	V	V	V

2-Year*


Specifications are subject to change without notice.

LCD Display Warranty

2-Year*

NON-CONTACT VOLTAGE TESTERS

FEATURES



Scan this QR code with your smartphone to learn more about the testers.



NON-CONTACT VOLTAGE TESTERS FEATURES



61-657 Dual Range 12 to 1000V AC NCVT w/Flashlight **CAT IV 1000V**

61-647 Single Range 50 to 1000V AC NCVT w/Flashlight **CAT IV 1000V**

61-637 Single Range 24 to 600V AC NCVT w/Flashlight CAT IV 600V

61-627 Single Range 50 to 600V AC NCVT CAT IV 600V













Dual Range on 61-657 only.



Standard Voltage Range Indicated by a Red LED



Power On Indicated by a Green LED



Low Voltage Range Indicated by a Blue LED



Presence of Voltage Indicated by a Flashing Red LED & Audible Tone

NON-CONTACT VOLTAGE TESTERS FEATURES

NON-CONTACT VOLTAGE TESTER SELECTION GUIDE	NEW	NEW	NEW	NEW
	61-657	61-647	61-637	61-627
FEATURES				
CAT Rating (Safety)	CAT IV 1000V	CAT IV 1000V	CAT IV 600V	CAT IV 600V
Listing	cULus, CE, RCM	cULus, CE, RCM	cULus, CE, RCM	cULus, CE, RCM
Voltage Sensing Range	12 ~ 1000V AC	50 ~ 1000V AC	24 ~ 600V AC	50 ~ 600V AC
Dual Range	✓	_	_	_
Flashlight	✓	✓	✓	_
Drop Protection	6.6 ft. (2m)	6.6 ft. (2m)	3.3 ft. (1m)	3.3 ft. (1m)
Ingress Protection	IP67	IP67	_	_
Dual Range Sensitivity	✓	_	_	_
Audible Indication	✓	✓	✓	✓
Audible Defeat	✓	✓	✓	_
Visual Indication	Green On, Flashing Red	Green On, Flashing Red	Green On, Flashing Red	Green On, Flashing Red
Visual Range Indicator	Blue Low, Red High	_	_	_
Lanyard Compatible	V	✓	✓	✓
Auto-Power Off (APO)	✓	V	✓	✓
Low Battery Indication	V	V	V	V
Battery Type (included)	2 x 1.5V AAA			
Warranty	2-Year*	2-Year*	2-Year*	2-Year*

INFRARED THERMOMETERS

FEATURES

Scan this QR code with your smartphone to learn more about the thermometers.























Complies with 21 CFR 1040.10 and 1040.11 except for conformance with IEC 60825-1 Ed. 3 as described in Laser Notice No. 56 dated May 8, 2019.

Specifications are subject to change without notice.

INFRARED THERMOMETER SELECTION GUIDE



Grip



	61-847	61-827
FEATURES		
Listing	cULus	cULus
Certification	CLASS 2, IEC 60825-1:2014	CLASS 2, IEC 60825-1:2014
Wavelength	630nm-670nm	630nm-670nm
Output	< 1mW	< 1mW
Listing	cULs, CE	cULs, CE
Drop Protection	6.6 ft. (2m)	3.3 ft. (1m)
Optical Resolution (distance-to-spot)	12 : 1	10 : 1
Measurement Range	-26° - 932°F (-32° to 500°C)	-4° to 752°F (-20° to 400°C)
Laser Targeting	Dual	Single
Auto Scan	✓	_
Max/Min/Avg/Diff	✓	_
High/Low Alarm	✓	_
Data Hold	✓	✓
Lock-on (for continuous measurements)	✓	_
Emissivity	0.10 - 1.00 Adjustable	0.95 Fixed
Backlit Display	✓	✓
Display	LCD	LCD
Auto Power-Off	✓	✓
Selectable Celsius / Fahrenheit	✓	✓
Battery Type (included)	2 x 1.5V AAA	2 x 1.5V AAA
Low Battery Indicator	✓	V
Response Time	250 ms	500 ms
Spectral Response	8 to 14µm	8 to 14µm
Warranty	2-Year*	2-Year*

SPECIALTY TESTERS



61-520 3-Phase Rotation Tester



61-521 3-Phase Motor/Rotation Tester



61-797 Insulation Tester w/PI, DAR



61-795 Insulation Tester











61-796 3-Pole Ground Resistance Tester



61-920Ground Resistance
Clamp Meter





61-686Digital Light
Meter





SPECIALTY TESTERS FEATURES







TL-521Test Lead Set



TL-795Test Lead Set w/Premium Alligator Clips

TL-797RPRemote Probe
Test Lead Set

GROUND ROD TESTING SELECTION GUIDE 61-796 61-920 **FEATURES** 3 Point Fall of Potential Method Clamp on Technique Auto Ranging 0 - 1200 Ω Measuring Range $0 - 2000 \Omega$ 100mA/1000mA/ Ground Leakage Current 15A/30A Warranty 2-Year* 2-Year* **ACCESSORIES (Included)** TL-796 Test Leads





TL-796Earth Resistance Lead Set

ACCESSORIES



TL-532A 120V AC Circuit Breaker Finder Adapter Kit




TL-757Universal Test Leads & Alligator Clips



UMHS-757
Universal Magnetic
Hanging Strap
(For use with 61-405, 61-415, 61-737, 61-747, 61-757, 61-327, 61-337, 61-347, 61-357, 61-547 & 61-557)



TC-757 Thermocouple



TL-521 Test Lead Set



TL-796Earth Resistance
Lead Set



TL-797RPRemove Probe
Test Lead



TL-795Test Leads w/
Alligator Clips
(premium)




61-070 Standard Test Leads (for use with 61-076 & 61-065)



TL-956 Test Lead Set

TEST LEAD SELECTION GUIDE



CARRYING CASES



61-179Nylon Carrying
Case



C-90Nylon Carrying
Case



C-290Nylon Carrying
Case

NEW



C-760Nylon Carrying
Case

NEW



C-770Nylon Carrying
Case



C-357 Nylon Carrying Case



C-757Nylon Carrying
Case

			OLTA(160		30	00		40	00		70	00		740	770	790
Selectio	n Guide	61-065	61-076	61-164	61-327	61-337	61-347	61-357	61-405	61-415	61-727	61-737	61-747	61-757	61-744	61-775	61-797
61-179	Nylon Carrying Case																
C-90	Nylon Carrying Case	•													•		
C-290	Nylon Carrying Case																•
C-357	Nylon Carrying Case				•	•	•	•									
C-760	Nylon Carrying Case														•		
C-757	Nylon Carrying Case								•	•	•	•	•	•			
C-770	Nylon Carrying Case															•	

REPLACEMENT PARTS SELECTION GUIDE

			090	070			300			74	400		500			730		740	750	760	770		790		950
			61-0	61-0	61-3	61-3	61-3	61-3	61-3	61-4	61-5	61-5	61-5	61-5	61-5	61-7	61-7	61-7	61-7	61-7	61-7	61-7	61-7	61-7	TR-9
SELECTION GUIDE			65	76	27	_							34	47	57	37	44	47	57	65	75	95	96	97	955
FUSES																									
F-105	1A (600V)	10.3 x 35mm																				•			
F-340	0.5A (500V)	6.35 x 32mm					•	•																	
F-341	10A (1000V)	10 x 38mm					•	•																	
F-400mA-337	400mA (600V)	6.5 x 32mm				•																			
F-10A-337	10A (600V)	10 x 38mm				•																			
F-600mA-347357	600mA (1000V) 6.5 x 32 mm	6.5 x 32 mm							•	•															
F-11A-347357	11A (1000V)	10 x 38mm							•	•															
F-497	600mA (1000V) 10 x 35mm	10 x 35mm								-	•														
F-498	11A (1000V)	10 x 38mm																							
F-797	315mA (1000V)	5 x 32mm																						•	
BATTERIES																									
	AA																					•	•	•	•
I	1.5V (AAA)				•	•			•	•					•	•	•	•	•						
I	Λ6										•	•	•							•	•				
	LR44			•																					
TEST LEADS																									
TL-796	Earth Resistance Lead Set	Lead Set																					•		
TL-797RP	Remote Probe Test Lead	est Lead																						•	
61-070	Standard Test Leads	ads	•	•																					
ТL-757	Universal Test Leads & Alligator Clips	ads &			•	•			•	•				•	•	•	•	•	•	•	•				
TL-521	Test Lead Set										•														
TL-795	Test Leads w/Alligator Clips (Premium)	gator Clips																				•		•	
TL-956	Test Lead Set																								•

SAFETY IN THE FIELD

IEC (International Electrotechnical Commission) Category Ratings



Category I - The signal level for telecommunications, electronic and other low-energy equipment with transient limiting protection. Peak impulse transient range is 600-4,000 volts with 30 ohm source.



Category II – The local level for fixed and non-fixed powered devices including appliances, lighting and portable equipment. Outlets located more than 30 feet from CAT III sources and 60 feet from CAT IV sources. Peak impulse transient range is from 600-6.000 volts with a 12 ohm source.




Category III - The distribution level for fixed primary feeders or branch circuits. Circuits that are separated from CAT IV sources by at least one level of transformer isolation. Peak impulse transient range is 600-8,000 volts with a 2 ohm source.



Category IV – The primary supply level for the highest levels of transient over voltage. Includes the utility service both outside and at the service entrance, service drop from the pole to the building, overhead line to remote buildings, and underground line to a well pump. Peak impulse transient range is 600-12,000 volts with less than a 1 ohm source.

Visit idealind.com for more technical product details, application support, white papers, videos and software.



CAT I Copiers

- Electronic equipment
- Low energy equipment with transient limiting protection

CAT II Appliances, PCs, TVs


- Outlets and long branch equipment
- All outlets at more than 10m (30 ft) from Category III source
- All outlets at more than 20m (60 ft) from Category IV source

CAT III MC Panels

- Feeders and short branch circuits
- Distribution panel devices
- Heavy appliance outlets with "short" connections to service entrance

CAT IV Exterior Transformers, Meters

- Outside and service entrance
- Service drop from pole to building
- Overhead line to detached building
- Underground line to well pump







Scan here to visit us at idealind.com

A DIVISION OF



1800 S. Prairie Drive, Sycamore, IL 60178, USA (815) 895-5181 | (800) 435-0705 in USA

For complete sales office contact information, visit us at idealindustries.com. International offices. Australia | Canada | China | India | Mexico | UK

4/21 Printed in U.S.A. Form No. P-6043 ©2021 IDEAL INDUSTRIES, INC.