

IHM-B module with Trench/Fieldstop IGBT4 and Emitter Controlled 4 diode

Features

- Electrical features
 - $V_{CES} = 4500\text{ V}$
 - $I_{C\text{nom}} = 1800\text{ A} / I_{CRM} = 3600\text{ A}$
 - High DC stability
 - High dynamic robustness
 - High short-circuit capability
 - Low V_{CESat}
 - Trench IGBT 4
 - V_{CESat} with positive temperature coefficient
- Mechanical features
 - Package with CTI > 600
 - Standard housing
 - ALSiC base plate for increased thermal cycling capability
 - IHM B housing
 - Isolated base plate



Potential applications

- Wind turbines
- High power converters
- Medium voltage converters
- Motor drives
- UPS systems

Product validation

- Qualified for industrial applications according to the relevant tests of IEC 60747, 60749 and 60068

Description




Table of contents

	Description	1
	Features	1
	Potential applications	1
	Product validation	1
	Table of contents	2
1	Package	3
2	IGBT, Inverter	3
3	Diode, Inverter	5
4	Characteristics diagrams	7
5	Circuit diagram	11
6	Package outlines	12
7	Module label code	13
	Disclaimer	14

1 Package

Table 1 Insulation coordination

Parameter	Symbol	Note or test condition	Values	Unit
Isolation test voltage	V_{ISOL}	RMS, $f = 50$ Hz, $t = 1$ min	6.0	kV
Partial discharge extinction voltage	V_{isol}	RMS, $f = 50$ Hz, $Q_{PD} \leq 10$ pC	3.5	kV
DC stability	$V_{CE(D)}$	$T_{vj} = 25^\circ\text{C}$, 100 Fit	2900	V
Material of module baseplate			AlSiC	
Creepage distance	d_{Creep}	terminal to heatsink	32.2	mm
Clearance	d_{Clear}	terminal to heatsink	19.1	mm
Comparative tracking index	CTI		> 600	

Table 2 Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit	
			Min.	Typ.	Max.		
Stray inductance module	L_{SCE}			6		nH	
Module lead resistance, terminals - chip	$R_{AA'+CC'}$	$T_C = 25^\circ\text{C}$, per switch		0.08		m Ω	
Module lead resistance, terminals - chip	$R_{CC'+EE'}$	$T_C = 25^\circ\text{C}$, per switch		0.095		m Ω	
Storage temperature	T_{stg}		-40		150	$^\circ\text{C}$	
Mounting torque for modul mounting	M	- Mounting according to valid application note	M6, Screw	4.25		5.75	Nm
Terminal connection torque	M	- Mounting according to valid application note	M4, Screw	1.8		2.1	Nm
			M8, Screw	8		10	
Weight	G			1200		g	

2 IGBT, Inverter

Table 3 Maximum rated values

Parameter	Symbol	Note or test condition	Values	Unit	
Collector-emitter voltage	V_{CES}		$T_{vj} = -40^\circ\text{C}$	4500	V
			$T_{vj} = 150^\circ\text{C}$	4500	
Continous DC collector current	I_{CDC}	$T_{vj\ max} = 150^\circ\text{C}$	$T_C = 105^\circ\text{C}$	1800	A
Repetitive peak collector current	I_{CRM}	$t_p = 1$ ms		3600	A
Gate-emitter peak voltage	V_{GES}			-20/+25	V

Table 4 Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Collector-emitter saturation voltage	$V_{CE\ sat}$	$I_C = 1800\ A, V_{GE} = 25\ V$	$T_{vj} = 25\ ^\circ C$	2.15	2.60	V
			$T_{vj} = 125\ ^\circ C$	2.50	3.05	
			$T_{vj} = 150\ ^\circ C$	2.60	3.15	
Gate threshold voltage	V_{GEth}	$I_C = 149\ mA, V_{CE} = V_{GE}, T_{vj} = 25\ ^\circ C$	5.5	6	6.5	V
Gate charge	Q_G	$V_{GE} = \pm 15\ V, V_{CE} = 2800\ V$		47		μC
Internal gate resistor	R_{Gint}	$T_{vj} = 25\ ^\circ C$		0.29		Ω
Input capacitance	C_{ies}	$f = 100\ kHz, T_{vj} = 25\ ^\circ C, V_{CE} = 25\ V, V_{GE} = 0\ V$		297		nF
Reverse transfer capacitance	C_{res}	$f = 100\ kHz, T_{vj} = 25\ ^\circ C, V_{CE} = 25\ V, V_{GE} = 0\ V$		5.4		nF
Collector-emitter cut-off current	I_{CES}	$V_{CE} = 4500\ V, V_{GE} = 0\ V$	$T_{vj} = 25\ ^\circ C$		5	mA
Gate-emitter leakage current	I_{GES}	$V_{CE} = 0\ V, V_{GE} = 20\ V, T_{vj} = 25\ ^\circ C$			400	nA
Turn-on delay time (inductive load)	t_{don}	$I_C = 1800\ A, V_{CE} = 2800\ V, V_{GE} = \pm 15\ V, R_{Gon} = 0.75\ \Omega$	$T_{vj} = 25\ ^\circ C$	0.260		μs
			$T_{vj} = 125\ ^\circ C$	0.290		
			$T_{vj} = 150\ ^\circ C$	0.310		
Rise time (inductive load)	t_r	$I_C = 1800\ A, V_{CE} = 2800\ V, V_{GE} = \pm 15\ V, R_{Gon} = 0.75\ \Omega$	$T_{vj} = 25\ ^\circ C$	0.210		μs
			$T_{vj} = 125\ ^\circ C$	0.230		
			$T_{vj} = 150\ ^\circ C$	0.230		
Turn-off delay time (inductive load)	t_{doff}	$I_C = 1800\ A, V_{CE} = 2800\ V, V_{GE} = \pm 15\ V, R_{Goff} = 4.7\ \Omega$	$T_{vj} = 25\ ^\circ C$	6.930		μs
			$T_{vj} = 125\ ^\circ C$	7.320		
			$T_{vj} = 150\ ^\circ C$	7.410		
Fall time (inductive load)	t_f	$I_C = 1800\ A, V_{CE} = 2800\ V, V_{GE} = \pm 15\ V, R_{Goff} = 4.7\ \Omega$	$T_{vj} = 25\ ^\circ C$	1.130		μs
			$T_{vj} = 125\ ^\circ C$	2.630		
			$T_{vj} = 150\ ^\circ C$	2.850		
Turn-on energy loss per pulse	E_{on}	$I_C = 1800\ A, V_{CE} = 2800\ V, L_\sigma = 110\ nH, V_{GE} = \pm 15\ V, R_{Gon} = 0.75\ \Omega, di/dt = 6500\ A/\mu s (T_{vj} = 150\ ^\circ C)$	$T_{vj} = 25\ ^\circ C$	5800		mJ
			$T_{vj} = 125\ ^\circ C$	8100		
			$T_{vj} = 150\ ^\circ C$	9100		
Turn-off energy loss per pulse	E_{off}	$I_C = 1800\ A, V_{CE} = 2800\ V, L_\sigma = 110\ nH, V_{GE} = \pm 15\ V, R_{Goff} = 4.7\ \Omega, dv/dt = 1250\ V/\mu s (T_{vj} = 150\ ^\circ C)$	$T_{vj} = 25\ ^\circ C$	7050		mJ
			$T_{vj} = 125\ ^\circ C$	9000		
			$T_{vj} = 150\ ^\circ C$	9700		
SC data	I_{SC}	$V_{GE} = 15\ V, V_{CC} = 3000\ V, V_{CEmax} = V_{CES} - L_{sCE} * di/dt$	$t_P \leq 10\ \mu s, T_{vj} = 150\ ^\circ C$	8100		A
Thermal resistance, junction to case	R_{thJC}	per IGBT			7.20	K/kW

Table 4 Characteristic values (continued)

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Thermal resistance, case to heatsink	R_{thCH}	per IGBT, $\lambda_{grease} = 1 \text{ W/(m}^2\text{K)}$		3.60		K/kW
Temperature under switching conditions	T_{vjop}		-40		150	°C

3 Diode, Inverter

Table 5 Maximum rated values

Parameter	Symbol	Note or test condition	Values	Unit	
Repetitive peak reverse voltage	V_{RRM}		$T_{vj} = -40 \text{ °C}$	4500	V
			$T_{vj} = 150 \text{ °C}$	4500	
Continuous DC forward current	I_F		1800	A	
Repetitive peak forward current	I_{FRM}	$t_p = 1 \text{ ms}$	3600	A	
I^2t - value	I^2t	$t_p = 10 \text{ ms}, V_R = 0 \text{ V}$	$T_{vj} = 125 \text{ °C}$	850	kA ² s
			$T_{vj} = 150 \text{ °C}$	930	
Maximum power dissipation	P_{RQM}	$T_{vj} = 150 \text{ °C}$	4000	kW	
Minimum turn-on time	t_{onmin}		10	µs	

Table 6 Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit	
			Min.	Typ.	Max.		
Forward voltage	V_F	$I_F = 1800 \text{ A}, V_{GE} = 0 \text{ V}$	$T_{vj} = 25 \text{ °C}$		2.60	3.05	V
			$T_{vj} = 125 \text{ °C}$		2.50	2.95	
			$T_{vj} = 150 \text{ °C}$		2.45	2.90	
Peak reverse recovery current	I_{RM}	$V_R = 2800 \text{ V}, I_F = 1800 \text{ A}, V_{GE} = -15 \text{ V}, -di_F/dt = 6500 \text{ A/}\mu\text{s} (T_{vj} = 150 \text{ °C})$	$T_{vj} = 25 \text{ °C}$		2360		A
			$T_{vj} = 125 \text{ °C}$		2600		
			$T_{vj} = 150 \text{ °C}$		2630		
Recovered charge	Q_r	$V_R = 2800 \text{ V}, I_F = 1800 \text{ A}, V_{GE} = -15 \text{ V}, -di_F/dt = 6500 \text{ A/}\mu\text{s} (T_{vj} = 150 \text{ °C})$	$T_{vj} = 25 \text{ °C}$		1560		µC
			$T_{vj} = 125 \text{ °C}$		3060		
			$T_{vj} = 150 \text{ °C}$		3560		
Reverse recovery energy	E_{rec}	$V_R = 2800 \text{ V}, I_F = 1800 \text{ A}, V_{GE} = -15 \text{ V}, -di_F/dt = 6500 \text{ A/}\mu\text{s} (T_{vj} = 150 \text{ °C})$	$T_{vj} = 25 \text{ °C}$		2340		mJ
			$T_{vj} = 125 \text{ °C}$		5200		
			$T_{vj} = 150 \text{ °C}$		6100		

Table 6 Characteristic values (continued)


Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Thermal resistance, junction to case	R_{thJC}	per diode			12.7	K/kW
Thermal resistance, case to heatsink	R_{thCH}	per diode, $\lambda_{grease} = 1 \text{ W/(m}^2\text{K)}$		5.30		K/kW
Temperature under switching conditions	$T_{vj\ op}$		-40		150	°C

4 Characteristics diagrams

output characteristic (typical), IGBT, Inverter

$$I_C = f(V_{CE})$$


$$V_{GE} = 25 \text{ V}$$



output characteristic (typical), IGBT, Inverter

$$I_C = f(V_{CE})$$


$$T_{vj} = 150 \text{ °C}$$



transfer characteristic (typical), IGBT, Inverter

$$I_C = f(V_{GE})$$


$$V_{CE} = 20 \text{ V}$$



switching losses (typical), IGBT, Inverter

$$E = f(I_C)$$

$$R_{Goff} = 4.7 \text{ } \Omega, R_{Gon} = 0.75 \text{ } \Omega, V_{GE} = \pm 15 \text{ V}, V_{CE} = 2800 \text{ V}$$




4 Characteristics diagrams

switching losses (typical), IGBT, Inverter


$E = f(R_G)$

$V_{GE} = \pm 15 \text{ V}$, $I_C = 1800 \text{ A}$, $V_{CE} = 2800 \text{ V}$



transient thermal impedance , IGBT, Inverter


$Z_{th} = f(t)$



reverse bias safe operating area (RBSOA), IGBT, Inverter

$I_C = f(V_{CE})$


$V_{CC} \leq 3200 \text{ V}$, $T_{vj} = 150 \text{ }^\circ\text{C}$, $R_{Goff} = 4.7 \text{ } \Omega$, $V_{GE} = \pm 15 \text{ V}$



Switching times (typical), IGBT, Inverter

$t = f(I_C)$

$R_{Goff} = 4.7 \text{ } \Omega$, $R_{Gon} = 0.75 \text{ } \Omega$, $V_{GE} = \pm 15 \text{ V}$, $V_{CE} = 2800 \text{ V}$, $T_{vj} = 150 \text{ }^\circ\text{C}$




4 Characteristics diagrams

Switching times (typical), IGBT, Inverter

$t = f(R_G)$


$V_{GE} = \pm 15\text{ V}$, $I_C = 1800\text{ A}$, $V_{CE} = 2800\text{ V}$, $T_{vj} = 150\text{ }^\circ\text{C}$



capacity characteristic (typical), IGBT, Inverter

$C = f(V_{CE})$


$f = 100\text{ kHz}$, $V_{GE} = 0\text{ V}$, $T_{vj} = 25\text{ }^\circ\text{C}$



gate charge characteristic (typical), IGBT, Inverter


$V_{GE} = f(Q_G)$

$I_C = 1800\text{ A}$, $T_{vj} = 25\text{ }^\circ\text{C}$



forward characteristic (typical), Diode, Inverter

$I_F = f(V_F)$




4 Characteristics diagrams

switching losses (typical), Diode, Inverter

$E_{rec} = f(I_F)$


$R_{Gon} = R_{Gon}(IGBT), V_{CE} = 2800 V$



switching losses (typical), Diode, Inverter


$E_{rec} = f(R_G)$

$V_{CE} = 2800 V, I_F = 1800 A$



transient thermal impedance, Diode, Inverter


$Z_{th} = f(t)$



safe operation area (SOA), Diode, Inverter

$I_R = f(V_R)$

$T_{vj} = 150^\circ C$



5 Circuit diagram




Figure 2

7 Module label code



Module label code			
Code format	Data Matrix	Barcode Code128	
Encoding	ASCII text	Code Set A	
Symbol size	16x16	23 digits	
Standard	IEC24720 and IEC16022	IEC8859-1	
Code content	Content	Digit	Example
	Module serial number	1 - 5	71549
	Module material number	6 - 11	142846
	Production order number	12 - 19	55054991
	Date code (production year)	20 - 21	15
	Date code (production week)	22 - 23	30
Example			
	71549142846550549911530		71549142846550549911530

Figure 4

Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

Edition 2021-04-16

Published by

Infineon Technologies AG

81726 Munich, Germany

© 2021 Infineon Technologies AG

All Rights Reserved.

Do you have a question about any aspect of this document?

Email: erratum@infineon.com

Document reference

IFX-

IMPORTANT NOTICE

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

Please note that this product is not qualified according to the AEC Q100 or AEC Q101 documents of the Automotive Electronics Council.

WARNINGS

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.