


Part Number: 195DX35XM

Type	Size	Rating	Description
LED	M22	24Vac/dc	Flat Bezel Panel Indicator



Part #	Colour	Current (mA)	Intensity (mcd)
195DX350M	Red	8/16	160
195DX351M	Green	8/16	400
195DX352M	Yellow	8/16	350
195DX357M	Blue	8/16	280
195DX35WMA	White	8/16	900

Notes:

- 1 X = Chrome Bezel finish. 0 = Satin, 1 = Black, 2 = Matt
- 2 Electrical & optical data are measured at an ambient temperature of 25°C
- 3 Storage temperature -25 °C to +80°C
- 4 Application temperature -20 °C to +60°C
- 5 Voltage tolerance ±10%
- 6 Due to component tolerances, colour temperature variations may be observed
- 7 The terminals are not qualified for soldering
- 8 Degree of protection IP67 when used with the supplied gasket
- 9 The plastic(polycarbonate) has limited chemical resistance
- 10 RoHS & REACH SVHC compliant