



Product data sheet

Power tools for trade & industry

Cordless Combi

GSB 12V-15



Drill driver with the best power-to-size ratio in Bosch's 12 V category – with impact drilling function

The most important data

Battery voltage	12 V
Max. drilling diameter in masonry	10 mm
Max. screw diameter	7 mm

Part Number 0 601 9B6 901

[> More product information](#)

Technical data

Technical data

Torque (soft/hard/max.)	15/30/- Nm
No-load speed (1st gear / 2nd gear)	0 – 380 / 0 – 1,300 rpm
Max. impact rate	19,500 bpm
Chuck capacity, min./max.	1 / 10 mm
Battery voltage	12 V
Torque settings	20+1
Tool dimensions (height)	175 mm
Packaging dimensions (width x length x height)	220 x 335 x 80 mm
Clamping range, min.	0 mm
Clamping range, max.	0 mm
Spindle collar diameter	0 mm
Weight incl. battery	1 kg

'Total vibration values (Drilling in metal)'

Vibration emission value ah	2.5 m/s ²
Uncertainty K	1.5 m/s ²

'Total vibration values (Impact drilling in masonry)'

Vibration emission value ah	10.5 m/s ²
Uncertainty K	1.5 m/s ²

'Total vibration values (Screwdriving)'

Vibration emission value ah	2.5 m/s ²
-----------------------------	----------------------

Uncertainty K	1.5 m/s ²
---------------	----------------------

Drilling diameter

Max. drilling diameter in wood	19 mm
Max. drilling diameter in steel	10 mm
Max. drilling diameter in masonry	10 mm

Screw diameter

Max. screw diameter	7 mm
---------------------	------

Noise/vibration information

Drilling in metal

Vibration emission value ah	2.5 m/s ²
Uncertainty K	1.5 m/s ²

Impact drilling in masonry

Vibration emission value ah	10.5 m/s ²
Uncertainty K	1.5 m/s ²

Screwdriving

Vibration emission value ah	2.5 m/s ²
Uncertainty K	1.5 m/s ²

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- 30 Nm hard torque and 0-1,300 rpm offer an ideal combination of power and size
- Compactness enables optimum handling and makes it ideal for working overhead and in tight spaces
- Electronic Cell Protection prevents overload, overheating, and deep discharge

