



Product data sheet

Power tools for trade & industry

Cordless Drill/Driver

GSR 18V-28



Professional performer in the 18 V category

The most important data

| | |
|----------------------|--------|
| Battery voltage | 18 V |
| Max. screw diameter | 8 mm |
| Weight excl. battery | 1.1 kg |

Part Number 0 601 9H4 100

[> More product information](#)

Technical data

Technical data

| | |
|-------------------------------------|-------------------------|
| Torque (soft/hard/max.) | 28/63/- Nm |
| No-load speed (1st gear / 2nd gear) | 0 – 500 / 0 – 1,900 rpm |
| Battery type | Lithium-ion |
| Chuck capacity, min./max. | 1.5 / 13 mm |
| Battery voltage | 18 V |
| Weight excl. battery | 1.1 kg |
| Torque settings | 20+1 |

'Total vibration values (Drilling in metal)'

| | |
|-----------------------------|----------------------|
| Vibration emission value ah | 2.5 m/s ² |
| Uncertainty K | 1.5 m/s ² |

Drilling diameter

| | |
|---------------------------------|-------|
| Max. drilling diameter in wood | 38 mm |
| Max. drilling diameter in steel | 13 mm |

Screw diameter

| | |
|---------------------|------|
| Max. screw diameter | 8 mm |
|---------------------|------|

Noise/vibration information

Drilling in metal

| | |
|-----------------------------|----------------------|
| Vibration emission value ah | 2.5 m/s ² |
| Uncertainty K | 1.5 m/s ² |

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- 63 Nm of hard torque ensures professional performance
- 13-mm full-metal chuck makes it highly durable, ensuring less wear and longer use
- Compact ergonomic design enables comfortable handling for convenient work

