



Product data sheet

Power tools for trade & industry

Cordless Combi

GSB 18V-21



Reliable entry-level cordless combi drill in the 18 V category
- with impact drilling function

The most important data

Battery voltage	18 V
Max. drilling diameter in masonry	10 mm
Max. screw diameter	10 mm

Part Number 0 601 9H1 108[> More product information](#)

Technical data

Technical data

Torque (soft/hard/max.)	21/55/- Nm
No-load speed (1st gear / 2nd gear)	0 – 480 / 0 – 1,800 rpm
Battery type	Lithium-ion
Max. impact rate	27,000 bpm
Chuck capacity, min./max.	1.5 / 13 mm
Battery voltage	18 V
Weight excl. battery	1.2 kg
Torque settings	20+2

'Total vibration values (Drilling in metal)'

Vibration emission value ah	2.5 m/s ²
Uncertainty K	1.5 m/s ²

'Total vibration values (Impact drilling in masonry)'

Vibration emission value ah	11 m/s ²
Uncertainty K	1.5 m/s ²

Drilling diameter

Max. drilling diameter in wood	35 mm
Max. drilling diameter in steel	10 mm
Max. drilling diameter in masonry	10 mm

Screw diameter

Max. screw diameter	10 mm
---------------------	-------

Noise/vibration information

Drilling in metal

Vibration emission value ah	2.5 m/s ²
Uncertainty K	1.5 m/s ²

Impact drilling in masonry

Vibration emission value ah	11 m/s ²
Uncertainty K	1.5 m/s ²



Product data sheet

Power tools for trade & industry

Advantages:

- 55 Nm of hard torque delivers the performance necessary for the basic drilling and drill driving applications
- Reliability, durability, and professional quality for daily use due to full-metal gear box and Electronic Cell Protection
- Professional design with keyless 13-mm chuck enables quality work

