



# Product data sheet

Power tools for trade &amp; industry

Cordless Combi

## GSB 18V-28



Professional performer in the 18 V category - with impact drilling function

### The most important data

Battery voltage	18 V
Max. drilling diameter in masonry	13 mm
Max. screw diameter	8 mm

**Part Number** 0 601 9H4 000[> More product information](#)

## Technical data

### Technical data

Torque (soft/hard/max.)	28/63/- Nm
No-load speed (1st gear / 2nd gear)	0 – 500 / 0 – 1,900 rpm
Battery type	Lithium-ion
Max. impact rate	28,500 bpm
Chuck capacity, min./max.	1.5 / 13 mm
Battery voltage	18 V
Weight excl. battery	1.2 kg
Torque settings	20+2

### 'Total vibration values (Drilling in metal)'

Vibration emission value ah	2.5 m/s <sup>2</sup>
Uncertainty K	1.5 m/s <sup>2</sup>

### 'Total vibration values (Impact drilling in masonry)'

Vibration emission value ah	11.5 m/s <sup>2</sup>
Uncertainty K	1.5 m/s <sup>2</sup>

### Drilling diameter

Max. drilling diameter in wood	38 mm
Max. drilling diameter in steel	13 mm
Max. drilling diameter in masonry	13 mm

### Screw diameter

Max. screw diameter	8 mm
---------------------	------

## Noise/vibration information

### Drilling in metal

Vibration emission value ah	2.5 m/s <sup>2</sup>
Uncertainty K	1.5 m/s <sup>2</sup>

### Impact drilling in masonry

Vibration emission value ah	11.5 m/s <sup>2</sup>
Uncertainty K	1.5 m/s <sup>2</sup>



**BOSCH**

Invented for life

# Product data sheet

Power tools for trade & industry

---

## Advantages:

- 63 Nm of hard torque ensures professional performance
- 13-mm full-metal chuck makes it highly durable, ensuring less wear and longer use
- Compact ergonomic design enables comfortable handling for convenient work

63/28  
Nm

